

WSI 25CC
WSI 25 10x38

WSI 25CC/LED
WSI 25 10x38/LED

NEW



Weidmüller offers DIN rail mounted terminal blocks for the popular 10.3 mm x 38 mm (13/32" x 1.5") midjet fuses. Compact and touch safe, these terminals meet CSA, UL and IEC requirements.

Features:

- CSA certified for 600 Vac, 30 A max.
- UL rated 600 Vac, 30 A max.
- 1, 2, 3 pole with or without indicator
- Mounting on 35 mm DIN rail
- Only 17.8 mm wide per pole
- Lever mechanism for quick and safe fuse replacement
- Vented housing to reduce internal heating and extend fuse life
- 3 W power dissipation maximum
- Two versions are available:
 - WSI 25 10x38 accepts all types of 13/32" x 1.5" midjet fuses including CC type.
 - WSI 25CC ONLY accepts CC type fuses which have a typical interrupting capacity of 200kA and in compliance to UL508A standard.
- Both version are available with or without LED

Canada

W Interconnections Canada Inc.
10 Spy Court
Markham, Ontario L3R 5H6
Telephone: (800) 268-4080
Facsimile: (905) 475-2798
Email: info1@weidmuller.ca
Website: www.weidmuller.ca

United States

W Interconnections, Inc.
821 Southlake Blvd.
Richmond, Virginia 23236
Telephone: (800) 849-9343
Facsimile: (804) 379-2593
Email: info@weidmuller.com
Website: www.weidmuller.com

Mexico

W Interconnections, S.A. de C.V.
Boulevard Hermanos Serdán 698
Col. San Rafael Oriente, C.P. 72029
Puebla, Pue. Mexico
Telephone: (222) 268 62 27
Facsimile: (222) 268 62 19
Website: www.weidmuller.com.mx

Fuse terminals

WSI 25 10x38

25 mm²

WSI 25 CC

25 mm²

For fuses 10x38



width x length x height with TS 35 x 7.5	mm
max. current / max. cond. cross-section	A/mm ²
max. clamping range	mm ²

17.8 x 58 x 81
32 / 25
1.5 ... 25

17.8 x 58 x 81
32 / 25
1.5 ... 25



Technical data

Rated data	
Rated voltage, adjacent terminal	V
Rated current	A
Rated cross-section	mm ²
Rated isolation voltage	V
Power loss 1 pole / 2 pole / 3 pole	
UL94 Flammability class	
Approvals	
Allowable power dissipation for standard version fuse	
Allowable power dissipation for semi-conductor protection version fuse	
Interrupting Capacity	
Clamped conductors (H05V/H07V)	
Solid / stranded	mm ²
Flexible / Flexible with wire end ferrule	mm ²
Tightening torque range (clamping screw)	Nm
Stripping length	mm
Note	

IEC 60947-7-3			
IEC	UL	CSA	EN 60079-7
690	600	600	
32	30	30	
25	AWG 18 ... 4	AWG 18 ... 4	
800			
0.3 / 0.6 / 0.9			
V-0			
			
3W			
4.3W (10mm², 25A)			
Rated connection			
1.5 ... 16 / 1.5 ... 16			
0.75 ... 25 / 0.75 ... 25			
2.0 ... 2.4			
11			

IEC 60947-7-3			
IEC	UL	CSA	EN 60079-7
690	600	600	
32	30	30	
25	AWG 18 ... 4	AWG 18 ... 4	
800			
0.3 / 0.6 / 0.9			
V-0			
			
200kA			
Rated connection			
1.5 ... 16 / 1.5 ... 16			
0.75 ... 25 / 0.75 ... 25			
2.0 ... 2.4			
11			

Ordering data

Version
1 pole without LED
2 pole without LED
3 pole without LED
1 pole with LED
2 pole with LED
3 pole with LED

Note

Type	Qty.	Order No.
WSI 25/1 10x38	12	1966020000
WSI 25/2 10x38	6	1966090000
WSI 25/3 10x38	4	1966080000
WSI 25/1 10x38/LED	12	1966060000
WSI 25/2 10x38/LED	6	7940029427
WSI 25/3 10x38/LED	4	7940029428

LED: 110-600Vac/dc, 2mA leakage

Type	Qty.	Order No.
WSI 25/1 CC	12	1966050000
WSI 25/2 CC	6	1966040000
WSI 25/3 CC	4	1966030000
WSI 25/1 CC/LED	12	1966070000
WSI 25/2 CC/LED	6	7940029425
WSI 25/3 CC/LED	4	7940029426

LED: 110-600Vac/dc, 2mA leakage


Accessories

- Marking Systems
- 2 pole ganging kit
- 3 pole ganging kit
- Single phase bus bar (insulated)

Type	Qty.	Order No.
ESG 6/15 K MC WHITE	200	1880100000
SET 2 POLE WSI 25	10	1044440000
SET 3 POLE WSI 25	10	1044450000
WQB 18MM/90 1METER	1	1044460000

Type	Qty.	Order No.
ESG 6/15 K MC WHITE	200	1880100000
SET 2 POLE WSI 25	10	1044440000
SET 3 POLE WSI 25	10	1044450000
WQB 18MM/90 1METER	1	1044460000

Dimensional drawing



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Weidmuller:](#)

[7940029426](#) [7940029428](#)