

**TERMSERIES**  
**TRS 12VDC 1COAU C1D2**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Product image**


Similar to illustration

TERMSERIES relay module, complete modules consisting of

a relay and a base with AC/DC/UC coils,  
 available in different versions:

- With screw and tension-clamp connection
- AgNi contact, optionally with hard gold-plated contacts
- 1 and 2 COs
- Optionally with multiple-voltage input: 24...230 V UC
- With various protective circuits  
 in the input (free-wheel diode, RC element)
- Illuminated ejection lever

**General ordering data**

|            |                                                                                                                                                         |
|------------|---------------------------------------------------------------------------------------------------------------------------------------------------------|
| Type       | TRS 12VDC 1COAU C1D2                                                                                                                                    |
| Order No.  | <a href="#">1984620000</a>                                                                                                                              |
| Version    | TERMSERIES, Relays, No. of contacts: 1 CO<br>contact AgNi 5µm Au, Rated control voltage: 12<br>V DC ±20 %, Continuous current: 6 A, Screw<br>connection |
| GTIN (EAN) | 4050118375701                                                                                                                                           |
| Qty.       | 10 pc(s).                                                                                                                                               |

**TERMSERIES**  
**TRS 12VDC 1COAU C1D2**
**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

**Technical data**
**Dimensions and weights**

|            |         |                 |            |
|------------|---------|-----------------|------------|
| Width      | 6.4 mm  | Width (inches)  | 0.252 inch |
| Height     | 89.6 mm | Height (inches) | 3.528 inch |
| Depth      | 87.8 mm | Depth (inches)  | 3.457 inch |
| Net weight | 33 g    |                 |            |

**Temperatures**

|                             |                                                                                |                             |                |
|-----------------------------|--------------------------------------------------------------------------------|-----------------------------|----------------|
| Humidity                    | 5-95% relative humidity,<br>$T_u = 40^\circ\text{C}$ , without<br>condensation | Operating temperature, max. | 60 °C          |
| Operating temperature, min. | -40 °C                                                                         | Storage temperature, max.   | 85 °C          |
| Storage temperature, min.   | -40 °C                                                                         | Operating temperature       | -40 °C...60 °C |
| Storage temperature         | -40 °C...85 °C                                                                 |                             |                |

**Environmental Product Compliance**

|            |                |
|------------|----------------|
| REACH SVHC | Lead 7439-92-1 |
|------------|----------------|

**Rated data UL**

|                                               |                                    |        |
|-----------------------------------------------|------------------------------------|--------|
| Ambient temperature (operational), max. 60 °C | Temperature class                  | T5     |
| Connection cross-section AWG, min. AWG 26     | Connection cross-section AWG, max. | AWG 14 |
| Type of conductor                             | Tightening torque, max.            | 0.4 Nm |
| Pollution severity level                      |                                    |        |
|                                               |                                    |        |

**Input**

|                                       |                                                     |                                                                                   |              |
|---------------------------------------|-----------------------------------------------------|-----------------------------------------------------------------------------------|--------------|
| Rated control voltage                 | 12 V DC $\pm$ 20 %                                  | Rated current DC                                                                  | 18 mA        |
| Power rating                          | 210 mW                                              | Pull-in/drop-out voltage, typ.                                                    | 9 V / 2 V DC |
| Pull-in/drop-out current, typ.        | 11.5 mA / 2 mA DC                                   | Status indicator                                                                  | Green LED    |
| Protective circuit                    | Free-wheeling diode,<br>Reverse polarity protection | Coil voltage of the replacement relay<br>deviating from the rated control voltage | No           |
| Coil voltage of the replacement relay | 12 V DC                                             |                                                                                   |              |

**Output**

|                                         |              |                                         |             |
|-----------------------------------------|--------------|-----------------------------------------|-------------|
| Rated switching voltage                 | 250 V AC     | Max. switching voltage, AC              | 250 V       |
| Max. switching voltage, DC              | 250 V        | Continuous current                      | 6 A         |
| Inrush current                          | 20 A / 20 ms | AC switching capacity (resistive), max. | 1500 VA     |
| DC switching capacity (resistive), max. | 144 W @ 24 V | Switch-on delay                         | $\leq$ 6 ms |
| Switch-off delay                        | $\leq$ 8 ms  | Min. switching power                    | 1 mA @ 1 V  |
| Max. switching frequency at rated load  | 0.1 Hz       |                                         |             |

**Contact data**

|              |                               |                         |                                      |
|--------------|-------------------------------|-------------------------|--------------------------------------|
| Contact type | 1 CO contact (AgNi 5µm<br>Au) | Mechanical service life | 5 x 10 <sup>6</sup> switching cycles |
|--------------|-------------------------------|-------------------------|--------------------------------------|

**General data**

|             |            |                                      |       |
|-------------|------------|--------------------------------------|-------|
| Version     | cULus C1D2 | Rail                                 | TS 35 |
| Test button | No         | Mechanical switch position indicator | No    |
| Colour      | black      | UL 94 flammability rating            | V-0   |

**TERMSERIES**  
**TRS 12VDC 1COAU C1D2**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Technical data**
**Insulation coordination**

|                                     |                              |                                                |                              |
|-------------------------------------|------------------------------|------------------------------------------------|------------------------------|
| Rated voltage                       | 300 V                        | Surge voltage category                         | III                          |
| Pollution severity                  | 2                            | Protection degree                              | IP20                         |
| Dielectric strength, Input/Output   | 4 kV <sub>eff</sub> / 1 Min. | Creepage and clearance distance input – output | ≥ 5.5 mm                     |
| Dielectric strength of open contact | 1 kV <sub>eff</sub> / 1 min  | Dielectric strength to mounting rail           | 4 kV <sub>eff</sub> / 1 Min. |
| Impulse withstand voltage           | 6 kV (1.2/50 µs)             |                                                |                              |

**Further details of approvals / standards**

|           |                                        |                           |         |
|-----------|----------------------------------------|---------------------------|---------|
| Standards | EN 50178, EN 55011, EN 61000-6-1, 2, 4 | Certificate no. (cULusEX) | E324123 |
|-----------|----------------------------------------|---------------------------|---------|

**Connection data**

|                                                                                         |                      |                                                                                         |                     |
|-----------------------------------------------------------------------------------------|----------------------|-----------------------------------------------------------------------------------------|---------------------|
| Wire connection method                                                                  | Screw connection     | Stripping length, rated connection                                                      | 8 mm                |
| Tightening torque, max.                                                                 | 0.4 Nm               | Clamping range, rated connection                                                        | 1.5 mm <sup>2</sup> |
| Clamping range, min.                                                                    | 0.14 mm <sup>2</sup> | Clamping range, max.                                                                    | 2.5 mm <sup>2</sup> |
| Wire connection cross section AWG, min.                                                 | AWG 26               | Wire connection cross section AWG, max.                                                 | AWG 14              |
| Wire cross-section, solid, min.                                                         | 0.14 mm <sup>2</sup> | Wire cross-section, solid, max.                                                         | 2.5 mm <sup>2</sup> |
| Wire connection cross-section, finely stranded, min.                                    | 0.14 mm <sup>2</sup> | Wire connection cross section, finely stranded, max.                                    | 2.5 mm <sup>2</sup> |
| Wire cross-section, finely stranded, min. (AWG)                                         | AWG 26               | Wire cross-section, finely stranded, max. (AWG)                                         | AWG 14              |
| Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/4, min. | 0.25 mm <sup>2</sup> | Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/4, max. | 2.5 mm <sup>2</sup> |
| Conductor cross-section, flexible, AEH (DIN 46228-1), min.                              | 0.25 mm <sup>2</sup> | Conductor cross-section, flexible, AEH (DIN 46228-1), max.                              | 2.5 mm <sup>2</sup> |
| Wire connection cross section, finely stranded, two clampable wires, min.               | 0.5 mm <sup>2</sup>  | Wire cross-section, finely stranded, two clampable wires, max.                          | 1 mm <sup>2</sup>   |
| Twin wire-end ferrules, min.                                                            | 0.5 mm <sup>2</sup>  | Twin wire-end ferrules, max.                                                            | 1 mm <sup>2</sup>   |
| Blade size                                                                              | size PHO             | Gauge to IEC 60947-1                                                                    | A1, B1              |

**Classifications**

|            |             |            |             |
|------------|-------------|------------|-------------|
| ETIM 5.0   | EC001437    | ETIM 6.0   | EC001437    |
| eClass 6.2 | 27-37-16-01 | eClass 7.1 | 27-37-16-01 |
| eClass 8.1 | 27-37-16-01 | eClass 9.0 | 27-37-16-01 |
| eClass 9.1 | 27-37-16-01 |            |             |

**Approvals**

Approvals



ROHS

Conform

## TERMSERIES TRS 12VDC 1COAU C1D2

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

### Downloads


|                                             |                                          |
|---------------------------------------------|------------------------------------------|
| Approval/Certificate/Document of Conformity | <a href="#">DE_PA5600_160229_001.pdf</a> |
| Brochure/Catalogue                          | <a href="#">CAT 4.2 ELECTR 18/19 EN</a>  |
| Engineering Data                            | <a href="#">EPLAN, WSCAD, Zuken E3.S</a> |
| Engineering Data                            | <a href="#">STEP</a>                     |
| User Documentation                          | <a href="#">Operating Instructions</a>   |

**TERMSERIES**  
**TRS 12VDC 1COAU C1D2**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
[www.weidmueller.com](http://www.weidmueller.com)


## Drawings

## Wiring diagram



## Graph


### DC load breaking capacity



DC load limit curve


## Graph

**Electrical endurance**  
230 V AC resistive load



Electrical service life230 V AC resistive load  
230 V AC resistive load

## Dimensional drawing



## TERMSERIES TRS 12VDC 1COAU C1D2

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmüller.com

## Drawings

## Miscellaneous



Type codes

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Weidmuller:](#)

[1984620000](#)