PRODUCT DATASHEET REV 1



BB630

630 tie-point Solderless Plug-in BreadBoard



AVAILABLE STYLES:


WHITE

PART#:

BB630

BB630 Features:


- 630 tie-point IC-circuit area.
- · White ABS plastic body with black printed legend.
- Contacts are Phosphor Bronze with Plated Nickel Finish, rated for 50,000 insertions.
- Rated at 36 Volts, 2 Amps.
- Insertion Wire Size is 21 to 26 AWG, 0.016 to 0.028 inches diameter (0.4 to 0.7mm diameter).
- Peelable adhesive tape backing provided for attaching to a surface.







BB630 Details:

BB630 is a solderless plug-in breadboard with 630 connection tie-points (i.e. wire insertion holes). Solderless breadboards are great for building and testing new circuits because parts can be easily inserted and removed. They are completely re-usable. The housing is made of white ABS plastic, with a printed legend giving numbers and letters for columns and rows. The internal contacts are phosphor bronze with a plated nickel finish. A peelable adhesive tape backing is provided for attaching it to a surface. BPS BreadBoards are Lead-Free and RoHS Compliant. Finished projects can be moved to a BR1 or SB830 Solderable PC BreadBoard to make them permanent.





Related Products:



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

BusBoard Prototype Systems:

BB630