



BB830™

830 tie-point Solderless Plug-In
BreadBoard with power rails



AVAILABLE SKUs:

WHITE

PART#:
BB830

150 BULK PART#:
BB830x150

200 BULK PART#:
BB830x200

TRANSPARENT


PART#:
BB830T

150 BULK PART#:
BB830Tx150

200 BULK PART#:
BB830Tx200

BB830 Features:



- 830 tie points total: 630 tie-point IC-circuit area plus two 100 tie-point distribution strips providing 4 power rails.
- ABS plastic body with black printed legend. Color legend on distribution strips.
- Contacts are Phosphor Bronze with Plated Nickel Finish, rated for 50,000 insertions.
- Rated at 36 Volts, 2 Amps.
- Insertion Wire Size is 21 to 26 AWG, 0.016 to 0.028 inches diameter (0.4 to 0.7mm diameter).
- Peelable adhesive tape backing provided for attaching to a surface. Metal back plate provided.




BB830 Details:

BreadBoard-830 is a solderless (plug-in) breadboard with 830 connection tie-points (i.e. 830 wire insertion holes). It has 4 power rails. Solderless breadboards are great for building and testing new circuits because parts can be easily inserted and removed. They are completely re-usable. The BB830 has a 630 tie-point IC-circuit area plus four 50 tie-point power rails.


The housing is made of white ABS plastic, with a printed legend giving numbers and letters for columns and rows. The internal contacts are phosphor bronze with a plated nickel finish. A peelable adhesive tape backing is provided for attaching it to a surface and an optional metal back plate is provided. BPS BreadBoards are Lead-Free and RoHS Compliant. Finished projects can be moved to a BR1 or SB830 Solderable PC BreadBoard to make them permanent.



Related Products:



SB830



BB400



BB1460



ZW-MM-10

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[BusBoard Prototype Systems:](#)

[BB830](#) [BB830T](#) [BB830M](#)