

ams Mira220

Datasheet

Published by ams-OSRAM AG

Tobelbader Strasse 30, 8141 Premstaetten, Austria

Phone +43 3136 500-0

ams-osram.com

© All rights reserved

ams **OSRAM**

Table of contents

- 1 General description 3
 - 1.1 Key benefits & features..... 3
 - 1.2 Applications 4
 - 1.3 Block diagram 5
- 2 Ordering information 6
- 3 Typical operating characteristics 7
 - 3.1 Electro-optical characteristics 7
 - 3.2 Functional characteristics 7
- 4 Revision information 9
- 5 Legal information 10

Mira220 1/2.7” 2.2MP NIR enhanced global shutter image

1 General description

Mira220 is a 2.2 MP NIR enhanced global shutter image sensor with a small 2.79 µm pixel size. It has excellent low light sensitivity made possible by a state-of-the-art stacked BSI technology. With an effective resolution of 1600 × 1400 and a maximum bit depth of 12 bits, the sensor supports on-chip operations like external triggering, windowing, horizontal or vertical mirroring. The maximum frame rate is 90 fps at full resolution and bit depth. The sensor has a MIPI CSI-2 interface to allow easy interfacing with a plethora of processors and FPGAs. On-chip registers can be accessed via the standard I²C interface for easy configuration of the sensor.

Due to its small size, configurability and high sensitivity both in visual as well as NIR, the Mira220 is well suited for 2D and 3D applications, which include Active Stereo Vision, Structured Light Vision for Robotics and AR/VR. High sensitivity in NIR enables increased measurement range and allows overall system power consumption optimization which is key for battery powered consumer and industrial applications.

1.1 Key benefits & features

Table 1: Added value of using Mira220

Benefits	Features
Compact size with high resolution and bit depth	<ul style="list-style-type: none">• 1/2.7”• 1600 x 1400• 8/10/12-bit• 2.79 µm
High speed applications	90 fps global shutter with CDS.
Use in low light conditions	High sensitivity
Compact size	Small die size achieved via state-of-the-art stacked BSI technology.
NIR enhanced with high sensitivity	Class leading QE at 940 nm combined with high sensitivity. Industry leading PLS at 940 nm.
On-chip noise reduction	Digital CDS and row noise correction


Benefits	Features
Reduced off-chip processing	<ul style="list-style-type: none">On-chip defect pixel detection and correctionOn-chip image statistics generation
Multiple variants	Available as Mono, RGB or RGBIR variant. Orderable with AR coated or plain glass and protective film
Extended battery operation	Low power consumption

1.2 Applications

- Mobile facial authentication
- Active stereo vision
- Smart home appliances
- QR readers
- Automatic identification and data capture (AIDC)
- AR/VR
- Structured light vision
- Drones
- Smart wearable devices
- SLAM for robotics

1.3 Block diagram

Figure 1: Functional blocks of Mira220



2 Ordering information

Product code	Ordering code	Type	Package	Glass	Protective film	Delivery form	MOQ
Mira220-2QM1WP	509780018 Q65114A0086	Mono	CSP	Plain	Yes	Tape and Reel	Multiples of 2000
Mira220-2QM1WA	509780022 Q65114A0087	Mono	CSP	AR	Yes	Tape and Reel	Multiples of 2000
Mira220-2QM1WO	509780037 Q65113A5069	Mono	CSP	Plain	No	Tape and Reel	Multiples of 2000
Mira220-2QC1WP	509780027 Q65113A5403	RGB	CSP	Plain	Yes	Tape and Reel	Multiples of 2000
Mira220-2QC1WA	509780029 Q65113A5404	RGB	CSP	AR	Yes	Tape and Reel	Multiples of 2000
Mira220-2QC1WO	509780038 Q65113A5405	RGB	CSP	Plain	No	Tape and Reel	Multiples of 2000
Mira220-2QI1WP	509780034 Q65113A5408	RGBIR	CSP	Plain	Yes	Tape and Reel	Multiples of 2000
Mira220-2QI1WA	509780036 Q65113A5409	RGBIR	CSP	AR	Yes	Tape and Reel	Multiples of 2000
Mira220-2QI1WO	509780039 Q65113A5410	RGBIR	CSP	Plain	No	Tape and Reel	Multiples of 2000
Mira220-2QM1D0	509780015 Q65114A0085	Mono	RW	-	-	Reconstructed Wafer	Contact Sales
Mira220-2QC1D0	509780024 Q65113A5399	RGB	RW	-	-	Reconstructed Wafer	Contact Sales
Mira220-2QI1D0	509780031 Q65113A5406	RGBIR	RW	-	-	Reconstructed Wafer	Contact Sales
Mira220-2QM1WP	509780042 Q65113A5999	Mono	CSP	Plain	Yes	Tape and Reel	Multiples of 500
Mira220-2QM1WA	509780043 Q65113A6000	Mono	CSP	AR	Yes	Tape and Reel	Multiples of 500
Mira220-2QC1WP	509780044 Q65113A5997	RGB	CSP	Plain	Yes	Tape and Reel	Multiples of 500
Mira220-2QC1WA	509780045 Q65113A5998	RGB	CSP	AR	Yes	Tape and Reel	Multiples of 500
Mira220-2QI1WP	509780046 Q65113A5995	RGBIR	CSP	Plain	Yes	Tape and Reel	Multiples of 500
Mira220-2QI1WA	509780047 Q65113A5996	RGBIR	CSP	AR	Yes	Tape and Reel	Multiples of 500
Mira220-2QM1WP	509780018 Q65114A0086	Mono	CSP	Plain	Yes	Tape and Reel	Multiples of 2000

3 Typical operating characteristics

3.1 Electro-optical characteristics

Below are the typical electro-optical specifications of Mira220.

Table 2: Optical features of Mira220

Parameter	Value	Remark
Active pixels	1600 (H) × 1400 (V)	
Pixel pitch	2.79 × 2.79 μm ²	
Optical format	1/2.7"	
Pixel type	BSI global shutter	With fixed pattern noise correction and reset (kTC) noise canceling by correlated double sampling (CDS) coupled with high sensitivity.
Shutter type	Pipelined global shutter	Exposure of next image during readout of the previous image.

Table 3: Typical electro-optical characteristics

Parameter	Value	Remark
Supported Lens Chief Ray Angles (CRA)	0° to 30°	Extra wide acceptance angle of the Mira220 pixel means any lens profile with these CRA values would provide decent performance.
Quantum Efficiency (QE)	94 / 55 / 36 %	550 / 850 / 940 nm

3.2 Functional characteristics

Table 4: Functional characteristics

Parameter	Value
Bit depth	12-bit
	10-bit
	8-bit
Timing generation	On-chip

Parameter	Value
Programmable registers	Sensor parameters. E.g. Window coordinates, Timing parameters, and Exposure time.
Power consumption	168 mW Active 30fps 40 mW Idle 4 mW Sleep
Data interface standard	MIPI CSI-2 DPHY
MIPI outputs	2 Data 1 Clock
Output interface bit rate	1.5 Gbit/s
Frame rates	90 fps
Black sun protection	Yes
Temperature sensor	Yes
Context switching	Two register contexts

4 Revision information

Document status	Product status	Definition
Product Preview	Pre-development	Information in this datasheet is based on product ideas in the planning phase of development. All specifications are design goals without any warranty and are subject to change without notice
Preliminary Datasheet	Pre-production	Information in this datasheet is based on products in the design, validation or qualification phase of development. The performance and parameters shown in this document are preliminary without any warranty and are subject to change without notice
Datasheet	Production	Information in this datasheet is based on products in ramp-up to full production or full production which conform to specifications in accordance with the terms of ams-OSRAM AG standard warranty as given in the General Terms of Trade

Other definitions

Draft / Preliminary:
The draft / preliminary status of a document indicates that the content is still under internal review and subject to change without notice. ams-OSRAM AG does not give any warranties as to the accuracy or completeness of information included in a draft / preliminary version of a document and shall have no liability for the consequences of use of such information.

Short datasheet:
A short datasheet is intended for quick reference only, it is an extract from a full datasheet with the same product number(s) and title. For detailed and full information always see the relevant full datasheet. In case of any inconsistency or conflict with the short datasheet, the full datasheet shall prevail.

Changes from previous released version to current revision v4-00	Page
Document contents transferred to latest ams OSRAM design	
Updated Ordering information	6

- Page and figure numbers for the previous version may differ from page and figure numbers in the current revision.
- Correction of typographical errors is not explicitly mentioned.

5 Legal information

Copyright & disclaimer

Copyright ams-OSRAM AG, Tobelbader Strasse 30, 8141 Premstaetten, Austria-Europe. Trademarks Registered. All rights reserved. The material herein may not be reproduced, adapted, merged, translated, stored, or used without the prior written consent of the copyright owner.

Devices sold by ams-OSRAM AG are covered by the warranty and patent indemnification provisions appearing in its General Terms of Trade. ams-OSRAM AG makes no warranty, express, statutory, implied, or by description regarding the information set forth herein. ams-OSRAM AG reserves the right to change specifications and prices at any time and without notice. Therefore, prior to designing this product into a system, it is necessary to check with ams-OSRAM AG for current information. This product is intended for use in commercial applications. Applications requiring extended temperature range, unusual environmental requirements, or high reliability applications, such as military, medical life-support or life-sustaining equipment are specifically not recommended without additional processing by ams-OSRAM AG for each application. This product is provided by ams-OSRAM AG "AS IS" and any express or implied warranties, including, but not limited to the implied warranties of merchantability and fitness for a particular purpose are disclaimed.

ams-OSRAM AG shall not be liable to recipient or any third party for any damages, including but not limited to personal injury, property damage, loss of profits, loss of use, interruption of business or indirect, special, incidental or consequential damages, of any kind, in connection with or arising out of the furnishing, performance or use of the technical data herein. No obligation or liability to recipient or any third party shall arise or flow out of ams-OSRAM AG rendering of technical or other services.

Product and functional safety devices/applications or medical devices/applications:

ams-OSRAM AG components are not developed, constructed or tested for the application as safety relevant component or for the application in medical devices. ams-OSRAM AG products are not qualified at module and system level for such application.

In case buyer – or customer supplied by buyer – considers using ams-OSRAM AG components in product safety devices/applications or medical devices/applications, buyer and/or customer has to inform the local sales partner of ams-OSRAM AG immediately and ams-OSRAM AG and buyer and/or customer will analyze and coordinate the customer-specific request between ams-OSRAM AG and buyer and/or customer.

ams OSRAM semiconductor RoHS compliance statement

RoHS compliant: The term RoHS compliant means that ams-OSRAM AG semiconductor products fully comply with current RoHS directives. Our semiconductor products do not contain any chemicals for all 6 substance categories plus additional 4 substance categories (per amendment EU 2015/863), including the requirement that lead not exceed 0.1% by weight in homogeneous materials.

Important information: The information provided in this statement represents ams-OSRAM AG knowledge and belief as of the date that it is provided. ams-OSRAM AG bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. ams-OSRAM AG has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. ams-OSRAM AG and ams-OSRAM AG suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

Headquarters

ams-OSRAM AG
Tobelbader Strasse 30
8141 Premstaetten
Austria, Europe
Tel: +43 (0) 3136 500 0

Please visit our website at ams-osram.com
For information about our products go to [Products](#)
For technical support use our [Technical Support Form](#)
For feedback about this document use [Document Feedback](#)
For sales offices and branches go to [Sales Offices / Branches](#)
For distributors and sales representatives go to [Channel Partners](#)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[ams OSRAM:](#)

[Mira220 2QMD0RW FT SE](#) [Mira220-2QC1WA FT SE](#) [Mira220-2QC1WO FT SE](#) [Mira220-2QC1WP FT SE](#) [Mira220-2QI1D0 RW](#) [Mira220-2QI1WA FT SE](#) [Mira220-2QI1WO FT SE](#) [Mira220-2QI1WP FT SE](#) [Mira220-2QC1D0 RW](#)
[Mira220-2QM1WA FT SE](#) [Mira220-2QM1WO FT SE](#) [Mira220-2QM1WP FT SE](#)