



CMV12000


12MP high speed global shutter image sensor

SENSOR DESCRIPTION

The CMV12000 is a global shutter CMOS image sensor with 4096 by 3072 pixels in a APS-C optical format supporting super HD imaging (4k). The image array consists of 5.5 μm by 5.5 μm pipelined global shutter pixels, which allow exposure during read out while performing CDS operation reducing fixed pattern and dark noise significantly. The CMV12000 has 64 12-bit digital LVDS outputs (serial) each running at 600 Mbps. The image sensor also integrates a programmable gain amplifier and offset regulation. Each channel runs at 600 Mbps maximum, which results in 300 fps frame rate at full resolution in 10-bit mode. Higher frame rates can be achieved in row-windowing mode or row-subsampling mode. All operation modes are all programmable using a SPI interface. A programmable on-board sequencer generates all internal exposure and read out timings. External triggering and exposure programming is also possible. Extended optical dynamic range can be achieved by multiple integrated high dynamic range modes. A 12-bit per pixel mode is available at reduced frame rates.

APPLICATION FIELDS

- Machine vision
- Motion control
- Traffic monitoring
- High speed inspection
- Broadcast



SENSOR FEATURES

- Pipelined global shutter with CDS
- 4096 (H) * 3072 (V) active pixels on a 5.5 μm pitch
- 300 frames/s at full resolution in 10 bit mode
- 140 frames/s at full resolution in 12 bit mode
- ROI windowing capability
(up to 32 separate ROIs - row based only)
- X-Y mirroring function
- 64 LVDS-outputs @ 600 Mbps multiplexable to 32, 16, 8, 4 and 2 at reduced frame rate
- Multiple High Dynamic Range modes supported up to 90 dB
- On chip temperature sensor
- On chip timing generation
- SPI-control
- On chip pixel averaging
(increased frame rate and dynamic range)
- 3.3 V signaling
- Monochrome and Bayer (RGB) configuration
- Ceramic 237-pins μPGA package (47 mm x 33.8 mm)
- 2 sided AR-coated cover glass lid

Please address all product inquiries and ordering information to:

CMOSIS · Coveliersstraat 15 · B-2600 Antwerpen · Phone: +32 3 260 17 33 · Fax: +32 3 260 17 79 · info@cmosis.com




CMV12000

12MP high speed global shutter image sensor

SENSOR SPECIFICATIONS

Specification	Value
Resolution	12MP - 4096 (H) x 3072 (V)
Pixel size	5.5 x 5.5 μm^2
Optical Format	APS-like
Shutter Type	Pipelined global shutter with true CDS
Frame Rate	300 fps (10 bit) 140 fps (12 bit)
Output Interface	64 LVDS @ 600 Mbps
Sensitivity	4.17 V/lux.s
Conversion gain	0.075 LSB/e
Full well charge	13500 e-
Dark noise	13 e- (RMS)
Dynamic range	60 dB
SNR max	41,3 dB
Parasitic light sensitivity	1/50000
Extended dynamic range	Yes, up to 90 dB
Dark current	125 e-/s (25 degC)
Fixed pattern noise	< 1 LSB (<0.1 % of full swing)
Chroma	Mono and RGB
Supply voltage	1,8 V / 3,3 V
Power	3000 mW
Operating temperature range	-30 to +70 degC (TBC)
RoHS compliance	Yes (TBC)
Package	237 pins μPGA



ORDERING INFORMATION

CMV12000	Description
CMV12000ES-2E5M1PA	Monochrome version
CMV12000ES-2E5M1PN	Monochrome version with removeable glass lid
CMV12000ES-2E12M1PA	Monochrome version NIR enhanced
CMV12000ES-2E5C1PA	RGB Bayer Color version

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

CMOSIS:

[CMV12000-2E5M1PA](#) [CMV12000-2E5M1PN](#) [CMV12000-2E12M1PA](#) [CMV12000-2E12M1PN](#) [CMV12000-2E5C1PA](#)
[CMV12000-2E5C1PN](#)