

BGA Heat Sink - High Performance maxiFLOW/maxiGRIP-Low Profile



| | |
|-------------------------|--|
| ATS Part#: | ATS-51375D-C1-R0 |
| Description: | 37.50 x 37.50 x 9.50 mm BGA Heat Sink - High Performance maxiFLOW/maxiGRIP-Low Profile |
| Heat Sink Type: | maxiFLOW |
| Heat Sink Attachment: | maxiGRIP |
| Equivalent Part Number: | ATS-51375D-C2-R0 Discontinued |

**Image above is for illustration purpose only.*

Features & Benefits

- **maxiFLOW™** design features a low profile, spread fin array that maximizes surface area for more effective convection (air) cooling
- **maxiGRIP™** attachment applies steady, even pressure to the component and does not require holes in the PCB
- Meets Telcordia GR-63-Core Office Vibration; ETSI 300 019 Transportation Vibration; and MIL-STD-810 Shock and Unpackaged Drop Testing standards
- Comes preassembled with high performance, phase changing, thermal interface material
- Designed for low profile components from 1.5 to 2.99mm

Thermal Performance

| AIR VELOCITY | | @200 LFM 1.0 M/S | @300 LFM 1.5 M/S | @400 LFM 2.0 M/S | @500 LFM 2.5 M/S | @600 LFM 3.0 M/S | @700 LFM 3.5 M/S | @800 LFM 4.0 M/S |
|--------------------|---------------|---------------------|---------------------|---------------------|---------------------|---------------------|---------------------|---------------------|
| THERMAL RESISTANCE | Unducted Flow | 4.9 °C/W | 3.6 °C/W | 3.1 °C/W | 2.7 °C/W | 2.5 °C/W | 2.3 °C/W | 2.1 °C/W |
| | Ducted Flow | 3 | N/A | N/A | N/A | N/A | N/A | N/A |

Product Detail

| Schematic Image | Dimension A | Dimension B | Dimension C | Dimension D | TIM | Finish |
|--|-------------|-------------|-------------|-------------|------|-----------------|
| <p><i>*Image above is for illustration purpose only.</i></p> | 37.50 mm | 37.50 mm | 9.50 mm | 51.4 mm | T766 | BLACK- ANODIZED |
| Notes: <ul style="list-style-type: none"> • Dimension A and B refer to component size. • Dimension C is the heat sink height from the bottom of the base to the top of the fin field. • ATS-51375D-C2-R0 is the exact heat sink assembly with an equivalent thermal interface material (Saint Gobain C1100F). NOTE: Saint Gobain C1100F is discontinued effective 12/31/10. • Thermal performance data are provided for reference only. Actual performance may vary by application. • ATS reserves the right to update or change its products without notice to improve the design or performance. • ATS certifies that this heat sink assembly is RoHS-6 and REACH compliant. • Optional maxiGRIP™ Installation/Removal Tool Set P/N: MGT375 • Contact ATS to learn about custom options available. | | | | | | |

For more information, to find a distributor or to place an order, please contact us at 781-769-2800 (North America), sales@qats.com or www.qats.com.

© 2013 Advanced Thermal Solutions, Inc. | 89-27 Access Road | Norwood MA | 02062 | USA



Rev - 011217

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Advanced Thermal Solutions:](#)

[ATS-51375D-C1-R0](#)