




# Shielded Power Inductors – XAL8080



- High current – up to 38 A
- Very low DCR – as low as 1.38 mOhms
- AEC-200 qualified
- Soft saturation

**Core material** Composite

**Environmental** RoHS compliant, halogen free

**Terminations** RoHS compliant tin-silver over copper. Other terminations available at additional cost.

**Weight** 3 g

**Operating voltage:** 0 – 60 V

**Ambient temperature** –40°C to +125°C with Irms current

**Maximum part temperature** +165°C (ambient + temp rise). [Derating](#).

**Storage temperature** Component: –55°C to +165°C.

Tape and reel packaging: –55°C to +80°C

**Resistance to soldering heat** Max three 40 second reflows at +260°C, parts cooled to room temperature between cycles

**Moisture Sensitivity Level (MSL)** 1 (unlimited floor life at <30°C / 85% relative humidity)

**Packaging** 450/13" reel Plastic tape: 24 mm wide, 0.4 mm thick, 16 mm pocket spacing, 8.36 mm pocket depth

**PCB washing** Tested to MIL-STD-202 Method 215 plus an additional aqueous wash. See [Doc787\\_PCB\\_Washing.pdf](#).

| Part number <sup>1</sup> | Inductance <sup>2</sup><br>±20% (µH) | DCR (mOhms) <sup>3</sup> |      | SRF typ <sup>4</sup><br>(MHz) | Isat <sup>5</sup><br>(A) | Irms (A) <sup>6</sup> |           |
|--------------------------|--------------------------------------|--------------------------|------|-------------------------------|--------------------------|-----------------------|-----------|
|                          |                                      | typ                      | max  |                               |                          | 20°C rise             | 40°C rise |
| XAL8080-681ME_           | 0.68                                 | 1.38                     | 1.65 | 70.0                          | 43.0                     | 27.0                  | 37.0      |
| XAL8080-841ME_           | 0.84                                 | 1.60                     | 1.90 | 55.2                          | 41.0                     | 25.5                  | 35.0      |
| XAL8080-102ME_           | 1.0                                  | 2.11                     | 2.33 | 49.2                          | 31.3                     | 24.9                  | 34.1      |
| XAL8080-222ME_           | 2.2                                  | 4.08                     | 4.49 | 36.7                          | 24.0                     | 16.0                  | 21.5      |
| XAL8080-472ME_           | 4.7                                  | 8.89                     | 9.77 | 24.1                          | 17.4                     | 10.5                  | 14.6      |
| XAL8080-682ME_           | 6.8                                  | 13.2                     | 14.5 | 20.6                          | 14.0                     | 8.0                   | 11.3      |
| XAL8080-103ME_           | 10                                   | 21.0                     | 23.1 | 15.6                          | 10.9                     | 6.6                   | 8.7       |
| XAL8080-123ME_           | 12                                   | 16.4                     | 18.2 | 11.3                          | 8.6                      | 7.6                   | 10.5      |
| XAL8080-153ME_           | 15                                   | 20.3                     | 22.5 | 10.5                          | 7.7                      | 6.9                   | 9.4       |
| XAL8080-183ME_           | 18                                   | 25.2                     | 28.0 | 9.1                           | 6.6                      | 6.0                   | 8.3       |
| XAL8080-223ME_           | 22                                   | 29.6                     | 32.9 | 8.2                           | 6.4                      | 5.6                   | 7.6       |
| XAL8080-333ME_           | 33                                   | 43.7                     | 48.5 | 6.8                           | 5.0                      | 4.4                   | 6.0       |
| XAL8080-473ME_           | 47                                   | 64.7                     | 71.8 | 5.9                           | 4.4                      | 3.5                   | 4.8       |

## Irms Testing

Irms testing was performed on 0.75 inch wide × 0.25 inch thick copper traces in still air.

Temperature rise is highly dependent on many factors including pcb land pattern, trace size, and proximity to other components. Therefore temperature rise should be verified in application conditions.

1. When ordering, please specify **packaging** code:

**XAL8080-473MED**

**Packaging: D** = 13" machine-ready reel. EIA-481 embossed plastic tape. (450 parts per full reel). Quantities less than full reel available: in tape (not machine ready) or with leader and trailer (\$25 charge).

**B** = Less than full reel. In an effort to simplify our part numbering system, Coilcraft is eliminating the need for multiple packaging codes. When ordering, simply change the last letter of your part number from B to D.

2. Inductance tested at 1 MHz, 0.1 Vrms, 0 Adc.

3. DCR measured on a micro-ohmmeter.

4. SRF measured using Agilent/HP 4395A or equivalent.

5. DC current at 25°C that causes a 30% (typ) inductance drop from its value without current.

[Click for temperature derating information.](#)

6. Current that causes the specified temperature rise from 25°C ambient. This information is for reference only and does not represent absolute maximum ratings. [Click for temperature derating information.](#)

7. Electrical specifications at 25°C.

Refer to Doc 362 "Soldering Surface Mount Components" before soldering.



www.coilcraft.com

**US** +1-847-639-6400 sales@coilcraft.com

**UK** +44-1236-730595 sales@coilcraft-europe.com

**Taiwan** +886-2-2264 3646 sales@coilcraft.com.tw

**China** +86-21-6218 8074 sales@coilcraft.com.cn

**Singapore** + 65-6484 8412 sales@coilcraft.com.sg

Document 839-1 Revised 08/13/25











© Coilcraft Inc. 2025

This product may not be used in medical or high risk applications without prior Coilcraft approval. Specification subject to change without notice. Please check web site for latest information.



# Shielded Power Inductors – XAL8080




## L vs Current








# Shielded Power Inductors – XAL8080

## L vs Current



## L vs Frequency



\* For optional tin-lead and tin-silver-copper terminations, dimensions are for the mounted part. Dimensions before mounting can be an additional 0.005 inch / 0.13

**Recommended Land Pattern**

Dimensions are in  $\frac{\text{inches}}{\text{mm}}$

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Coilcraft:

|                                       |                                       |                                       |                                       |                                       |                                       |
|---------------------------------------|---------------------------------------|---------------------------------------|---------------------------------------|---------------------------------------|---------------------------------------|
| <a href="#"><u>XAL8080-102MED</u></a> | <a href="#"><u>XAL8080-103MEB</u></a> | <a href="#"><u>XAL8080-222MEB</u></a> | <a href="#"><u>XAL8080-222MED</u></a> | <a href="#"><u>XAL8080-682MED</u></a> | <a href="#"><u>XAL8080-682MEB</u></a> |
| <a href="#"><u>XAL8080-472MED</u></a> | <a href="#"><u>XAL8080-102MEB</u></a> | <a href="#"><u>XAL8080-472MEB</u></a> | <a href="#"><u>XAL8080-103MED</u></a> | <a href="#"><u>XAL8080-681MEB</u></a> | <a href="#"><u>XAL8080-681MED</u></a> |
| <a href="#"><u>XAL8080-822MED</u></a> | <a href="#"><u>XAL8080-822MEB</u></a> | <a href="#"><u>XAL8080-223MED</u></a> | <a href="#"><u>XAL8080-473MED</u></a> |                                       |                                       |