




No-Opto Flyback Transformers



- Three output versions optimized for Texas Instruments LM5180 and LM5180-Q1 Flyback Converter, Analog Device LT830x Flyback Converter and similar ICs
- Designed to operate up to 350 kHz with 4.5 – 70 V input
- 1500 Vrms, one minute isolation between primary and secondary

Core material Ferrite

Terminations RoHS tin-silver-copper over tin over nickel over phos bronze. Other terminations available at additional cost.

Weight 2.05 – 2.15 g

Ambient temperature –40°C to +85°C

Max Part Temperature +125°C (ambient + temperature rise)

Storage temperature Component: –40°C to +125°C

Tape and reel packaging: –40°C to +80°C

Resistance to soldering heat Max three 40 second reflows at +260°C, parts cooled to room temperature between cycles

Moisture Sensitivity Level (MSL) 1 (unlimited floor life at <30°C / 85% relative humidity)

Failures in Time (FIT) / Mean Time Between Failures (MTBF)

38 per billion hours / 26,315,789 hours, calculated per Telcordia SR-332

Packaging 300/13" reel Plastic tape: 32 mm wide, 0.42 mm thick, 20 mm pocket spacing, 10.69 mm pocket depth

PCB washing Tested to MIL-STD-202 Method 215 plus an additional aqueous wash. See [Doc787_PCB_Washing.pdf](#).

Part number ¹	Inductance at 0 A ² ±10% (μH)	Inductance at 2 A ³ (μH)	DCR max (Ohms) ⁴			Leakage inductance max (μH) ⁵	Turns ratio		Power (W)	Output
			pri	sec1	sec2		pri : sec1	pri : sec2		
YA8779-BLD	30	24	0.140	0.013	—	0.380	1 : 0.330	—	6	5 V, 1.20 A
YA8916-BLD	30	27	0.360	0.695	0.392	0.565	1 : 1	1 : 0.52	4.60	15 V, 0.20 A (sec1) 8 V, 0.20 A (sec2)
YA8864-BLD	30	27	0.180	0.680	0.180	0.295	1 : 1.5	1 : 0.40	3.50	20 V, 0.10 A (sec1) 5 V, 0.30 A (sec2)

1. **Packaging:** D = 13" machine-ready reel. EIA-481 embossed plastic tape. Quantities less than full reel available: in tape (not machine ready) or with leader and trailer (\$25 charge).

2. Inductance is for the primary, measured at 300 kHz, 0.1 Vrms, 0 Adc.

3. Minimum inductance for the primary, measured at 300 kHz, 0.1 Vrms, 2 Adc.

4. Sec1 DCR for YA8779 is with windings connected in parallel.

5. Leakage Inductance is for the primary, measured with secondary windings shorted together.


6. Electrical specifications at 25°C.

Refer to Doc 362 "Soldering Surface Mount Components" before soldering.




No-opto Flyback Transformers – YA8779, YA8916, YA8864

YA8779, YA8916, YA8864




Schematics


YA8779*



YA8916



YA8864



*Connect pin 5 to 6 and pin 7 to 8 on the PC board

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Coilcraft:](#)

[YA8779-BL](#)