



AG6020 SERIES



External Dimensions



Frame:Plastic(UL:94V-0)
Impeller:Plastic(UL:94V-0)
Lead wire:UL1007AWG26

Specifications(Nominal)


*:Noise is measured at the distance of one (1) meter from the axis of intake.

Bearing type: ◎=Ball ※=Sleeve ●=Hypro bearing

Frame size (mm)	Model No.	Bearing System Type	Rated Voltage (VDC)	Current (A)	Power (W)	Rated Speed (rpm)	Maximum AirFlow		Maximum Pressure		*Noise Level (dB/A)	Weight (g)
60x60x20	AG06012DB207300	◎ ●	12	0.16	1.92	4000	0.558	19.728	0.164	4.165	35.1	56.0
	AG06012LB207300	◎ ●	12	0.18	2.16	4500	0.606	21.419	0.203	5.156	36.6	
	AG06012MB207300	◎ ●	12	0.20	2.40	5000	0.707	25.000	0.260	6.604	39.0	
	AG06012HB207300	◎ ●	12	0.23	2.76	5500	0.825	29.140	0.323	8.210	42.1	
	AG06012UB207300	◎ ●	12	0.28	3.36	6000	0.863	30.500	0.370	9.418	43.5	
	AG06024DB207300	◎ ●	24	0.10	2.40	4000	0.558	19.728	0.164	4.165	35.1	
	AG06024LB207300	◎ ●	24	0.12	2.88	4500	0.606	21.419	0.203	5.156	36.6	
	AG06024MB207300	◎ ●	24	0.14	3.36	5000	0.707	25.000	0.260	6.604	39.0	
	AG06024HB207300	◎ ●	24	0.16	3.84	5500	0.825	29.140	0.323	8.210	42.1	
	AG06024UB207300	◎ ●	24	0.19	4.56	6000	0.863	30.500	0.370	9.418	43.5	
	AG06012DX207600	◎ ●	12	0.16	1.92	4000	0.558	19.728	0.164	4.165	35.1	
	AG06012LX207600	◎ ●	12	0.18	2.16	4500	0.606	21.419	0.203	5.156	36.6	
	AG06012MX207600	◎ ●	12	0.22	2.64	5000	0.707	25.000	0.260	6.604	39.0	
	AG06012HX207600	◎ ●	12	0.26	3.12	5500	0.825	29.140	0.323	8.210	42.1	
	AG06012UX207600	◎ ●	12	0.32	3.84	6000	0.863	30.500	0.370	9.418	43.5	

Specifications subject to change without notice.

The specification for bearing type is for reference only , for more bearing types information, please contact with your ADDA sales representative, thanks!!
(網頁上呈現產品軸承資訊均以2Ball為主，若需其他產品資訊請聯絡您在ADDA的業務代表，謝謝！！)



*Motor protective circuit and third lead wire functions

0	1	2	3	4	6	7	8	9	A	B
✓	✓		✓		✓					

*Safety approvals

UL	UL	SP	CE	CE
✓	✓		✓	✓

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[ADDA:](#)

[AG06012HB207300](#) [AG06012HB207100](#) [AG06012HX207100](#) [AG06012HX207300](#) [AG06012MX207100](#)
[AG06012LX207100](#)