

ZP 4/1AN/7**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Product image

The plugs for our WeiCoS-System are available for all different connection systems. The product range includes preassembled connectors from 1 to 10 poles and the possibility of an individual assembly. This ensures maximum flexibility for every application. The customized accessories increase the safety and protection against environmental influences.

General ordering data

| | |
|------------|---|
| Version | Z-series, Plug-in connector, beige, Direct mounting |
| Order No. | 1855040000 |
| Type | ZP 4/1AN/7 |
| GTIN (EAN) | 4032248396115 |
| Qty. | 20 pc(s). |

ZP 4/1AN/7

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

| | | | |
|------------|---------|-----------------|------------|
| Depth | 47.5 mm | Depth (inches) | 1.87 inch |
| Height | 22.5 mm | Height (inches) | 0.886 inch |
| Width | 45.5 mm | Width (inches) | 1.791 inch |
| Net weight | 43.05 g | | |

Temperatures

| | | | |
|----------------------------------|----------------|----------------------------------|-----|
| Storage temperature | -25 °C...55 °C | Continuous operating temp., min. | -50 |
| Continuous operating temp., max. | 120 | | |

Material data

| | | | |
|---------------------------|-------|--------|------------|
| Material | Wemid | Colour | dark beige |
| UL 94 flammability rating | V-0 | | |

System specifications

| | | | |
|-----------------------------------|--|-------------------------------------|----|
| Version | Set of connectors, pluggable, Tension-clamp connection | End cover plate required | No |
| Number of levels | 1 | Number of clamping points per level | 1 |
| Levels cross-connected internally | No | PE connection | No |

Additional technical data

| | | | |
|---------------------|-----------------|------------|--------|
| Installation advice | Direct mounting | Open sides | closed |
| Type of mounting | Plugged | | |

CSA rating data

| | | | |
|-------------------------------|----------------|-------------------------------|--------|
| Certificate No. (CSA) | 200039-1720292 | Current size C (CSA) | 28 A |
| Voltage size C (CSA) | 600 V | Wire cross section max. (CSA) | 10 AWG |
| Wire cross section min. (CSA) | 26 AWG | | |

Conductors for clamping (rated connection)

| | | | |
|---------------------------------------|--|---------|----------------------|
| Blade size | 0.6 x 3.5 mm | | |
| Clamping range, max. | 6 mm ² | | |
| Clamping range, min. | 0.13 mm ² | | |
| Connection direction | top | | |
| Gauge to IEC 60947-1 | A3 | | |
| Number of connections | 7 | | |
| Stripping length | 12 mm | | |
| Tube length for twin wire-end ferrule | Cross-section for conductor connection | nominal | 0.5 mm ² |
| | | min. | 8 mm |
| | | max. | 12 mm |
| | Cross-section for conductor connection | nominal | 0.75 mm ² |
| | | min. | 8 mm |
| | | max. | 12 mm |

ZP 4/1AN/7

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

| | | | | |
|---|--|--------------------------|----------------------|--|
| Tube length for wire-end ferrule with plastic collar DIN 46228/4 | Cross-section for conductor connection | nominal | 0.5 mm ² | |
| | | min. | 8 mm | |
| | | max. | 10 mm | |
| | Cross-section for conductor connection | nominal | 0.75 mm ² | |
| | | min. | 6 mm | |
| | | max. | 12 mm | |
| | Cross-section for conductor connection | nominal | 1 mm ² | |
| | | min. | 6 mm | |
| | | max. | 12 mm | |
| | Cross-section for conductor connection | nominal | 1.5 mm ² | |
| | | min. | 8 mm | |
| | | max. | 12 mm | |
| | Cross-section for conductor connection | nominal | 2.5 mm ² | |
| | | min. | 8 mm | |
| | | max. | 12 mm | |
| | Cross-section for conductor connection | nominal | 4 mm ² | |
| | | min. | 10 mm | |
| | | max. | 12 mm | |
| Tube length for wire-end ferrule without plastic collar DIN 46228/1 | Cross-section for conductor connection | nominal | 0.5 mm ² | |
| | | nominal | 10 mm | |
| | Cross-section for conductor connection | nominal | 0.75 mm ² | |
| | | nominal | 10 mm | |
| | Cross-section for conductor connection | nominal | 1 mm ² | |
| | | nominal | 10 mm | |
| | Cross-section for conductor connection | nominal | 1.5 mm ² | |
| | | min. | 10 mm | |
| | | max. | 12 mm | |
| | Cross-section for conductor connection | nominal | 2.5 mm ² | |
| | | min. | 10 mm | |
| | | max. | 12 mm | |
| | Cross-section for conductor connection | nominal | 4 mm ² | |
| | | nominal | 12 mm | |
| | Type of connection | Tension-clamp connection | | |
| | Wire connection cross section AWG, max. | AWG 10 | | |
| | Wire connection cross section AWG, min. | AWG 26 | | |
| | Wire connection cross section, finely stranded, max. | 6 mm ² | | |
| Wire connection cross section, finely stranded, min. | 0.5 mm ² | | | |
| Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, max. | 4 mm ² | | | |
| Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, min. | 0.5 mm ² | | | |
| Wire connection cross-section, solid core, max. | 6 mm ² | | | |
| Wire connection cross-section, solid core, min. | 0.5 mm ² | | | |

General

| | | | |
|---|----------------------------------|---|--------|
| Installation advice | Direct mounting | Number of poles | 7 |
| Standards | In accordance with IEC 60947-7-1 | Wire connection cross section AWG, max. | AWG 10 |
| Wire connection cross section AWG, min. | AWG 26 | | |

Creation date September 16, 2022 7:18:02 PM CEST

ZP 4/1AN/7

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Rating data

| | | | |
|---------------------------------|----------------------------------|--|--------|
| Rated cross-section | 4 mm ² | Rated voltage | 800 V |
| Rated current | 32 A | Current at maximum wires | 32 A |
| Standards | In accordance with IEC 60947-7-1 | Volume resistance according to IEC 60947-7-x | 1 mΩ |
| Rated impulse withstand voltage | 8 kV | Power loss in accordance with IEC 60947-7-x | 1.02 W |
| Pollution severity | 3 | | |

UL rating data

| | | | |
|--|--------|--|--------|
| Certificate No. (cURus) | E60693 | Conductor size Factory wiring max. (cURus) | 10 AWG |
| Conductor size Factory wiring min. (cURus) | 26 AWG | Conductor size Field wiring max. (cURus) | 10 AWG |
| Conductor size Field wiring min. (cURus) | 26 AWG | Current size C (cURus) | 28 A |
| Voltage size C (cURus) | 600 V | | |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC002848 | ETIM 7.0 | EC002848 |
| ETIM 8.0 | EC002848 | ECLASS 9.0 | 27-14-11-92 |
| ECLASS 9.1 | 27-14-11-92 | ECLASS 10.0 | 27-14-11-92 |
| ECLASS 11.0 | 27-14-11-92 | ECLASS 12.0 | 27-14-11-92 |

Approvals

Approvals



| | |
|-------------------------|------------|
| ROHS | Conform |
| UL File Number Search | UL Website |
| Certificate No. (cURus) | E60693 |

Downloads

| | |
|---|---|
| Approval/Certificate/Document of Conformity | EAC certificate |
| Engineering Data | CAD data – STEP |
| Engineering Data | EPLAN, WSCAD |
| User Documentation | StorageConditionsTerminalBlocks |
| Catalogues | Catalogues in PDF-format |
| Brochures | |

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Weidmuller:](#)

[1855040000](#)