


ZMSM Series with Mounting Hole Subminiature Snap-acting Switches (IP65)

Features/Benefits

- Reliable snap-acting mechanism
- Long electrical and mechanical life
- Various PCB terminals and actuators
- RoHS compatible
- IP67 with potted wires only

Typical Applications

- Communication devices
- Testing equipment
- Security/Alarm systems



UL61058-1



Specifications

CONTACT RATING: 3A@ 125 V AC/ 3A@ 12 V DC, 0.01 A@ 12 V DC.
ELECTRICAL LIFE: 100,000 cycles @ 0.01 A, 12 V DC / 100,000 cycles @ 3A, 12 V DC, 6,000 cycles @ 3A, 125 VAC
INSULATION RESISTANCE: 100 M ohm min.
DIELECTRIC STRENGTH: 500 Vrms.
OPERATING TEMPERATURE: see chart below.
OPERATING FORCE: 130 grams.

* Low Level=conditions where no arcing occurs during switching, i.e., 0.4 VA max.
@ 20 V AC or DC max.

Materials

CASE: Nylon
COVER/ACTUATOR: PBT
MOVABLE CONTACTS: 3 Amp silver, 0.01A gold
STATIONARY CONTACTS: 3 Amp silver, 0.01A gold
TERMINALS: Brass, Pre-plated with silver
LEVER: Stainless steel

NOTE: Specifications and materials listed above are for switches with standard options.
For information on specific and custom switches, consult Customer Service Center.

Build-A-Switch

To order, simply select desired option from each category and place in the appropriate box. Available options are shown and described on pages J-62 through J-64. For additional options not shown in catalog, consult Customer Service Center.

Z M S M																			
Series ZMSM SP, Mom.																			
Over Travel H High Travel L Low Travel																			
		Electrical Rating 0 0.01 A @ 12 V DC 3 3A 125 V AC 3A 12 V DC																	
				Operating Force 130 130 grams / 4.59															
						Actuator P00 Pin plunger T10 .25 lever T11 .28 simulated roller													
								Terminations P PC Thru-hole S Solder type J Wire leads 20 AWG UL 1007 K Wire leads 22 AWG UL1430 W Wire leads 24 AWG UL1061 N Wire leads 26 AWG UL1330											
																Circuitry C SPDT W SPST N.C. Y SPST N.O.			
														Mounting Styles M No support post L Two support post left R Two support post right T One support post left and right					






Snap-acting

ZMSM Series with Mounting Hole Subminiature Snap-acting Switches (IP65)



SERIES

ZMSMH HIGH OVER TRAVEL



ZMSML LOW OVER TRAVEL

MODEL SHOWN: ZMSMHXXXP00PLC



MODEL SHOWN: ZMSMLXXXP00PLC

Snap-acting

ELECTRICAL RATING

OPTION CODE	RoHS COMPLIANT*	RoHS COMPATIBLE*	CONTACT MATERIAL		ELECTRICAL RATING
			MOVABLE CONTACT	STATIONARY CONTACT	
0	Yes	Yes	Gold alloy		0.01 A @ 12 V DC
3	Yes	Yes	Silver alloy		3 AMPS @ 125 V AC 3 AMPS @ 12 V DC

Model **C&K** US with option “S” (solder type) only.
Consult Customer Service center for availability and delivery of nonstandard ratings.

OPERATING FORCE


OPTION CODE	BASIC SWITCH OPERATING FORCE (OZ./GRAMS)
130	130 4.59



ZMSM Series with Mounting Hole Subminiature Snap-acting Switches (IP65)


ACTUATOR

P00 PIN PLUNGER (IP65)




MODEL SHOWN: ZMSMLXXXXP00PLC

T10 .25 LEVER (IP65)



MODEL SHOWN: ZMSMLXXXXT10PLC

T11 LEVER (IP65)




MODEL SHOWN: ZMSMLXXXXT11PLC

SWITCH CHARACTERISTICS


Actuator code	Maximum Operate Force (grams/oz.)	Minimum Release Force (grams/oz.)	Free Position Max (mm)	Maximum Pre-travel (mm)	Operate Position (mm)	Maximum Differential (mm)	Low Overtravel min. (mm)	High Overtravel min. (mm)
P00	130 4.59	13 0.45	7.35	0.8	6.75 ± 0.3	0.3	0.8	1.75
T10	195 6.88	55 1.93	10.70	3.85	7.40 ± 0.8	0.5	1.35	2.3
T11	160 5.64	45 1.58	13.80	4.8	9.90 ± 0.8	0.7	1.65	2.6

TERMINATIONS

P PC THRU-HOLE (IP65)




MODEL SHOWN: ZMSMHXXXXP00PLC




PC MOUNTING HOLE

S SOLDER TYPE (IP65)



MODEL SHOWN: ZMSMHXXXXP00SMC

J, K, W, N WIRE LEADS BOTTOM (IP67)



Standard Wire: 20 AWG UL 1007


Available options - must specify

J - 20AWG UL1007 (Standard)

K - 22AWG UL1430

W - 24AWG UL1061

N - 26AWG UL1330



Dimensions are shown: mm

Specifications and dimensions subject to change




2 May 2018

ZMSM Series with Mounting Hole Subminiature Snap-acting Switches (IP65)



MOUNTING STYLES

M NO SUPPORT POSTS





MODEL SHOWN:
ZMSMHXXXP00PMC

L TWO SUPPORT POSTS LEFT





POSTS LEFT
MODEL SHOWN:
ZMSMHXXXP00PLC

R TWO SUPPORT POSTS RIGHT



POSTS RIGHT
MODEL SHOWN:
ZMSMHXXXP00PRC

T ONE SUPPORT POST
LEFT & RIGHT



LEFT & RIGHT
MODEL SHOWN:
ZMSMHXXXP00PTC

Snap-acting

CIRCUITRY

C SPDT (Single Pole, Double Throw)

W SPST, NC (Single Pole, Single Throw, Normally Closed)

Y SPST, NO (Single Pole, Single Throw, Normally Open)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

C&K Switches:

[ZSMH3130P00SRC](#) [ZSMH0130T10JTY](#) [ZSMH3130T10KTY](#) [ZSMH3130P00JMC](#) [ZSMH0130T11KMY](#)
[ZSMH0130T11JTY](#) [ZSMH3130P00SLC](#) [ZSMH0130P00JLC](#) [ZSMH0130P00JMY](#) [ZSMH0130P00SMY](#)
[ZSMH0130P00KMY](#) [ZSMH0130P00JMC](#)