


# LC Series

## Small Size Precision Snap-acting Switches



### Features/Benefits

- Compact design
- Long life and high electrical capacity
- Quick connect, wire lead or PC mounting
- Wide variety of actuator styles

### Typical Applications

- Motorized equipment
- Sump pump
- Thermostatic controls

UL61058-1



### Specifications

CONTACT RATING: From low level\* to 10.1 AMPS @ 250 V AC.

ELECTRICAL LIFE: 100,000 cycles

INSULATION RESISTANCE: 1,000 M ohm min.

DIELECTRIC STRENGTH: 1,000 Vrms min. @ sea level.

OPERATING TEMPERATURE: -17°F to 185°F (-25°C to 85°C).

OPERATING FORCE: From 142 to 170 grams at actuator button.

Forces are less at free end of lever actuators; (see OPERATING FORCE and ACTUATOR option sections).

MOUNTING: 2-56 screws, torque 2.3 in/lbs max.

\* Low Level=conditions where no arcing occurs during switching, i.e., 0.4 VA max. @ 20 V AC or DC max.

**NOTE:** Specifications and materials listed above are for switches with standard options. For information on specific and custom switches, consult Customer Service center.

### Materials

SWITCH HOUSING: Thermoplastic polyester or high temperature thermoplastic (PTS) (UL 94V-0).

ACTUATOR BUTTON: Thermoplastic polyester (UL 94V-0).

SPRING: Copper alloy.

PIVOT: Copper alloy.

MOVABLE CONTACTS: Fine silver for ratings greater than 1 AMP @ 125 V AC. Fine silver with 24K gold plate for 1 AMP @ 125 V AC or less.

STATIONARY CONTACTS: Fine silver welded on copper alloy for ratings greater than 1 AMP @ 125 V AC. Gold alloy welded on copper alloy for ratings less than 1 AMP @ 125 V AC.

TERMINALS: Copper alloy.

TERMINAL SEAL: Epoxy.

### Build-A-Switch

To order, simply select desired option from each category and place in the appropriate box. For additional options not shown in catalog, consult Customer Service Center.

<div style="border: 1px solid black; padding: 2px; display: inline-block;">L C</div> <div style="border: 1px solid black; width: 20px; height: 15px; display: inline-block;"></div> <div style="border: 1px solid black; width: 20px; height: 15px; display: inline-block;"></div> <div style="border: 1px solid black; width: 20px; height: 15px; display: inline-block;"></div> <div style="border: 1px solid black; width: 20px; height: 15px; display: inline-block;"></div> <div style="border: 1px solid black; width: 20px; height: 15px; display: inline-block;"></div> <div style="border: 1px solid black; width: 20px; height: 15px; display: inline-block;"></div> <div style="border: 1px solid black; width: 20px; height: 15px; display: inline-block;"></div> <div style="border: 1px solid black; width: 20px; height: 15px; display: inline-block;"></div>			
<p><b>Series</b></p> <p><b>LC</b> SP, Mom.</p> <p><b>Operating Force</b></p> <p><b>GG</b> 5 oz./142 grams</p> <p><b>GD</b> 3.3 oz./94 grams</p> <p><b>GH</b> 6 oz./170 grams</p> <p><b>Electrical Rating</b></p> <p><b>X1</b> UL 61058-1 (see chart)</p> <p><b>V6</b> UL 61058-1 (see chart)</p> <p><b>V7</b> UL 61058-1 (see chart)</p> <p><b>F5</b> UL 1054 (see chart)</p> <p><b>L9</b> UL 1054 (see chart)</p> <p><b>M1</b> UL 1054 (see chart)</p>	<p><b>Actuator</b></p> <p><b>P00</b> Pin plunger</p> <p><b>A10</b> .28" lever roller, high force</p> <p><b>A15</b> .51" lever roller, high force</p> <p><b>A20</b> .39" lever roller, low force</p> <p><b>A25</b> .61" lever roller, low force</p> <p><b>T10</b> .29" lever, high force</p> <p><b>T13</b> .22" simulated roller, high force</p> <p><b>T15</b> .57" lever, high force</p> <p><b>T20</b> .38" lever, low force</p> <p><b>T23</b> .32" simulated roller, low force</p> <p><b>T25</b> .67" lever, low force</p>	<p><b>Terminations</b></p> <p><b>E</b> Solder</p> <p><b>H</b> .110" quick connect</p> <p><b>J</b> Wire lead</p> <p><b>L</b> Left formed PC thru-hole</p> <p><b>R</b> Right formed PC thru-hole</p> <p><b>S</b> PC Thru-hole</p> <p><b>Circuitry</b></p> <p><b>C</b> SPDT</p> <p><b>W</b> SPST N.C.</p> <p><b>Y</b> SPST N.O.</p>	<p><b>Electrical Life</b></p> <p><b>NONE</b> 6,000 operations</p> <p><b>U*</b> Extended 100,000 operations</p>

\* Extended operations only available on Electrical Rating options F5, L9 and M1

**Seal**

**NONE (STD.)** No seal

**E** Epoxy seal





Dimensions are shown: Inch (mm)  
Specifications and dimensions subject to change

# LC Series Small Size Precision Snap-acting Switches

## SERIES

**LC** SMALL SIZE PRECISION SNAP-ACTING SWITCHES  
SP MOMENTARY



## OPERATING FORCE

OPTION CODE	BASIC SWITCH OPERATING FORCES (OZ./GRAMS)
<b>GG</b>	5 142
<b>GD</b>	3.3 94
<b>GH</b>	6 170

**NOTE:** Operating force varies with actuator option, see ACTUATOR option section.

## ELECTRICAL RATING

UL 61058-1		CONTACT MATERIAL		RoHS COMPLIANT*	RoHS COMPATIBLE*
OPTION CODE	ELECTRICAL RATING	MOVABLE CONTACT	STATIONARY CONTACT		
<b>X1</b>	1A GP, 250 Vac, 50/60 Hz, 25E3, T85 1RA, 30 Vdc, 1E4, T85	Fine silver with 24K gold plate	Fine silver with 24K gold plate on copper base alloy	Yes	Yes
<b>V6</b>	5(2)A RM, 250 Vac, 50/60 Hz, 1E4, T85 5A GP, 250 Vac, 50/60 Hz, 1E4, T85 5RA, 30 Vdc, 1E4, T85 1/3 HP, 125/250 Vac, 50/60 Hz, 1E4, T85	Fine silver	Fine silver welded on copper base alloy	Yes	Yes
<b>V7</b>	10(2)A RM, 250 Vac, 50/60 Hz, 1E4, T85 10A GP, 250 Vac, 50/60 Hz, 1E4, T85 10RA, 30 Vdc, 1E4, T85 1/3 HP, 125/250 Vac, 50/60 Hz, 1E4, T85	Fine silver	Fine silver welded on copper base alloy	Yes	Yes

UL 1054		CONTACT MATERIAL		RoHS COMPLIANT*	RoHS COMPATIBLE*
OPTION CODE	ELECTRICAL RATING	MOVABLE CONTACT	STATIONARY CONTACT		
<b>F5</b>	1A, 125 V AC, 30 VDC 100,000 cycles ("U" option)	Fine silver with 24K gold plate	Fine silver with 24K gold plate on copper base alloy	Yes	Yes
<b>L9</b>	5A, 1/3 HP @ 125 and 250 V AC 100,000 cycles ("U" option)	Fine silver	Fine silver welded on copper base alloy	Yes	Yes
<b>M1</b>	10.1A, 1/3 HP @ 125 and 250 V AC 100,000 cycles ("U" option)	Fine silver	Fine silver welded on copper base alloy	Yes	Yes



\* Note: See Technical Data section of this catalog for RoHS compliant and compatible definition and specifications.

Consult Customer Service Center for availability and delivery of nonstandard ratings.

\*Low Level = conditions where no arcing occurs during switching, i.e., 0.4 VA max. @ 20 V AC or DC max.



Dimensions are shown: Inches (mm)

Specifications and dimensions subject to change




# LC Series

## Small Size Precision Snap-acting Switches

### ACTUATOR

OPTION CODE	FIG.	DIM. A	DIM. B	DIM. C
P00	1	0.297 (7,6)	.330 ± .015 (8,38 ± 0,38)	—
A10	7	0.28 (7,1)	.570 ± .070 (14,48 ± 1,78)	.19 dia. (4,80)
A25	2	0.61 (15,5)	.570 ± .175 (14,22 ± 4,45)	.19 dia. (4,80)
T10	3	0.29 (7,4)	.340 ± .070 (8,64 ± 1,78)	—
T13	5	0.220 (5,3)	.455 ± .065 (11,56 ± 1,65)	—
T20	4	0.39 (9,9)	.340 ± .140 (8,64 ± 3,56)	—
T23	6	0.32 (8,1)	.455 ± .125 (11,56 ± 3,18)	—
T25	4	0.67 (17,0)	.340 ± .091 (8,64 ± 4,70)	—
A15	7	0.51 (13,0)	.560 ± .090 (14,22 ± 2,29)	.19 dia. (4,80)
A20	2	0.38 (9,7)	.560 ± .135 (14,22 ± 2,29)	.19 dia. (4,80)
T15	3	0.57 (14,51)	.340 ± .100 (8,64 ± 2,54)	—



### SWITCH CHARACTERISTICS

OPTION CODE	MAXIMUM OPERATING FORCE (OZ./GRAMS)			MINIMUM RELEASE FORCE (OZ./GRAMS)			MAXIMUM DIFFERENTIAL TRAVEL	MAXIMUM PRETRAVEL	MINIMUM OVERTRAVEL
	GG	GD	GH	GG	GD	GH	ALL FORCES	ALL FORCES	ALL FORCES
A10	1.69 48	1 28	2.0 57	.21 6	.11 3	.42 12	.034 (0,86)	.140 (3,56)	.029 (0,74)
A15	1.3 37	.68 19	1.6 44	.16 4.5	.07 2	.32 9	.044 (1,12)	.180 (4,57)	.037 (0,94)
A20	0.9 26	.52 15	1.1 31	.11 3	.05 15	.21 6	.067 (1,70)	.272 (6,91)	.053 (1,53)
A25	.70 20	.42 12	.85 24	.07 2	.04 1	.16 4.5	.086 (2,18)	.351 (8,92)	.068 (1,73)
P00	5 142	3.3 95	6 170	1 28	.05 14	2.0 57	.004 (0,10)	.030 (0,76)	.010 (0,25)
T10	1.7 48	1 28	2.1 60	.21 6	.10 3	.39 11	.035 (0,90)	.140 (3,56)	.029 (0,74)
T13	1.8 52	1.2 34	2.2 62	.21 6	.03 1	.42 12	.032 (0,81)	.130 (3,30)	.026 (0,66)
T20	0.9 26	.52 15	1.1 30	.10 3	.03 1	.21 6	.067 (1,70)	.276 (7,01)	.053 (1,35)
T23	1.0 28	.52 15	1.2 34	.10 3	.03 1	.21 6	.062 (1,57)	.252 (6,40)	.049 (1,24)
T25	0.7 19	.05 14	0.8 24	.07 2	.03 1	.14 4	.090 (2,29)	.372 (9,45)	.072 (1,83)
T15	1.2 35	1.3 39	1.5 42	0.14 4	.21 6	.28 81	.047 (1,19)	.190 (4,83)	.040 (1,02)

NOTE: For basic switch operating forces, see page J-32.



Dimensions are shown: Inch (mm)


Specifications and dimensions subject to change




# LC Series Small Size Precision Snap-acting Switches

## TERMINATIONS

### E SOLDER




### H .110" QUICK CONNECT



**NOTE:** Use Amp Quick Connect Part No. 640932-1.

### J WIRE LEAD




RATING	WIRE SIZE
1 AMP	22 AWG
5 AMPS	20 AWG
10.1 AMPS	18 AWG


  

TERMINAL	WIRE COLOR
COMMON	BLACK
NORMALLY OPEN	WHITE
NORMALLY CLOSED	RED


### L LEFT FORMED PC THRU-HOLE




#### PC MOUNTING




### R RIGHT FORMED PC THRU-HOLE




#### PC MOUNTING



### S PC THRU-HOLE



#### PC MOUNTING



## CIRCUITRY

### C SPDT (Single Pole, Double Throw)

### W SPST N.C. (Single Pole, Single Throw, Normally Closed)

### Y SPST N.O. (Single Pole, Single Throw, Normally Open)

## ELECTRICAL LIFE


### NONE 6,000 OPERATIONS

### U EXTENDED 100,000 OPERATIONS

## SEAL

### NONE NO SEAL

### E EPOXY SEAL



Third Angle Projection

Dimensions are shown: mm  
Specifications and dimensions subject to change

**C&K**

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

## C&K Switches:

[LCGGX1A10EC](#) [LCGHF5A10RC](#) [LCGHF5A10LC](#) [LCGDL9T10EC](#) [LCGGX1P00EC](#) [LCGGX1T25EC](#)  
[LCGHF5T10SY](#) [LCGGL9P00EC](#) [LCGHF5A10ECE](#) [LCGGL9P00SCE](#) [LCGGX1T20EY](#) [LCGHF5A10LCE](#)  
[LCGGF5T23SC](#) [LCGGF5A10ECU](#) [LCGGV6P00SCUE](#) [LCGGF5A25ECU](#) [LCGGL9P00EYE](#) [LCGDF5P00HCU](#)  
[LCGGM1T20EYE](#) [LCGGF5T23ECU](#) [LCGGF5T20JC](#) [LCGGL9T10SCE](#) [LCGGF5T13ECUE](#) [LCGGF5P00ECUE](#)  
[LCGDL9P00SCE](#) [LCS052P00WA24AC](#) [LCGDL9P00ECU](#)