

Mini Sample Kit

<u>SL03 10001</u> Max Dia = 3.0mm $\pm$ 10% R@25°C = 10Ω $\pm$ 25% SSI = 1.00 A Energy = 2.0 J	<u>SL03 20001</u> Max Dia = 3.0mm $\pm$ 10% R@25°C = 20.0Ω $\pm$ 25% SSI = 1.00 A Energy = 2.0 J	<u>SL03 50001</u> Max Dia = 3.0mm $\pm$ 10% R@25°C = 50.0Ω $\pm$ 25% SSI = 1.00 A Energy = 2.0 J	<u>SL05 10001</u> Max Dia = 5.0mm $\pm$ 10 % R@25°C = 10Ω $\pm$ 25% SSI = 1.00 A Energy = 6.0 J
<u>SL05 12101</u> Max Dia = 5.5 mm $\pm$ 10% R@25°C = 120Ω $\pm$ 25% SSI = 1.00 A Energy = 5.0J	<u>SL05 60001</u> Max Dia = 5.5 mm $\pm$ 10% R@25°C = 60.0Ω $\pm$ 25% SSI = 1.00 A Energy = 5.0 J	<u>SL08 10002</u> Max Dia = 8.0mm $\pm$ 10% R@25°C = 10Ω $\pm$ 25% SSI = 2.00 A Energy = 10 J	<u>SL08 12101</u> Max Dia = 8.0mm $\pm$ 10% R@25°C = 120Ω $\pm$ 25% SSI = 1.00 A Energy = 10 J

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Ametherm:](#)

[Mini sample kit](#)