

VG H M32 MS**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Similar to illustration**

In addition to the extensive range of enclosures, Weidmüller offers a variety of cable glands for a wide range of applications.

The cable glands made of brass, plastic and stainless steel meet the most various IP protection classes to suit any industrial enclosure.

Depending on the series of cable glands and the application, the cable glands are approved and tested according to VDE, UL, UR, cULus, DNV GL or EN 45545.

General ordering data

Version	VG H (HDC halved cable gland), Cable glands, M 32, IP65, Brass, nickel-plated
Order No.	1921760000
Type	VG H M32 MS
GTIN (EAN)	4032248563029
Qty.	20 pc(s).
Available until	2015-10-30

VG H M32 MS

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Net weight	27.15 g
------------	---------

Temperatures

Operating temperature	-20 °C...60 °C
-----------------------	----------------

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
------------	----------------

General information

AF size 1	32 mm	Cable glands	metric
External thread	M 32	Material	Brass, nickel-plated
Notch multi-layer sealing diameter 1	16 mm	Notch multi-layer sealing diameter 2	19 mm
Notch multi-layer sealing diameter 3	22 mm	Notch multi-layer sealing diameter 4	25 mm
O-Ring	NBR	Operating temperature range, max.	60 °C
Operating temperature range, min.	-20 °C	Pitch of thread	1.5 mm
Protection degree	IP65	Protection degree with GWDR	IP65

Classifications

ETIM 6.0	EC000441	ETIM 7.0	EC000441
ETIM 8.0	EC000441	ECLASS 9.0	27-14-44-32
ECLASS 9.1	27-14-44-32	ECLASS 10.0	27-14-44-32
ECLASS 11.0	27-14-44-32		

Approvals

Approvals



ROHS

Conform

Downloads

Engineering Data	EPLAN, WSCAD
Catalogues	Catalogues in PDF-format
Brochures	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Weidmuller:](#)

[1921760000](#)