




File: E209153



## Mechanical Specifications (mm)

D:	10.0	± max
T:	4.5	± max
Lead Diameter	0.5	± nom
S:	5.0	± nom
L:	38.0	± nom
Coating Lead Run Down (straight Leads)	3.0	± max
B:	5.00	± nom
C:	2.00	± nom



## Electrical Specifications

Resistance:	2.5	Ω	± 30 %
Max Steady State Current upto 65°C:	5.00	A	
Max Rec. Energy Rating:	30	J	
Maximum Capacitance @ 120 VAC:	2,000	µf	
Maximum Capacitance @ 240 VAC:	520	µf	
Resistance @ 100% Max Current:	0.00	Ω	
Resistance @ 50% Max Current:	0.22	Ω	
Body Temperature at 100% Max Current:	165.00	°C	
Dissipation Constant:	10.0	mw/°C	
Thermal Time Constant:	25	Sec.	
Material Type (for Beta and Curve):	A		

### SL10 2R505

Date: 11/11/2008	Drawn by: Erin Landis
Ametherm, Inc. 961 Fairview Drive Carson City, Nevada USA 89701 www.ametherm.com	Approved By: Mehdi Samii
	Revision: A

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Ametherm:](#)

[SL10 2R505](#)