




File: E209153



ISO9001:2008 Certified

Mechanical Specifications (mm)

D:	11.0	± Max
T:	6.0	± Max
Lead Diameter	0.5	± Nom
S:	5.1	± Nom
L:	38.0	± Nom
Coating Lead Run Down (straight Leads)	3.5	± Nom
B:	6.35	± Nom
C:	2.75	± Nom



Electrical Specifications

Resistance:	40.0 Ω	± 20 %
Max Steady State Current upto 65°C:	2.00	A
Max Rec. Energy Rating:	15	J
Actual Failure Instantaneous Energy:	40	J
Resistance @ 100% Max Current:	0.65	Ω
Resistance @ 50% Max Current:	1.55	Ω
Body Temperature at 100% Max Current:	142.00	°C
Dissipation Constant:	11.0	mw/°C
Thermal Time Constant:	25	Sec.
Material Type (for Beta and Curve):	H	

SL10 40002	
Date: 07/14/2014	Drawn by: Erin Landis
Ametherm, Inc. 3111 N. Deer Run Road Carson City, Nevada USA 89701 www.ametherm.com	Approved By: Mehdi Samii
	Revision: C

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Ametherm:](#)

[SL10 40002](#)