


Part Number: SL15 22101

Ordering Different Lead Types:

Inside Kinked Leads	Use -A after Ametherm's part #
Outside Kinked Leads	Use -B after Ametherm's part #

For example: to order an inside kinked lead use part number SL15 22101-A



Electrical Specifications:

Resistance @ 25°C	220.0 $\Omega \pm 25\%$
Max Steady State Current Up to 65°C	1.0 A
Max Recommended Energy Rating (Joules)	50.0 J
Resistance @ 100% of Max Current	1.900 Ω
Resistance @ 50% of Max Current	4.500 Ω
Body Temperature @ 100% Current Rating	179 °C
Dissipation Constant	15mW/°C
Thermal Time Constant	45 seconds
Material Type	"L"
Max Capacitance @ 120VAC/240VAC	3200 μ F/800 μ F

Mechanical Specifications:

D	15.0 ± 0.5 mm
T	5.0 ± 0.2 mm
Lead Diameter	0.8 ± 0.1 mm
S	7.8 ± 0.30 mm
L	38.0 ± 1.50 mm
Straight Leads	Standard
B	7.50 ± 0.70 mm
C	3.60 ± 0.40 mm
Coating Run Down on the Straight Leads	5.00 ± 0.5 mm

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Ametherm:](#)

[SL15 22101](#)