


SNAP-IN PANEL MOUNTING, ON-ON-ON MAINTAINED ACTION, 1 AND 2 POLES

The industry's smallest ON-ON-ON triple throw rocker switch is a sealed, logic level switch offering 1M cycle life in a short, snap-in package. Available in both single and double pole configurations, with maintained action, this ON-ON-ON rocker is perfect for use as a Forward-Neutral-Reverse (FNR) switch. The double pole version offers redundancy for each switch state providing increased safety. Termination options include a Molex connector or wire leads.

The K1S contact system is sealed to IP68S and uses a flow-thru design. With an optional boot, the switch is panel sealed to IP68S. The rugged K1S is shorter behind panel than OTTO's K1 rocker series, making it an ideal choice for use in grips and panels. The K1S also consists of two rocker button style/size options for best user comfort. Only one panel opening size is required, regardless of button size. Choose from a set of 73 standard legend choices which are offered with both normal and large-size rocker top styles, or add a custom logo, lettering or legend.

Features:

- **Shorter behind panel depth**
- **High cycle life, 1,000,000 cycles**
- **Maintained action**
- **Single or double pole, ON-ON-ON triple throw switch**
- **Switch contacts sealed to IP68S (panel sealed to IP68S with optional rubber boot for standard rocker only)**
- **Logic level only**
- **2 sizes of rocker styles, standard and large**
- **2 termination types, connector and wire leads**
- **Choose from 73 standard legends per SAE or create your own**
- **RoHS compliant**

**Standard Characteristics/Ratings:**

ELECTRICAL:

Electrical Ratings:	10mA @ 5VDC max. Logic Level
Electrical Life:	1,000,000 cycles
Max Power:	0.5 VA
Max Voltage:	32VDC
Min Voltage:	20mV
Max Current:	50mA
Min Current:	1mA
DWV:	250 Vrms

MECHANICAL:



Mechanical Life:	1,000,000 cycles
Switch Contact Seal:	IP68S (Panel Seal IP68S with Optional Boot)

ENVIRONMENTAL:

Temperature Range: -40°C to +85°C

MATERIALS:

Base:	Black Thermoplastic
Button:	Black Thermoplastic
Bezel:	Black Thermoplastic
Wire:	26 AWG UL 11028 Wire
Gasket:	EPDM



HIGH CYCLE LIFE, SEALED ROCKER SWITCHES

K1S
SNAP-IN
ROCKERS

SNAP-IN PANEL MOUNTING, ON-ON-ON MAINTAINED ACTION, 1 AND 2 POLES

K1S PART NUMBER CODE

Part Number Code Continues Below

K1S	X	X	X	XX	XX	XX
	Connection Style	Rocker Color/Style	Switch Action / Circuit	Legend Style	Legend Style	Legend Style
	A. 6 PIN Connector ^{①*} B. 8 PIN Connector ^{②**} E. 18" Wires [457] ^③	A. Red Rocker B. Black Rocker C. White Rocker D. Large Red Rocker ^④ E. Large Black Rocker ^④ F. Large White Rocker ^④ G. Yellow Rocker H. Large Yellow Rocker ^④ J. Large Black Rocker with Embossed FNR (White) ^④ K. Large Yellow Rocker with Embossed FNR (Black) ^④ L. Red Rocker with Black Boot M. Red Rocker with Translucent Boot N. Black Rocker with Black Boot P. Black Rocker with Translucent Boot R. White Rocker with Black Boot T. White Rocker with Translucent Boot U. Yellow Rocker with Black Boot V. Yellow Rocker with Translucent Boot	Position "A" Position "B" Position "C" Circuit H. ON ON ON SPTT** T. ON ON ON DPTT *	Position "A" ZZ. No Legend	Position "B" ZZ. No Legend	Position "C" ZZ. No Legend

NOTE: For all other Legend Options, refer to Standard Legend Table below. Find the two digit code and enter the code in the appropriate positions


GASKET PART NUMBER (INCLUDED)

C807039-25-1

PANEL THICKNESS AND MOUNTING OPENING GUIDELINES^③

PANEL THICKNESS: .086±.003 [2.18±0.08]
RECOMMENDED PANEL THICKNESS REQUIRES EITHER THE PANEL GASKET OR THE OPTIONAL RUBBER BOOT FOR PROPER FITMENT.

PANEL OPENING:



K1S PART NUMBER CODE - Continued From Above

XXX	X
Legend Color***	Legend Orientation
Position A / B / C 1. Red 2. Black 9. White Z. No Legend	POSITION "A" POSITION "C" 1. Std. < A B C 2. 90° < B C 3. 180° < V A C 4. 270° < A B C Z. NO ORIENTATION

① Mating Connector: MOLEX 51021-0600

② Mating Connector: MOLEX 51021-0800

③ Unless otherwise specified, all dimensions are in inch [metric]. In the event of a conflict, the inch nominal value and tolerance will take precedence.

④ Rubber boot not available

* 6 PIN Connector not available with DPTT Circuit

** 8 PIN Connector not available with SPTT Circuit

*** Legend color cannot be same color as button color (i.e. Red Button color cannot have Red Legend color)

OPTIONAL BOOT PART NUMBER

C405810-25-12 (Translucent)

C405810-25-2 (Black)

STANDARD LEGENDS PER SAE SPECIFICATIONS					
A1	ANCHOR	H2	HORN REAR	P4	BILGE PUMP
B1	BATTERY	K1	LOCK	P5	BILGE BLOWER
B2	ELECTRIC POWER	K2	UNLOCK	R1	LIFT
C1	AC/COOLING SYSTEMS	L1	LIGHT	R2	LOWER
C2	DEHUMIDIFIER	L2	MASTER LIGHTING SWITCH	R3	UP
C3	HEATER/INTERIOR HEATING	L3	HEADLIGHTS	R4	DOWN
D1	WINDSHIELD DEFROSTER	L4	HEADLIGHTS-LOW / DIPPED BEAM	R5	RIGHT
D2	REAR WINDOW DEFROSTER	L5	HEADLIGHTS-HIGH / UPPER BEAM	R6	LEFT
D3	MIRROR DEFROSTER	L6	PARKING LIGHT	R7	FWD FORWARD
E1	ENGINE/START	L7	WORK LAMP	R8	REV REVERSE
E2	ENGINE/STOP	L8	WORK LAMP	S1	RADIO
E3	ON/START	L9	INTERIOR DOME LIGHT	S2	MUTE
E4	OFF/STOP	M1	BEACON	T1	FAST
E5	ON	M2	HAZARD/POSITION LIGHTS	T2	SLOW
E6	OFF	M3	CLEARANCE LIGHTS	T3	TRIM TAB / TRIMMING OPERATION
E7	ENGINE ELECTRIC PREHEAT	M4	SIDE MARKER LIGHT	T4	TRANSMISSION
E8	ENGINE-GAS INJECTION	M5	RUNNING LIGHTS (UNDER POWER)	V1	VENTILATING / AC FAN
E9	POWER	M6	ANCHOR LIGHT	W1	WINDSHIELD WIPER
F1	FRONT FOG LIGHTS	M7	RUNNING/ANCHOR LIGHTS	W2	WINDSHIELD-WASHER
F2	REAR FOG LIGHTS	M8	SEARCH LIGHT	W3	WINDSHIELD-WASHER/WIPER
F3	FORWARD	M9	LEFT TURN SIGNAL	W4	REAR WINDOW WIPER
F4	NEUTRAL	MA	RIGHT TURN SIGNAL	W5	REAR WINDOW-WASHER
F5	REVERSE	P1	BILGE PUMP #1	W6	REAR WINDOW-WASHER/WIPER
G1	FUEL	P2	BILGE PUMP #2	ZZ	NO LEGEND
H1	HORN	P3	BILGE PUMP #3		

SNAP-IN PANEL MOUNTING, ON-ON-ON MAINTAINED ACTION, 1 AND 2 POLES

WIRED CIRCUIT DIAGRAM	<p>K1SE _ H _ _ _ _</p> <p>SPTT - ON-ON-ON WIRED SCHEMATIC</p>
	<p>K1SE _ T _ _ _ _</p> <p>DPTT - ON-ON-ON WIRED SCHEMATIC</p>
CONNECTOR CIRCUIT DIAGRAM	<p>K1SB _ H _ _ _ _</p> <p>SPTT - ON-ON-ON SCHEMATIC W/CONNECTOR PIN OUT</p>
	<p>K1SB _ T _ _ _ _</p> <p>DPTT - ON-ON-ON SCHEMATIC W/CONNECTOR PIN OUT</p>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

OTTO:

[K1SEBHF3F4F59994](#) [K1SEBHZZZZZZZZZZ](#) [K1SEBTF3F4F59994](#) [K1SEJTZZZZZZZZZZ](#) [K1SEKHZZZZZZZZZZ](#)
[K1SEKTZZZZZZZZZZ](#)