

EXAMPLES OF APPLICATION-SPECIFIC DESIGNS

Pendant Switch

Remote hand held pushbutton switch with coiled cord that extends to approximately 3'.

Circuit: SPNO-DB

Rating: 10 amps Resistive @ 28VDC

Button: Black nylon

Housing: Black nylon

Cord: Black polyurethane, 28 AWG

U2-098



Coiled Cord Switch

Remote hand held pushbutton switch with a 6' coiled cord. Sealed against dust and moisture.

Rating: 10 amps Resistive @ 28VDC

Button: Green nylon

Housing: Black anodized aluminum

Cord: 6' extended, 18 AWG

P3-80012



Grip Switch Assembly

Switch is built into a grip designed for rugged outdoor use. Automotive type connector.

Circuit: SPNC-DB

Rating: 10 amps Resistive @ 28VDC

Button: Red nylon

Housing: Black nylon

Cord: Black polyurethane, 18 AWG

Left and right hand operation with various connection types available.

U2-076



Pendant Switch

Remote hand held pushbutton switch with 24" coiled cord that extends to approximately 15'. Terminated with a 1/4" right angle molded phone plug (optional).

Circuit: SPNO-DB

Rating: 5 amps Resistive @ 28VDC

Button: Black nylon

Housing: Black nylon

Cord: Black polyurethane, 22 AWG

U2-034



Pendant Switch

Remote hand held pushbutton switch with 7.0" +/- 1.0" wire leads.

Circuit: SPST Alternate Action

Rating: 5 amps Resistive @ 28VDC

Button: Red nylon

Housing: Black nylon

Cord: Black polyurethane, 18 AWG

U2-150



Pendant Switch

Remote hand held pushbutton switch with coiled cord that extends to approximately 20'. Terminated with a connector.

Circuit: SPNO-DB

Rating: 5 amps Resistive @ 28VDC

Button: Red nylon

Housing: Black nylon

Cord: Black neoprene, 18 AWG

Connector: Deutsch

U2-096



Pendant Switch

Remote hand held P8 pushbutton switch with a 3' coiled cord. Switch is dusttight per MIL-PRF-8805, Design 2.

Rating: 10 amps Resistive @ 28VDC

Button: Red thermoplastic

Housing: Black anodized aluminum

Cord: Black polyurethane, 28 AWG

U2-331



For more options contact factory.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[OTTO:](#)

[U2-430](#)