

0.750" DIAMETER FLANGE MOUNT, SHORT TRAVEL

Conical Hat
Shown


Standard Characteristics/Ratings:

ELECTRICAL RATINGS:

Insulation Resistance:	100MΩ min @ 50VDC
Null Temp Coefficient:	+/- 0.04% of full scale per degree C max
Hysteresis:	+/- 0.5% of full scale within 1 second after release
Sensitivity Temp Coefficient:	+/- 0.2% full scale per degree C
Resolution:	Infinite
Seal:	Enclosure dusttight per MIL-PRF-8805 Design 2
Operating Force:	3.0 lbs.
Operating Temp Range:	-40°C to +71°C
Storage Temp Range:	-55°C to +85°C
Travel:	To mechanical stop 0.05 inches max

MATERIALS:

Button:	Thermoplastic or anodized aluminum
Terminals:	Tin plate over copper plate over brass
Wire:	MIL-W-16878/4, 12 inches min, 24 AWG
Hardware:	None provided



J2-S1 PART NUMBER CODE

J2-S1 X XX X X XX

Circuit Type

- A. Full Bridge
B. Half Bridge
C. Isolated

Electrical I/O
(See Table)

- B1.
B2.
B3.
B4.
B5.
B6.
B7.
G1.
G2.
G3.
G4.
G5.
G6.
G7.

Termination

1. Wire Leads
2. Terminals

Button Style

- A. Conical Hat
B. Flat Button

Color

- P1. Red Thermoplastic ①
P2. Black Thermoplastic ①
P8. Gray Thermoplastic ①
BA. Black Anodized Aluminum ②
CA. Clear Anodized Aluminum ②

- ① Conical hat only.
② Flat button only.

EXCITATION VOLTAGE TABLE

Circuit Configuration	Excitation Voltage (Units VDC)	Sensitivity Until Stop (Units VDC/lb. +/- 20%)	Max Output at Stop (Units VDC)	Null Output at 25°C Bipolar (Units VDC)	Null Output at 25°C Supply to Ground (Units VDC)	Full Scale Travel Cycles (Units x 10 ⁶)
B1	+/- 12.0	+/- 0.45	+/- 1.40	+/- 0.12		0.2
G1	+24.0	+/- 0.45	+/- 1.40		12.0 +/- 0.12	0.2
B2	+/- 10.0	+/- 0.45	+/- 1.40	+/- 0.12		0.2
G2	+20.0	+/- 0.45	+/- 1.40		10.0 +/- 0.12	0.2
B3	+/- 7.5	+/- 0.45	+/- 1.40	+/- 0.10		0.3
G3	+15.0	+/- 0.45	+/- 1.40		7.5 +/- 0.10	0.3
B4	+/- 6.0	+/- 0.45	+/- 1.40	+/- 0.10		0.2
G4	+12.0	+/- 0.45	+/- 1.40		6.0 +/- 0.10	0.2
B5	+/- 6.0	+/- 0.33	+/- 1.03	+/- 0.06		1.0
G5	+12.0	+/- 0.33	+/- 1.03		6.0 +/- 0.06	1.0
B6	+/- 5.0	+/- 0.33	+/- 1.03	+/- 0.05		1.0
G6	+10.0	+/- 0.33	+/- 1.03		5.0 +/- 0.05	1.0
B7	+/- 5.0	+/- 0.25	+/- 0.78	+/- 0.05		2.0
G7	+10.0	+/- 0.25	+/- 0.78		5.0 +/- 0.05	2.0

0.655" DIAMETER FLANGE MOUNT, SHORT TRAVEL







Flat Button Shown

Standard Characteristics/Ratings:**ELECTRICAL RATINGS:**

Insulation Resistance:	100MΩ min @ 50VDC
Null Temp Coefficient:	+/- 0.04% of full scale per degree C max
Hysteresis:	+/- 0.5% of full scale within 1 second after release
Sensitivity Temp Coefficient:	+/- 0.2% full scale per degree C
Resolution:	Infinite
Seal:	Enclosure dusttight per MIL-PRF-8805 Design 2
Operating Force:	3.0 lbs.
Operating Temp Range:	-40°C to +71°C
Storage Temp Range:	-55°C to +85°C
Travel:	To mechanical stop 0.05 inches max

MATERIALS:

Button:	Thermoplastic or anodized aluminum
Terminals:	Tin plate over copper plate over brass
Wire:	MIL-W-16878/4, 12 inches min, 24 AWG
Hardware:	None provided

**AVAILABLE CIRCUITS****J2-S2 PART NUMBER CODE**

J2-S2 X XX X X XX


Circuit Type Electrical I/O (See Table) Termination Button Style Color

A. Full Bridge	B1.	1. Wire Leads	A. Conical Hat	P1. Red Thermoplastic ①
B. Half Bridge	B2.	2. Terminals	B. Flat Button	P2. Black Thermoplastic ①
C. Isolated	B3.			P8. Gray Thermoplastic ①
	B4.			BA. Black Anodized Aluminum ②
	B5.			CA. Clear Anodized Aluminum ②
	B6.			
	B7.			
	G1.			
	G2.			
	G3.			
	G4.			
	G5.			
	G6.			
	G7.			

① Conical hat only.
② Flat button only.**EXCITATION VOLTAGE TABLE**

Circuit Configuration	Excitation Voltage (Units VDC)	Sensitivity Until Stop (Units VDC/lb. +/- 20%)	Max Output at Stop (Units VDC)	Null Output at 25°C Bipolar (Units VDC)	Null Output at 25°C Supply to Ground (Units VDC)	Full Scale Travel Cycles (Units x 10s)
B1	+/- 12.0	+/- 0.45	+/- 1.40	+/- 0.12		0.2
G1	+ 24.0	+/- 0.45	+/- 1.40		12.0 +/- 0.12	0.2
B2	+/- 10.0	+/- 0.45	+/- 1.40	+/- 0.12		0.2
G2	+ 20.0	+/- 0.45	+/- 1.40		10.0 +/- 0.12	0.2
B3	+/- 7.5	+/- 0.45	+/- 1.40	+/- 0.10		0.3
G3	+ 15.0	+/- 0.45	+/- 1.40		7.5 +/- 0.10	0.3
B4	+/- 6.0	+/- 0.45	+/- 1.40	+/- 0.10		0.2
G4	+ 12.0	+/- 0.45	+/- 1.40		6.0 +/- 0.10	0.2
B5	+/- 6.0	+/- 0.33	+/- 1.03	+/- 0.06		1.0
G5	+ 12.0	+/- 0.33	+/- 1.03		6.0 +/- 0.06	1.0
B6	+/- 5.0	+/- 0.33	+/- 1.03	+/- 0.05		1.0
G6	+ 10.0	+/- 0.33	+/- 1.03		5.0 +/- 0.05	1.0
B7	+/- 5.0	+/- 0.25	+/- 0.78	+/- 0.05		2.0
G7	+ 10.0	+/- 0.25	+/- 0.78		5.0 +/- 0.05	2.0

0.560" DIAMETER FLANGE MOUNT, SHORT TRAVEL



Flat Button Shown



Standard Characteristics/Ratings:

ELECTRICAL RATINGS:


Insulation Resistance:	100MΩ min @ 50VDC
Null Temp Coefficient:	+/- 0.04% of full scale per degree C max
Hysteresis:	+/- 0.5% of full scale within 1 second after release
Sensitivity Temp Coefficient:	+/- 0.2% full scale per degree C
Resolution:	Infinite
Seal:	Enclosure dusttight per MIL-PRF-8805 Design 2
Operating Force:	3.0 lbs.
Operating Temp Range:	-40°C to +71°C
Storage Temp Range:	-55°C to +85°C
Travel:	To mechanical stop 0.05 inches max

MATERIALS:

Wire:	MIL-W-16878/4, 12 inches min 24 AWG
Button:	Thermoplastic or anodized aluminum
Hardware:	None provided



AVAILABLE CIRCUITS



J2-S3 PART NUMBER CODE

J2-S3	X	XX	X	X	XX
Circuit Type	Electrical I/O (See Table)	Termination	Button Style	Color	
A. Full Bridge	B1.	1. Wire Leads	A. Conical Hat	P1. Red Thermoplastic ①	
B. Half Bridge	B2.		B. Flat Button	P2. Black Thermoplastic ①	
	B3.			P8. Gray Thermoplastic ①	
	B4.			BA. Black Anodized Aluminum ②	
	B5.			CA. Clear Anodized Aluminum ②	
	G1.				
	G2.				
	G3.				
	G4.				
	G5.				

① Conical hat only.
② Flat button only.

EXCITATION VOLTAGE TABLE						
Circuit Configuration	Excitation Voltage (Units VDC)	Sensitivity Until Stop (Units VDC/lb. +/- 20%)	Max Output at Stop (Units VDC)	Null Output at 25°C Bipolar (Units VDC)	Null Output at 25°C Supply to Ground (Units VDC)	Full Scale Travel Cycles (Units x 10 ⁴)
B1	+/- 7.5	+/- 0.45	+/- 1.40	+/- 0.10		0.3
G1	+ 15.0	+/- 0.45	+/- 1.40		7.5 +/- 0.10	0.3
B2	+/- 6.0	+/- 0.45	+/- 1.40	+/- 0.10		0.2
G2	+ 12.0	+/- 0.45	+/- 1.40		6.0 +/- 0.10	0.2
B3	+/- 6.0	+/- 0.33	+/- 1.03	+/- 0.06		1.0
G3	+ 12.0	+/- 0.33	+/- 1.03		6.0 +/- 0.06	1.0
B4	+/- 5.0	+/- 0.33	+/- 1.03	+/- 0.05		1.0
G4	+ 10.0	+/- 0.33	+/- 1.03		5.0 +/- 0.05	1.0
B5	+/- 5.0	+/- 0.25	+/- 0.78	+/- 0.05		2.0
G5	+ 10.0	+/- 0.25	+/- 0.78		5.0 +/- 0.05	2.0

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

OTTO:

[J2-S2AG62BBA](#) [J2-S2AB61BBA](#) [J2-S1AG52BBA](#) [J2-S1CB62BBA](#) [J2-S3BB51BBA](#) [J2-S2AB61AP2](#) [J2-S3AB51BBA](#) [J2-S2CB61BBA](#) [J2-S1CB42BCA](#) [J2-S3AG11BBA](#) [J2-S2CB62BBA](#) [J2-S3AB51AP2](#) [J2-S2CG61BBA](#) [J2-S2CB61AP2](#) [J2-S3AB41BBA](#) [J2-S3AB51BCA](#) [J2-S1AG52BCA](#) [J2-S1CB71BBA](#) [J2-S2AB22BBA](#) [J2-S2AB62BBA](#) [J2-S1CG71BBA](#) [J2-S1CB42BBA](#) [J2-S2AB42BBA](#) [J2-S2BB31BBA](#) [J2-S2BG72BCA](#)