

## Evaluating the AD5683R (SPI) and the AD5693R (I<sup>2</sup>C) Single-Channel, 16-Bit, Serial, Voltage Output DACs

### FEATURES

- ▶ Full-featured evaluation boards for the [AD5683R](#) (SPI) and [AD5693R](#) (I<sup>2</sup>C)
- ▶ On-board reference
- ▶ Various link options
- ▶ PC control in conjunction with the Analog Devices, Inc., [EVAL-SDP-CK1Z \(SDP-K1\)](#) controller board

### EVALUATION KIT CONTENTS

- ▶ EVAL-AD5683RARDZ (SPI) or EVAL-AD5693RARDZ (I<sup>2</sup>C) evaluation board
- ▶ AD5683R (SPI) or AD5693R (I<sup>2</sup>C) device

### HARDWARE REQUIRED

- ▶ EVAL-SDP-CK1Z (SDP-K1) controller board, which must be purchased separately

### SOFTWARE REQUIRED

- ▶ [Analysis | Control | Evaluation \(ACE\) Software](#), which is available for download from the EVAL-AD5683RARDZ (SPI) or EVAL-AD5693RARDZ (I<sup>2</sup>C) product page

### GENERAL DESCRIPTION

This user guide details the operation of the EVAL-AD5683RARDZ (serial peripheral interface (SPI)) evaluation board and the EVAL-AD5693RARDZ (I<sup>2</sup>C) evaluation board for the AD5683R (SPI) and the AD5693R (I<sup>2</sup>C), respectively, which are both single-channel, serial voltage output digital-to-analog converters (DACs).

The EVAL-AD5683RARDZ and the EVAL-AD5693RARDZ are designed to facilitate quick prototyping of the AD5683R and AD5693R circuits, thereby reducing design time. Both devices operate from a single 2.7 V to 5.5 V supply. Additionally, these devices also incorporate an internal 2.5 V on-board reference. A different reference voltage can be applied via the EXT\_REF SMB connector, if required. While sharing common features, the two DACs differ in their digital interface protocols. The AD5683R employs SPI, while the AD5693R employs I<sup>2</sup>C.

The EVAL-AD5683RARDZ and the EVAL-AD5693RARDZ interface with the USB port of a PC via the System Demonstration Platform (SDP) controller board (EVAL-SDP-CK1Z (SDP-K1)). The Analysis | Control | Evaluation (ACE) software is available for download from both the EVAL-AD5683RARDZ product page and the EVAL-AD5693RARDZ product page. This software can be used with either evaluation board to allow the user to program the AD5683R and AD5693R, respectively. A PMOD connection is also available to allow the connection of a microcontroller to either evaluation board. Note that when a microcontroller is used through the PMOD

### TYPICAL EVALUATION BOARD SETUP



**Figure 1. Evaluation Board Connected to the SDP-K1 Controller Board (EVAL-AD5683RARDZ or EVAL-AD5693RARDZ Version)**

connection, the EVAL-SDP-CK1Z (SDP-K1) must be disconnected, and the user cannot use the ACE software.

The EVAL-AD5683RARDZ and the EVAL-AD5693RARDZ both require the EVAL-SDP-CK1Z (SDP-K1) controller board, which is available for purchase from Analog Devices.

For full details on the AD5683R and the AD5693R, see the AD5683R and AD5693R data sheets, which must be consulted in conjunction with this user guide when using either of the EVAL-AD5683RARDZ or the EVAL-AD5693RARDZ evaluation boards.

TABLE OF CONTENTS

Features.....	1	Block Diagram and Description.....	4
Evaluation Kit Contents.....	1	Memory Map.....	5
Hardware Required.....	1	Evaluation Board Hardware.....	6
Software Required.....	1	Power Supplies.....	6
Typical Evaluation Board Setup.....	1	Link Configuration Options.....	7
General Description.....	1	Evaluation Board Schematics and Artwork.....	8
Getting Started.....	3	Ordering Information.....	11
Installing the Software.....	3	Bill of Materials.....	11
Initial Setup.....	3		

REVISION HISTORY

1/2024—Revision 0: Initial Version

## GETTING STARTED

### INSTALLING THE SOFTWARE

The EVAL-AD5683RARDZ and EVAL-AD5693RARDZ evaluation boards use the **Analysis | Control | Evaluation (ACE)** software, a desktop software application that allows the evaluation and control of multiple evaluation systems.

The ACE software is available for download on the EVAL-AD5683RARDZ or EVAL-AD5693RARDZ evaluation board page and must be installed before connecting the **EVAL-SDP-CK1Z (SDP-K1)** controller board to the USB port of the PC to ensure that the EVAL-SDP-CK1Z (SDP-K1) is recognized when it connects to the PC. Note that the ACE software installs all the necessary SDP drivers and the Microsoft® .NET Framework 4 by default. For full instructions on how to install and use this software, see the ACE software page on the Analog Devices website.

After the ACE software installation completes and the software is opened, the EVAL-AD5683RARDZ or EVAL-AD5693RARDZ evaluation board plugin appears.

### INITIAL SETUP

To set up the EVAL-AD5683RARDZ or EVAL-AD5693RARDZ evaluation board, take the following steps:

1. Connect the EVAL-AD5683RARDZ or EVAL-AD5693RARDZ to the EVAL-SDP-CK1Z (SDP-K1) controller board and then connect a USB cable between the SDP-K1 and the PC.
2. Run the ACE software, and the main window appears as shown in [Figure 2](#). The EVAL-AD5683RARDZ or EVAL-AD5693RARDZ board plugins appear in the **Attached Hardware** section of the **Start** tab.
3. Double-click the board plugin to open the board view shown in [Figure 3](#).
4. Double-click the **AD5683R** or **AD5693R** chip to access the chip view as shown in [Figure 4](#). This view provides a basic representation of the functionality of the board. See [Figure 5](#) and [Table 1](#) for the details on the main function blocks of the board.




Figure 3. Board View of the EVAL-AD5683RARDZ or EVAL-AD5693RARDZ




Figure 4. Chip Block Diagram View of the AD5683R or AD5693R




Figure 2. ACE Software Main Window

# BLOCK DIAGRAM AND DESCRIPTION

The EVAL-AD5683RARDZ or EVAL-AD5693RARDZ software is organized so that it appears similar to the functional block diagram shown in the data sheets. In this way, it is easy to correlate the functions on the board with the descriptions in the data sheets. A full description of each block, register, and its settings is given in the [AD5683R](#) or [AD5693R](#) data sheets.

Some of the blocks and their functions are described in this section as they pertain to the EVAL-AD5683RARDZ or EVAL-AD5693RARDZ. The block diagram is shown in [Figure 5](#), and [Table 1](#) describes the functionality of each block.




Figure 5. Block Diagram with Labels

Table 1. Block Diagram Functions

Label	Button/Function Name	Function
A	<b>CONFIGURATION</b>	This function is used to set the initial configuration for the evaluation board. Select the reference gain case from the <b>Output Gain</b> dropdown menu. A gain of 1 is the default. For a gain of 2, an external supply is needed ( $V_{DD} = V_{REF} + 1.5\text{ V}$ ). After setting up the initial configuration, click <b>Apply Changes</b> (J) to apply the values. These settings can be modified at any stage while evaluating the board.
B	<b>LDAC</b> and <b>RESET</b> (GPIO buttons)	The <b>LDAC</b> and <b>RESET</b> buttons act as external GPIO pulses to the $\overline{\text{LDAC}}$ and $\overline{\text{RESET}}$ pins. The <b>LDAC</b> button transfers data from the input registers (D) to the DAC registers (E). The <b>RESET</b> button clears all data from input registers and DAC registers. These buttons are live; therefore, there is no need to click <b>Apply Changes</b> (J).
C	<b>Select a Command</b>	The <b>Select a Command</b> dropdown menu controls how the data transfer to the device affects the input and DAC registers. When a data value is entered in an input register (D), it can be transferred to one or both of the internal DAC registers. The data transfer can be either to the DAC input register only or to both the DAC input register and the DAC register simultaneously. If both registers are updated, the channel DAC register (E) shows the new value.
D	Input register	This function is used to select the 16-bit data-word to transfer to the device. Then, click <b>Apply Changes</b> (J) to transfer the selected 16-bit data-word to the device.
E	DAC register	This box displays the value that is currently present in the DAC register on the device. Selecting the appropriate command option or toggle <b>LDAC</b> (B) to update the DAC register.
F	<b>Software RESET</b>	Click <b>Software RESET</b> to return the evaluation board and software to their default values. This button is live; therefore, there is no need to click <b>Apply Changes</b> (J).
G	<b>Load DAC</b>	Click <b>Load DAC</b> to individually control which channel loads the values from the input register to the DAC register.
H	<b>DAC</b>	The DAC configuration options provide access to individual channel configuration options, such as power-down options and hardware $\overline{\text{LDAC}}$ mask enable and disable settings.
I	<b>Internal Reference</b>	In the <b>Internal Reference</b> area, select <b>Enable</b> from the dropdown menu to enable the on-chip reference for the evaluation board. If <b>Disable</b> is selected, an external reference must be applied.
J	<b>Apply Changes</b>	Click <b>Apply Changes</b> to update the device with all the modified values. However, if there is no evaluation board connected, the input register value is not transferred to the DAC register.

BLOCK DIAGRAM AND DESCRIPTION

MEMORY MAP

All registers are fully accessible from the memory map tab. The memory map allows registers to be edited at a bit level. The bits shaded in dark gray are read only bits and cannot be accessed from [ACE](#). All other bits are toggled. Click **Apply Changes** to transfer data to the device. All changes here correspond to the

block diagram; for example, if the internal register bit is enabled, it shows as enabled on the block diagram. Any bits or registers that are in bold are modified values that have not been transferred to the evaluation board. After clicking **Apply Changes**, data is transferred to the evaluation board.




Figure 6. AD5683R or AD5693R Memory Map Tab




Figure 7. Memory Map of AD5683R or AD5693R with Pending Changes in the DAC0\_Input Register

EVALUATION BOARD HARDWARE

Before applying power and signals to the EVAL-AD5683RARDZ or EVAL-AD5693RARDZ, ensure that all link positions are as required by the operating mode. The two modes available for operating the evaluation board are SDP control mode, which must be used with the [EVAL-SDP-CK1Z \(SDP-K1\)](#), or standalone mode where an external supply must be provided.

POWER SUPPLIES

The EVAL-AD5683RARDZ and EVAL-AD5693RARDZ evaluation boards provide an on-board, 3.3 V regulator powered through the USB supply. If the evaluation board is controlled through a PMOD, or a gain of 2 is required, an external supply must be provided

via the EXT\_VDD connectors. See [Table 2](#) and the power requirements specifications in the [AD5683R](#) or [AD5693R](#) data sheets for additional details.

Both the AGND and DGND inputs are provided on the board. The AGND and DGND planes are connected at one location close to the AD5683R or AD5693R. To avoid ground loop problems, it is recommended that AGND and DGND not be connected elsewhere in the system.

All supplies are decoupled to ground with 10  $\mu$ F and 0.1  $\mu$ F capacitors.

Table 2. Power Supply Connectors

Connector	Label	External Voltage Supplies Description
EXT_VDD, Pin 1	EXT_VDD	External analog power supply from 2.7 V to 5.5 V, $V_{DD}$ .
EXT_VDD, Pin 2	EXT_VDD	Analog ground.
EXT_REF, SMB Connector	EXT_REF	External voltage reference supply.

## EVALUATION BOARD HARDWARE

## LINK CONFIGURATION OPTIONS

A number of link and switch options are incorporated on the EVAL-AD5683RARDZ or EVAL-AD5693RARDZ evaluation board and must be set for the required operating conditions before using the board. The link function options are described in [Table 4](#).

[Table 3](#) lists the positions of the different links controlled by the PC via the USB port, and an SDP controller board operating in single-supply mode is required.

**Table 3. Link Options Setup for SDP-K1 Control (Default)**

Link	Options
VDD_SEL	Position A (1-2)
REF_SEL	Position A (1-2)
VDD_VIO	Disconnected

**Table 4. Link Functions**

Link	Function Options
VDD_SEL	This link selects the DAC analog voltage source. Position A (1-2): the 3V3 option selects the on-board voltage source ( <a href="#">SDP-K1</a> , <a href="#">ADP121</a> ). Position B (2-3): the VDD_EXT option selects an external supply voltage (EXT_VDD connector).
REF_SEL	This link selects the DAC voltage reference source. Position A (1-2): the VREF_EXT option selects an external reference source (EXT_REF connector). If no external supply is present, it defaults to the internal on-chip reference. Position B (2-3) the VREF_2V5 option selects the on-board reference from the <a href="#">ADR4525</a> .
VDD_VIO	The VDD_VIO link selects the DAC digital voltage source. The following two options are available: Connected: shorts $V_{DD}$ and $V_{LOGIC}$ . Only use this option when the SDP-K1 controller board is not connected. Disconnected: opens the connection of $V_{DD}$ and $V_{LOGIC}$ . Only use this option when using the SDP-K1 controller board.





## EVALUATION BOARD SCHEMATICS AND ARTWORK




Figure 9. NanoDAC+ Evaluation Board Schematic Diagram, SDP Connector

## PMOD CONNECTOR




Figure 10. NanoDAC+ Evaluation Board Schematic Diagram, PMOD Connector






Figure 11. NanoDAC+ Evaluation Board, Component Placement

## EVALUATION BOARD SCHEMATICS AND ARTWORK



*Figure 12. NanoDAC+ Evaluation Board, Top Side Routing*



*Figure 13. NanoDAC+ Evaluation Board, Bottom Side Routing*

## ORDERING INFORMATION

## BILL OF MATERIALS

Table 5. Bill of Materials

Quantity	Reference Designator	Description	Supplier, Part Number <sup>1</sup>
1	U1	Tiny 16-bit SPI nanoDAC+, with $\pm 2$ (16-bit) LSB INL and 2 ppm/ $^{\circ}$ C reference	Analog Devices, <a href="#">AD5683R</a> or <a href="#">AD5693R</a>
1	U3	Ultra-low noise, high accuracy 2.5 V voltage reference	Analog Devices, <a href="#">ADR4542DEZ</a>
1	U5	150 mA, low quiescent current, complementary metal-oxide semiconductor (CMOS) linear regulator in 5-lead TSOT or 4-ball WLCSP	Analog Devices, <a href="#">ADP121-AUJZ33</a>
1	U6	IC, 32 KBIT serial, electrically erasable programmable read-only memory (EEPROM)	Generic
2	AGND, DGND	Connector, printed circuit board (PCB), black test points	Generic
4	C1, C8, C10, C11	0.1 $\mu$ F ceramic capacitors, 16 V, 10%, X7R, 0603	Generic
3	C12, C21, C23	0.1 $\mu$ F ceramic capacitors, 50 V, 10%, X7R, 0603	Generic
1	C22	10 $\mu$ F ceramic capacitor, 6.3 V, 20%, X5R, 0603	Generic
3	C4, C5, C24	1 $\mu$ F ceramic capacitors, 16 V, 10%, X7R, 0603	Generic
1	C34	4.7 $\mu$ F ceramic capacitor, 10 V, 20%, X5R, 0603	Generic
2	C7, C9	10 $\mu$ F ceramic capacitors, 10 V, 20%, X5R, 0603	Generic
1	EXT_VDD	Connector-PCB, 2-position terminal block, side entry, 5 mm pitch	Generic
1	L2	Inductor, ferrite bead, 600 $\Omega$ , 25%, 100 MHz, 2.9 A, 0.038 $\Omega$ , 1206, AEC-Q200	Generic
5	LDACB, RESETB, SCLK/A0, SDIN/SDA, SYNCB/SCL	Connector-PCB, white test points	Generic
2	P4, P7	Connector-PCB, receptacles, 25 mil square post, 2.54 mm pitch	Generic
1	P5	Connector-PCB, receptacle, 25 mil square post, 2.54 mm pitch	Generic
1	P6	Connector-PCB, receptacle, 25 mil square post, 2.54 mm pitch	Generic
4	R1, R2, R8, R25	100 k $\Omega$ resistors, surface-mounted device (SMD), 1%, 1/10 W, 0603	Generic
2	R14, R24	0 $\Omega$ resistors, SMD, jumper, 1/16 W, 0402	Generic
1	R21	1.6 $\Omega$ resistor, SMD, 1%, 1/5 W, 0603, AEC-Q200	Generic
1	R22	0 $\Omega$ resistor, SMD, jumper, 1/2 W, 0805, AEC-Q200, pulse proof	Generic
2	REF_SEL, VDD_SEL	Connector-PCB, high temperature, 3-position, male headers, unshrouded, single row, straight, 2.54 mm pitch, 3.05 mm solder tail	Generic
4	VDD, VLOGIC, VOUT, VREF	Connector-PCB, red test points	Generic
1	VDD_VIO	Connector-PCB, header, 1 row, 2 way	Generic
4	R4, R7, R10, R18	0 $\Omega$ resistors, SMD, jumper, 1/10 W, 0603	Generic- Pref/install for EVAL-AD5683RARDZ
5	R5, R9, R13, R17, R19	0 $\Omega$ resistors, SMD, jumper, 1/10 W, 0603	Generic- Pref/install for EVAL-AD5693RARDZ
4	R4, R7, R10, R18	0 $\Omega$ resistors, SMD, jumper, 1/10 W, 0603, Do not insert (DNI) or do not populate (DNP) for EVAL-AD5693RARDZ	Not applicable
6	R5, R9, R11, R13, R17, R19	0 $\Omega$ resistors, SMD, jumper, 1/10 W, 0603, DNI or DNP for EVAL-AD5683RARDZ	Not applicable
1	C2	0.1 $\mu$ F ceramic capacitor, 16 V, 10%, X7R, 0603, DNI or DNP for both boards	Not applicable
1	C6	10 nF ceramic capacitor, 200 V, 10%, X7R, 0805, FLEXITERM <sup>®</sup> , DNI or DNP for both boards	Not applicable
2	EXT_REF, V_OUT	Connector-PCB, coax, SMB, jacks, RF vertical, PC mount gold, DNI or DNP for both boards	Not applicable
1	PMOD	Connector-PCB, BERG, header, straight, male, 12 position, DNI or DNP for both boards	Not applicable

## ORDERING INFORMATION

Table 5. Bill of Materials (Continued)

Quantity	Reference Designator	Description	Supplier, Part Number <sup>1</sup>
1	R12	2 k $\Omega$ resistor, SMD, 1%, 1/8 W, 0805, AEC-Q200, DNI or DNP for both boards	Not applicable
1	R15	0 $\Omega$ resistor, SMD, jumper, 1/16 W, 0402, DNI or DNP for both boards	Not applicable
1	R16	100 k $\Omega$ resistor, SMD, 1%, 1/10 W, 0603, AEC-Q200, DNI or DNP for both boards	Not applicable
1	R3	100 k $\Omega$ resistor, SMD, 1%, 1/10 W, 0603, DNI or DNP for both boards	Not applicable

<sup>1</sup> Generic indicates that any part with the specified value, size, and rating can be used.

## NOTES

I<sup>2</sup>C refers to a communications protocol originally developed by Philips Semiconductors (now NXP Semiconductors).

**ESD Caution**

**ESD (electrostatic discharge) sensitive device.** Charged devices and circuit boards can discharge without detection. Although this product features patented or proprietary protection circuitry, damage may occur on devices subjected to high energy ESD. Therefore, proper ESD precautions should be taken to avoid performance degradation or loss of functionality.

**Legal Terms and Conditions**

By using the evaluation board discussed herein (together with any tools, components documentation or support materials, the "Evaluation Board"), you are agreeing to be bound by the terms and conditions set forth below ("Agreement") unless you have purchased the Evaluation Board, in which case the Analog Devices Standard Terms and Conditions of Sale shall govern. Do not use the Evaluation Board until you have read and agreed to the Agreement. Your use of the Evaluation Board shall signify your acceptance of the Agreement. This Agreement is made by and between you ("Customer") and Analog Devices, Inc. ("ADI"), with its principal place of business at Subject to the terms and conditions of the Agreement, ADI hereby grants to Customer a free, limited, personal, temporary, non-exclusive, non-sublicensable, non-transferable license to use the Evaluation Board FOR EVALUATION PURPOSES ONLY. Customer understands and agrees that the Evaluation Board is provided for the sole and exclusive purpose referenced above, and agrees not to use the Evaluation Board for any other purpose. Furthermore, the license granted is expressly made subject to the following additional limitations: Customer shall not (i) rent, lease, display, sell, transfer, assign, sublicense, or distribute the Evaluation Board; and (ii) permit any Third Party to access the Evaluation Board. As used herein, the term "Third Party" includes any entity other than ADI, Customer, their employees, affiliates and in-house consultants. The Evaluation Board is NOT sold to Customer; all rights not expressly granted herein, including ownership of the Evaluation Board, are reserved by ADI. CONFIDENTIALITY. This Agreement and the Evaluation Board shall all be considered the confidential and proprietary information of ADI. Customer may not disclose or transfer any portion of the Evaluation Board to any other party for any reason. Upon discontinuation of use of the Evaluation Board or termination of this Agreement, Customer agrees to promptly return the Evaluation Board to ADI. ADDITIONAL RESTRICTIONS. Customer may not disassemble, decompile or reverse engineer chips on the Evaluation Board. Customer shall inform ADI of any occurred damages or any modifications or alterations it makes to the Evaluation Board, including but not limited to soldering or any other activity that affects the material content of the Evaluation Board. Modifications to the Evaluation Board must comply with applicable law, including but not limited to the RoHS Directive. TERMINATION. ADI may terminate this Agreement at any time upon giving written notice to Customer. Customer agrees to return to ADI the Evaluation Board at that time. LIMITATION OF LIABILITY. THE EVALUATION BOARD PROVIDED HEREUNDER IS PROVIDED "AS IS" AND ADI MAKES NO WARRANTIES OR REPRESENTATIONS OF ANY KIND WITH RESPECT TO IT. ADI SPECIFICALLY DISCLAIMS ANY REPRESENTATIONS, ENDORSEMENTS, GUARANTEES, OR WARRANTIES, EXPRESS OR IMPLIED, RELATED TO THE EVALUATION BOARD INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTY OF MERCHANTABILITY, TITLE, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF INTELLECTUAL PROPERTY RIGHTS. IN NO EVENT WILL ADI AND ITS LICENSORS BE LIABLE FOR ANY INCIDENTAL, SPECIAL, INDIRECT, OR CONSEQUENTIAL DAMAGES RESULTING FROM CUSTOMER'S POSSESSION OR USE OF THE EVALUATION BOARD, INCLUDING BUT NOT LIMITED TO LOST PROFITS, DELAY COSTS, LABOR COSTS OR LOSS OF GOODWILL. ADI'S TOTAL LIABILITY FROM ANY AND ALL CAUSES SHALL BE LIMITED TO THE AMOUNT OF ONE HUNDRED US DOLLARS (\$100.00). EXPORT. Customer agrees that it will not directly or indirectly export the Evaluation Board to another country, and that it will comply with all applicable United States federal laws and regulations relating to exports. GOVERNING LAW. This Agreement shall be governed by and construed in accordance with the substantive laws of the Commonwealth of Massachusetts (excluding conflict of law rules). Any legal action regarding this Agreement will be heard in the state or federal courts having jurisdiction in Suffolk County, Massachusetts, and Customer hereby submits to the personal jurisdiction and venue of such courts. The United Nations Convention on Contracts for the International Sale of Goods shall not apply to this Agreement and is expressly disclaimed.



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Analog Devices Inc.:](#)

[EVAL-AD5693RARDZ](#)