

Johanson Company: Johanson Technology inc. NCNR: 1

Deprecated P/N: 7000AT44A1100E-AEC

Thickness (Max): 0.063

Datasheet Date: 08-10-2024

Thickness (Min): 0.055

Description: Antennas, 1712, 1570-1580MHz, 2W,
0.5dBi (typ), 1575MHz GPS Ultra-Compact
Antenna, Ni/Sn (RoHS), 7" Reel Embossed Tape,
AEC Q200 Qualified

End Band (Min):

End Band (Max):

Life Cycle Stage: EOL

Lead Time Typical (Weeks)*:

*This can vary significantly so it is important
to obtain a quotation with lead time for
production planning purposes. 20

AEC Q200 Qualified: 1

Length (Min): 0.165

Schedule B: 8529

Length (Max): 0.189

ECCN: EAR99

Width (Min): 0.110

RoHS Compliance: Yes, RoHS 10/10

Width (Max): 0.134

REACH: 1

Packaging: 7" Reel Embossed Tape

Country of Origin: TW

Operating Temp Range: -40°C to +85°C

Product Family: Antennas

Storage Temp Range (Packaged): -55°C to
+125°C

Product Subfamily: Antennas

Storage Temp Range (Non Operating): +5°C to
+40°C with RH 20% to 70%

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Johanson:](#)

[7000AT44A1100E-AEC](#)