



MCZ SC 0-10V**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Product image****MCZ: The smallest solution**

- The smallest analogue signal converter in terminal block format on the market
- Space-saving conversion of analogue signals in the control cabinet thanks to the slim, 6 mm wide module width
- Simple wiring with plug-in cross-connectors

General ordering data

Version	Limit value monitoring, Input : 0-10 V, Output 2 x transistor
Order No.	8260280000
Type	MCZ SC 0-10V
GTIN (EAN)	4008190985417
Qty.	10 pc(s).

MCZ SC 0-10V

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	63.2 mm	Depth (inches)	2.488 inch
Width	6 mm	Width (inches)	0.236 inch
Length	91 mm	Length (inches)	3.583 inch
Weight	30 g	Net weight	29.6 g

Temperatures

Storage temperature	-25 °C...60 °C	Operating temperature	0 °C...50 °C
Humidity	40 °C / 93 % rel. humidity, no condensation		

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
------------	----------------

Input

Input resistance, voltage	60 kΩ	Input voltage	0...10 V
Number of inputs	1		

Output

Contact assembly	Transistor output, double switch output PNP	Cut-off frequency (-3 dB)	100 Hz
Number of outputs	2	Switching thresholds	Via 2 potentiometers (12 turns)

General data

Configuration	Potentiometer	Current consumption	15 mA
Galvanic isolation	Without isolation	Rail	TS 35
Step response time	< 250 μs (switching threshold at 90% of max. input signal; $R_i \leq 1$ kΩ)	Temperature coefficient	max. 250 ppm/K
Type of connection	Tension-clamp connection	Voltage supply	24 V DC $\pm$ 20 %

Insulation coordination

EMC standards	EN 55011, EN 61000-6	Galvanic isolation	Without isolation
Insulation voltage input or output/rail	4 kV _{eff} / 1 min.		

Connection data

Type of connection	Tension-clamp connection	Clamping range, rated connection	1.5 mm ²
Clamping range, min.	0.5 mm ²	Clamping range, max.	1.5 mm ²

Classifications

ETIM 6.0	EC002654	ETIM 7.0	EC002654
ETIM 8.0	EC002654	ECLASS 9.0	27-21-01-22
ECLASS 9.1	27-21-01-22	ECLASS 10.0	27-21-01-22
ECLASS 11.0	27-21-01-22		

MCZ SC 0-10V

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Tender specification sheets

Long specification

Trip amplifier for monitoring a 0...10 V standard signal with two switching outputs
Trip amplifier in 6 mm width for analogue 0...10 V standard signals with two PNP-transistor switch outputs for monitoring an upper and lower threshold (adjustable via potentiometer).
DIP switches can be used to select a range of 300 mV to 10 V, 30 mV to 1 V, and 10 mV to 100 mV on the input side.

Add-on housing for TS35 rail mounting
Dimensions: L/W/H 91/6/ 63.2 mm
Tension-clamp connection / Nominal cross-section 1.5 mm²
Protection degree: IP 20

Input
0...10 V

ranges 300 mV...10 V / 30 mV...1 V / 10 mV...100 mV

Output
Double switching output PNP/ 50 mA per channel

adjustable via potentiometer
Switching hysteresis 1 % of input
Step response time < 250 us (10...90 %)
Temperature coefficient < 250 ppm K
Auxiliary power 24 V DC +/- 20 %
Ambient temperature range 0°C...+50 °C

Isolation 1.5 kV
Approvals cURus, CSA

Type
MCZ SC 0-10V

Short specification

Trip amplifier for monitoring a 0...10 V standard signal with two switching outputs
Trip amplifier in 6 mm width for analogue 0...10 V standard signals with two PNP-transistor switch outputs for monitoring an upper and lower threshold (adjustable via potentiometer).
DIP switches can be used to select a range of 300 mV to 10 V, 30 mV to 1 V, and 10 mV to 100 mV on the input side.

MCZ SC 0-10V

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS	Conform
UL File Number Search	E141197

Downloads

Approval/Certificate/Document of Conformity	Declaration of Conformity
Engineering Data	CAD data – STEP
Engineering Data	EPLAN, WSCAD
User Documentation	Instruction sheet
Catalogues	Catalogues in PDF-format
Brochures	



MCZ SC 0-10V

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany


www.weidmueller.com

Drawings

Connection diagram



dimensions



MCZ SC 0-10V

Weidmüller Interface GmbH & Co. KG


Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

4 mm²

The plug-in cross-connections feature easy handling and quick installation. This saves a great deal of time during installation in comparison with screwed solutions.

General ordering data

Type	ZQV 4N/2 GE	Version
Order No.	1758250000	Accessories, Cross-connector, 32 A
GTIN (EAN)	4032248169795	
Qty.	60 pc(s).	
Type	ZQV 4N/3 GE	Version
Order No.	1762630000	Accessories, Cross-connector, 32 A
GTIN (EAN)	4032248169788	
Qty.	60 pc(s).	
Type	ZQV 4N/4 GE	Version
Order No.	1762620000	Accessories, Cross-connector, 32 A
GTIN (EAN)	4032248169771	
Qty.	60 pc(s).	
Type	ZQV 4N/10 GE	Version
Order No.	1758260000	Accessories, Cross-connector, 32 A
GTIN (EAN)	4032248169764	
Qty.	20 pc(s).	

AP MCZ 1.5 - End plate



Open miniature housing in modular terminal format with five tension clamp connections. A transparent hinged top plate can be used for labelling and provides access to potentiometer and status displays. Plug-in cross-connectors can be used to interconnect the three top connections. A cover plate for closing off the housing is also available.

General ordering data

Type	AP MCZ1.5 1674	Version
Order No.	8389030000	Small housing, OMNIMATE Housing - TERMINALBOX grey-beige, End plate, Width: 1.5 mm
GTIN (EAN)	4008190386849	
Qty.	50 pc(s).	

MCZ SC 0-10V

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

Blank



WS markers are the perfect match for the W-series connectors. Thanks to their system compatibility, the WS tags can also be used with the I-series and the Z-series. The large marking surfaces do not only permit long character strings but also multi-line text. WS markers are ideal for labels with long, customised character strings. Thanks to the proven MultiCard format, printing with PrintJet CONNECT oder/or Plotter is possible.

- Can be fitted in strips or individually
- Markers in proven MultiCard format

For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

General ordering data

Type	WS 10/6 MC NE WS	Version
Order No.	1828450000	WS, Terminal marker, 10 x 6 mm, Pitch in mm (P): 6.00 Weidmueller,
GTIN (EAN)	4032248350513	Allen-Bradley, white
Qty.	600 pc(s).	

SAK-Series



Weidmüller's range of products includes end brackets that guarantee a permanent, reliable mounting on the terminal rail and prevent sliding. Versions with and without screws are available. The end brackets include marking options, also for group markers, and also a test plug holder.

General ordering data

Type	EW 35	Version
Order No.	0383560000	Accessories, End bracket
GTIN (EAN)	4008190181314	
Qty.	50 pc(s).	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Weidmuller:](#)

[8260280000](#)