
# **RF CERAMIC CHIP INDUCTORS**



Polarity Half-Marked Inductors (0201 only)

### **PRODUCT RANGE SUMMARY**

High frequency multi-layer chip inductors feature a monolithic body made of low loss ceramic and high conductivity metal electrodes to achieve optimal high frequency performance.

These RF chip inductors are compact in size and feature lead-free tin plated nickel barrier terminations and tape and reel packaging which makes them ideal for small size/high volume wireless applications.

### **APPLICATIONS & FEATURES**

- CELL/PCS Modules
- Wireless LAN

RFID


- Broadband Components
- RF Tranceivers
- RoHS Compliant (Standard, "V" Code)
- Sn/Pb Terminations Optional ("T" Code)

EIA SIZE (mm)	SIZE CODE	L RANGE	Q FACTOR (Min.)	SRF (Typ.)	TEMPERATURE
0201 (0603)	L-05	0.6 - 39 nH	4 (100 MHz)	>21 GHz (1.0 nH)	-55°C to +100°C
0402 (1005)	L-07	1.0 - 120 nH	8 (100 MHz)	>21 GHz (1.0 nH)	-55°C to +100°C
0603 (1608)	L-14	1.0 - 220 nH	12 (100 MHz)	>23 GHz (1.0 nH)	-55°C to +100°C

#### **Mechanical Characteristics**

	0201 (	(0603)	0402 (	(1005)	0603 (	(1608)
	Inches	mm	Inches	mm	Inches	mm
Length	.024 ±.001"	(0.6 ±0.03)	.039 ±.004"	(1.00 ±.10)	$.063 \pm .006"$	(1.60 ±.15)
Width	.012 ±.001"	(0.3 ±0.03)	.020 ±.004"	(0.50 ±.10)	.031 ±.006"	(0.80 ±.15)
Thickness	.012 ±.001"	(0.3 ±0.03)	.020 ±.004"	(0.50 ±.10)	.031 ±.006"	(0.80 ±.15)
End Band	.006 ±.002"	(0.15 ±0.05)	$.009 \pm .004"$	(0.23 ±.10)	.012 ±.008"	(0.30 ±.20)

#### How to Order





\*Please note that all 0402 inductors (L-07C) have orientation full marking only.




## **RF CHIP INDUCTOR SELECTION CHART**

EIA Size		A Size	0201 (L-05)	0402 (L-07)	0603 (L-14)
			(= ••)	(= •••)	(= · · )
Induc		Tolerance			
nH	Code		000 1		
0.6	0N6 0N7	-	300 mA 300 mA		
0.7	0N7 0N8	-	300 mA		
0.0	0N9	-	300 mA		
1.0	1N0	-	300 mA	300 mA	300 mA (S only)
1.2	1N2		300 mA	300 mA (S only)	300 mA (S only)
1.3	1N3	-	300 mA		
1.5	1N5		300 mA	300 mA (S only)	300 mA (S only)
1.8	1N8		300 mA	300 mA (S only)	300 mA (S only)
1.9	1N9	S 🗆	300 mA	300 mA (S only)	
2.0	2N0		300 mA	300 mA (S only)	
2.2	2N2		300 mA	300 mA (S only)	300 mA (S only)
2.3	2N3		300 mA		
2.4	2N4		300 mA	300 mA (S only)	
2.5	2N5		300 mA		
2.7	2N7		300 mA	300 mA (S only)	300 mA (S only)
3.0	3N0		300 mA	300 mA (S only)	
3.3	3N3		300 mA	300 mA	300 mA
3.6	3N6		300 mA	300 mA	
3.7	3N7		300 mA		
3.9	3N9	K 🗖	300 mA	300 mA	300 mA
4.3	4N3			300 mA	
4.7	4N7	S —	300 mA	300 mA	300 mA
5.1	5N1		300 mA	300 mA	
5.6	5N6		300 mA	300 mA	300 mA
6.2	6N2			300 mA	
6.8	6N8		250 mA	250 mA	300 mA
7.5	7N5	-		250 mA	
8.2	8N2	-	250 mA	250 mA	300 mA
10	10N	-	250 mA	250 mA	300 mA
12	12N	-	250 mA	250 mA	300 mA
13 15	13N 15N	-	250 mA	250 mA	300 mA
		-	250 mA	250 mA	
18 22	18N 22N	-	200 mA 200 mA	200 mA 200 mA	300 mA 300 mA
23	22N 23N		200 MA	200 mA	500 MA
23	23N 27N		200 mA	200 mA	300 mA
33	33N		200 mA	200 mA	300 mA
39	39N		200 mA	150 mA	300 mA
43	43N	J	2001111	150 mA	000111/1
47	47N			150 mA	300 mA
56	56N	K –		150 mA	300 mA
68	68N	IX		100 mA	300 mA
82	82N			100 mA	300 mA
100	R10			100 mA	300 mA
120	R12			100 mA	300 mA
150	R15				300 mA
180	R18		· · · · · · · · · · · · · · · · · · ·		300 mA
220	R22				300 mA
270	R27				
330	R33				
390	R39				
420	R42				
560	R56				
680	R68				

Consult factory for Non-Standard values. C tolerance are non-standard terms See web page for Chip Inductor Product Detail Summary by part number



## **RF** CHARACTERISTICS CHARACTERISTICS (Typical)





# **Mouser Electronics**

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

## Johanson:

L-07C3N3SV6T L-07C12NJV6T L-07C18NJV6T L-07C8N2JV6T L-07C10NJV6T L-07C3N9SV6T L-14C39NJV4T
L-07C7N5JV6T L-07C1N8SV6T L-07C1N5SV6T L-07C15NJV6T L-07C6N8JV6T L-07C2N2SV6T L-07C5N6SV6T
L-07C27NJV6T L-07C4N7SV6T L-05B2N2SV6T L-14C6N8JV4T L-07C2N7SV6T L-07C4N3SV6T L-05B3N0KV6T
L-14C15NKV4T L-05B1N8SV6T L-05B33NKV6T L-05B1N0SV6T L-07C7N5KV6T L-05B8N2KV6T L-14C39NKV4T
L-05B6N8JV6T L-14C1N0SV4T L-07C33NKV6T L-07C47NJV6T L-14CR22JV4T L-14C6N8KV4T L-14C68NJV4T
L-07C2N4SV6T L-07C20NJV6T L-14C3N9KV4T L-05B15NKV6T L-05B27NJV6T L-07CR12JV6T L-07C68NKV6T
L-05B12NKV6T L-14C27NKV4T L-05B5N1SV6T L-14C12NJV4T L-05B4N7KV6T L-05B2N4SV6T L-14CR12JV4T
L-14C56NKV4T L-07C27NKV6T L-07C18NKV6T L-14C4N7KV4T L-14C33NJV4T L-07C5N6KV6T L-14CR15KV4T
L-07C3N6KV6T L-07C56NJV6T L-14CR10KV4T L-07C3N0KV6T L-05B22NKV6T L-07CR10KV6T L-05B12NJV6T
L-07C5N1SV6T L-05B3N9SV6T L-14C1N8SV4T L-05B3N3SV6T L-14C8N2JV4T L-07C22NKV6T L-14C27NJV4T
L-14C47NKV4T L-07C13NKV6T L-05B5N6KV6T L-05B6N8KV6T L-14C18NJV4T L-05B39NJV6T L-14C12NKV4T
L-14C68NKV4T L-07C2N0SV6T L-14C5N6KV4T L-14C33NKV4T L-14C3N3KV4T L-07C1N0SV6T L-07C47NKV6T
L-14CR22KV4T L-14CR18JV4T L-07C43NJV6T L-05B18NJV6T L-05B2N7SV6T L-05B1N2SV6T L-07C6N2KV6T
<u>L-07C6N8KV6T</u> <u>L-07C3N9KV6T</u> <u>L-14CR15JV4T</u> <u>L-14CR18KV4T</u> <u>L-14C5N6SV4T</u> <u>L-07C1N2SV6T</u> <u>L-07C6N2SV6T</u>
L-05B15NJV6T L-07C43NKV6T