

IE-C5CS8UG-100**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Bulk stock, copper cable, rigid, 4 x 2 x AWG 24/1, Cat. 5,
green

General ordering data

Version	Installation cable, Cat.5 (ISO/IEC 11801) / Cat.5e (TIA T568-B), PUR, 100 m
Order No.	8813160000
Type	IE-C5CS8UG-100
GTIN (EAN)	4032248513017
Qty.	1 pc(s).

IE-C5CS8UG-100

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Length	100 m	Length (inches)	3,937.008 inch
Net weight	4,544 g		

Temperatures

Storage temperature	-40 °C...80 °C	Operating temperature	-40 °C...80 °C
Installation temperature	-15 °C...60 °C		

Technical specifications for cable

Halogen	halogen-free, according to IEC 60754-2	Insulation	PE
Number of poles	8	Number of wires	8
Resistance to oils	in accordance with IEC 60811-2-1	Resistance to spread of flame	in accordance with IEC 60332-1
Sheathing colour	green (RAL 6018)	Test voltage: wire-wire-shield	700 V AC

Cable specific standards

Generic communication cable facilities	EN 50173-1:2007, ISO / IEC 11801:2002
--	---------------------------------------

Standards

Generic communication cable facilities	EN 50173-1:2007, ISO / IEC 11801:2002
--	---------------------------------------

Cable structure

Arrangement of wire cores		Colour sequence or wires - wire pairs	white - blue, white - orange, white - green, white - brown
	Twisted pair		
Complete shielding	Aluminium foil, Shielding braid made from copper wiring	Cross-section	4*2*AWG 24/1 - 4*2*0.205 mm ²
Insulation	PE	Insulation cross-section	1 mm
Material sheath	PUR	Number of wires	8
Sheath diameter, max.	6.7 mm	Sheath diameter, min.	6.3 mm
Sheathing colour	green (RAL 6018)	Shielding	SF/UTP
Standard designations	IE-5IC4x2xAWG24/1-PUR 02YS(ST)C11Y, SF/UTP	Strands	1
Wire material	Non-insulated copper wire		

Electrical properties of cable

Capacity at 1 kHz	50 nF/km	Category	Cat.5 (ISO/IEC 11801) / Cat.5e (TIA T568-B)
Characteristic impedance	100 ± 5 Ω at 100MHz	Deviation	15 ns/100m
Loop resistance	190 Ω/km	Signal propagation time	4.5 ns/m
Test voltage: wire-wire-shield	700 V AC	Transfer impedance	10 mΩ/m at 10 MHz

IE-C5CS8UG-100

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Mechanical and material properties of cable

Abrasion resistance	very good	Colour	green
Halogen	halogen-free, according to IEC 60754-2	Min. bending radius, once only	5 x cable diameter
Min. bending radius, repetitive	10 x cable diameter	Resistance to oils	in accordance with IEC 60811-2-1
Resistance to spread of flame	in accordance with IEC 60332-1		

Classifications

ETIM 6.0	EC000830	ETIM 7.0	EC003249
ETIM 8.0	EC003249	ECLASS 9.0	27-06-18-05
ECLASS 9.1	27-06-90-90	ECLASS 10.0	27-06-18-01
ECLASS 11.0	27-06-18-01		

Approvals

ROHS	Conform
------	---------

Downloads

User Documentation	MAN IE GUIDE DE MAN IE GUIDE EN
Catalogues	Catalogues in PDF-format
Brochures	FL FIELDWIRING EN PI PROFINET CABLING EN PI PROFINET CABLING EN

IE-C5CS8UG-100

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26


D-32758 Detmold

Germany

www.weidmueller.com

Drawings

Detailed drawing



IE-C5CS8UG-100**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****Tools**

The CST with blue blade cartridge produces the best stripping results. The blue double-stage blade cartridge is particularly suited for Ethernet cables. It saves time and also ensures optimal stripping results.

General ordering data

Type	IE-CST	Version
Order No.	9204350000	Tools, Sheathing strippers
GTIN (EAN)	4032248653072	
Qty.	1 pc(s).	

Tools

Sheathing stripper for PVC cables

**General ordering data**

Type	AM 12	Version
Order No.	9030060000	Tools, Sheathing strippers
GTIN (EAN)	4008190337827	
Qty.	1 pc(s).	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Weidmuller:](#)

[8813160000](#)