

**H1,5/20D ZH SW****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

- supplied loose in poly-bag
- Weidmüller colour code
- DIN colour code

**General ordering data**

|            |                                                              |
|------------|--------------------------------------------------------------|
| Version    | Wire-end ferrule, Twin wire-end ferrule, 15 mm, 12 mm, black |
| Order No.  | <a href="#">9037480000</a>                                   |
| Type       | H1,5/20D ZH SW                                               |
| GTIN (EAN) | 4008 190493059                                               |
| Qty.       | 500 pc(s).                                                   |
| Packaging  | loose                                                        |

## H1,5/20D ZH SW

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

|            |         |
|------------|---------|
| Net weight | 0.178 g |
|------------|---------|

## Technical data

|                        |                              |         |                       |
|------------------------|------------------------------|---------|-----------------------|
| Description of article | Twin wire end ferrule, black | Version | Twin wire-end ferrule |
|------------------------|------------------------------|---------|-----------------------|

## Wire-end ferrules

|                                         |        |                             |                     |
|-----------------------------------------|--------|-----------------------------|---------------------|
| Collar height (A)                       | 6.5 mm | Collar width (B)            | 3.6 mm              |
| Colour code                             | DIN    | Conductor cross-section     | 1.5 mm <sup>2</sup> |
| Contact surface diameter (D1)           | 2.2 mm | Contact surface length (L2) | 12 mm               |
| L1 in mm                                | 20 mm  | Metal sleeve thickness (S1) | 0.15 mm             |
| Plastic collar thickness (S2)           | 0.3 mm | Stripping length            | 15 mm               |
| Wire connection cross section AWG, max. | AWG 16 |                             |                     |

## Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC000005    | ETIM 7.0    | EC000005    |
| ETIM 8.0    | EC000005    | ECLASS 9.0  | 27-40-02-01 |
| ECLASS 9.1  | 27-40-02-01 | ECLASS 10.0 | 27-40-02-01 |
| ECLASS 11.0 | 27-40-02-01 |             |             |

## Approvals

Approvals



|                       |         |
|-----------------------|---------|
| ROHS                  | Conform |
| UL File Number Search | E499744 |

## Downloads

|                    |                                                                                          |
|--------------------|------------------------------------------------------------------------------------------|
| Engineering Data   | <a href="#">CAD data – STEP</a>                                                          |
| Engineering Data   | <a href="#">EPLAN, WSCAD, Zuken E3.S</a>                                                 |
| User Documentation | <a href="#">Technical information - EN</a><br><a href="#">Technical information - DE</a> |
| Catalogues         | <a href="#">Catalogues in PDF-format</a>                                                 |
| Brochures          |                                                                                          |

**H1,5/20D ZH SW****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Drawings****Drawing**

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Weidmuller:](#)

[9037480000](#)