

Z Series


Vertical Compression (Z-axis), Open-Pin Field

Contact spacing: 0.050" (1.27 mm)

A high-density, open-field, vertically-compressed connector utilizing a patented z-axis contact system configured for between-board (board-to-board) compression applications.

DIMENSIONS

COLUMNS	C	D
10	0.952	0.742
15	1.202	0.992
20	1.452	1.242
25	1.702	1.492
ROWS	E	F
2	0.210	0.105
3	0.260	0.105
4	0.310	0.155
5	0.360	0.155
6	0.410	0.205
7	0.460	0.205



HARDWARE HEIGHT (A)	CONTACT HEIGHT (B)
0.100	0.120
0.150	0.170
0.200	0.230
0.250	0.280
0.300	0.330
0.350	0.380

Sample Part Number Format: RZ250-320-115-1000



SERIES
Vertical
(Z-Axis)
Compression
Multi-Rows
0.050" Spacing
Open-Field



HEIGHT
100 – 0.100"
150 – 0.150"
200 – 0.200"
250 – 0.250"
300 – 0.300"
350 – 0.350"



ROWS
2 – 2 Rows
3 – 3 Rows
4 – 4 Rows
5 – 5 Rows
6 – 6 Rows
7 – 7 Rows



COLUMNS
10 – 10 Columns
15 – 15 Columns
20 – 20 Columns
25 – 25 Columns



CONTACT
11 – Double
compression



PLATING
5 – 50 μ" Au
3 – 30 μ" Au




HARDWARE
10 – Ø.090" Thru-hole
20 – Ø.050" Guide pin



TYPE
00 – No polarization





VARIATION
Blank – None
XXX – Consult
factory



PLEASE CONSULT THE AIRBORN WEBSITE FOR THE LATEST REVISION OF THIS DOCUMENT PRIOR TO BEGINNING ANY DESIGN WORK.

MATED HEIGHT

Mated height is defined as the space between the hardware clamping surfaces (top hardware surface to bottom hardware surface.) See Table 1.



SI DATA – Differential 100 Ohm

1	Diff. Insertion Loss	3.0 GHz @ -3 dB
2	Diff. Return Loss	1.0 GHz @ -20 dB
3	NEXT	2.0 GHz @ -50 dB
4	FEXT	2.0 GHz @ -48 dB

MATERIALS and FINISHES

Contact: BeCu C17200 per ASTM B194 (brush alloy 190)
Contact Finish: Gold per ASTM B488 over nickel per SAE AMS-QQ-N-290
Molded Insulator: Glass-filled polyphenylene sulfide (PPS) per MIL-M-24519
Hardware: Stainless steel per ASTM A582/582M, passivated per SAE AMS-2700

NOTE: AirBorn can manufacture special configurations to your exact specifications.

PERFORMANCE

Contact Compression: 0.010 inches per side (nominal) for 0.100" and 0.150" connector heights; 0.015" per side (nominal) for 0.200", 0.250", 0.300" and 0.350" connector heights
Compression Force: 25-40 grams per contact having a 0.010" deflection
35-50 grams per contact having a 0.015" deflection
Contact Wipe: ≈0.007" for 0.100" and 0.150" connector heights
≈0.014" for 0.200", 0.250", 0.300" and 0.350" connector heights
Current Rating: 0.5 amperes
Contact Resistance: 0.025 ohms typical (contact height-dependent)
Operating Temperature: -65° C to +125° C
Insulation Resistance: 5,000 megaohms minimum @ 100 VDC
Durability: 50 connector mating cycles
Dielectric Withstanding: 250 VDC @ sea level, 100 VDC @ altitude

NOTE: Performance values are estimates at this time. Actual values will be determined when final product testing is complete.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

AirBorn:

RZ100-425-115-2000	RZ150-210-115-1000	RZ350-325-115-1000	RZ150-310-115-1000	RZ150-315-115-1000
RZ150-415-115-2000	RZ200-415-115-1000	RZ200-425-115-1000	RZ250-315-115-1000	RZ250-425-115-2000
RZ250-620-115-1000	RZ300-225-115-1000	RZ350-415-115-1000	RZ350-415-115-2000	RZ250-520-115-1000
RZ100-315-115-2000	RZ150-310-115-2000	RZ200-225-115-1000	RZ250-210-115-1000	RZ250-625-115-1000
RZ300-210-115-1000	RZ300-520-115-2000	RZ300-620-115-1000	RZ350-325-115-2000	RZ350-725-115-2000
RZ100-210-115-1000	RZ100-225-115-1000	RZ100-225-115-2000	RZ150-325-115-2000	RZ150-415-115-1000
RZ200-520-115-2000	RZ250-415-115-1000	RZ250-415-115-2000	RZ250-425-115-1000	RZ350-625-115-2000
RZ350-725-115-1000	RZ300-520-115-1000	RZ350-425-115-1000	RZ100-325-115-1000	RZ100-725-115-2000
RZ150-620-115-1000	RZ200-520-115-1000	RZ150-315-115-2000	RZ200-310-115-1000	RZ200-310-115-2000
RZ200-315-115-2000	RZ200-325-115-1000	RZ250-725-115-1000	RZ300-210-115-2000	RZ300-415-115-1000
RZ350-310-115-1000	RZ100-310-115-1000	RZ100-520-115-1000	RZ100-520-115-2000	RZ150-425-115-2000
RZ200-225-115-2000	RZ200-625-115-1000	RZ200-725-115-1000	RZ250-520-115-2000	RZ250-620-115-2000
RZ300-225-115-2000	RZ300-425-115-1000	RZ300-625-115-2000	RZ350-520-115-1000	RZ350-620-115-1000
RZ100-315-115-1000	RZ100-725-115-1000	RZ100-415-115-1000	RZ100-620-115-2000	RZ150-225-115-1000
RZ200-210-115-2000	RZ250-310-115-2000	RZ350-310-115-2000	RZ350-425-115-2000	RZ350-520-115-2000
RZ350-620-115-2000	RZ350-315-115-1000	RZ100-310-115-2000	RZ150-225-115-2000	RZ150-425-115-1000
RZ300-310-115-1000	RZ300-415-115-2000	RZ300-425-115-2000	RZ300-725-115-1000	RZ250-225-115-1000
RZ250-225-115-2000	RZ250-725-115-2000	RZ300-620-115-2000	RZ100-425-115-1000	RZ100-620-115-1000
RZ100-325-115-2000	RZ250-625-115-2000	RZ100-210-115-2000	RZ150-325-115-1000	RZ200-325-115-2000
RZ250-210-115-2000	RZ250-325-115-2000	RZ300-315-115-1000	RZ350-210-115-2000	RZ350-225-115-1000