

AX92322

2-port/4-port GigE PCI Express Card

Features

- 2 or 4 independent Intel® Ethernet Controller i210-AT
- Supports 9.5KB Jumbo Frame and IEEE 1588
- Supports two or four GbE LAN ports
- PCI Express x4 interface
- Operating temperature from 0°C to 70°C



Specifications

GigE	
Host Bus	4-lane Gen2 PCIe interface, compliant with PCI Express base specification, revision 2.0
Channels	2/4 ports
Ethernet Chip	2 or 4 x Intel® Ethernet Controller i210-AT Supports 9.5KB Jumbo Frame and IEEE 1588
Data Transfer Rate	10/100/1000 Mbps

General Specifications

Bus Type	PCI Express x4
Power Consumption	Power from PCIe slot 1.73A@+3.3V max.
Dimensions	125 x 111 mm
I/O Connector	RJ-45
Operating temperature	0°C to +70°C (+32°F to +158°F)
Storage temperature	-20°C to +80°C (-4°F to +176°F)
Operating Humidity	10 - 95% RH, non-condensing
OS	Windows® 7/10 (32/64-bit), Linux
Certification	CE

Ordering Information

AX92322-2GbE (P/N: E392322103)	2-port GigE PCI Express card
AX92322-4GbE (P/N: E392322102)	4-port GigE PCI Express card

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Axiomtek:](#)

[AX92322-4GbE PCI Express Card](#) [AX92322-2GbE PCI Express Card](#) [AX92322-2GbE PClex4 card](#) [AX92322-4GbE PClex4 card](#)