




Elastische Einpresszone 2.5 mm / *compliant pressfit zone 2.5 mm*
 Anforderungsstufe 1 = 500 Steckzyklen / *performance class 1 = 500 mating cycles*
 Bauart 2 / *type 2*
 Fehlende Masse und Angaben nach IEC 60 603-2 / DIN EN 60 603-2
Missing information and dimensions per IEC 60 603-2 / DIN EN 60 603-2
 Schichtaufbau im metallisiertem Loch siehe Zeichnung 164062 Nr.:6
hole design see ERNI-specification 164062 No.:6


Bestückungsplan / *contact layout*



Leiterplatten-Layout / *PCB-drillhole pattern*



- 1) 1.0 +0.09 -0.06 Durchmesser des metallisierten Loches
 1.0 +0.09 -0.06 *Diameter of finished plated- through hole*



Copyright by ERNI GmbH
Proprietary notice pursuant to ISO 10165 to be observed.

Information:				Tolerances		 All Dimensions in mm		Scale		2:1			
All rights reserved. Only for Information. To ensure that this is the latest version of this drawing, please contact one of the ERNI companies before using.				Subject to modification without prior notice. Drawing will not be updated.				Designation Federleiste H15 EE <i>Fem. Connector H15 Pressfit</i>					
				f		01.07.2016				www.ERNI.com		594752	
Index		Date						A3					
								Class		STVH15			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[ERNI Electronics:](#)

[594752](#)