



### Bestückungsplan / contact layout



bestückt / assemble

### Leiterplatten-Lochbild / PCB drillhole pattern



Elastische Einpresszone 2,5 mm / compliant pressfit zone 2,5 mm

Isolierwerkstoff / housing material : LCP GF30

Bauart 2 / type 2

Anforderungsstufe 1 = 500 Steckzyklen / performance class 1 = 500 mating cycles

Fehlende Masse und Angaben gemäß IEC 60 603-2 / DIN EN 60 603-2

Missing information and dimensions according to IEC 60 603-2 / DIN EN 60 603-2



Schichtaufbau im metallisierten Loch siehe Zeichnung 164062/Nr.6

diameter of drilled hole see drawing 164062/Nr.6

- 1)  $\varnothing 1,0 \pm 0,06$  Durchmesser des metallisierten Loches
- $\varnothing 1,0 \pm 0,06$  Diameter of finished plated-through hole

Consider protection memo from DIN 34

Consider protection memo from DIN 34

Information:			Tolerances			Scale	2:1	
					All Dimensions in mm			
All rights reserved. Only for information. To insure that this is the latest version of this drawing, please contact one of the ERNI companies before using.			Subject to modification without prior notice. Drawing will not be updated.		Designation			
					Federleiste H 11 EE <i>Fem. Connector H 11 EE</i>			
c		14.12.2010			www.ERNI.com	424655		I
Index		Date		V:00070330.SZA		STVH11		

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[ERNI Electronics:](#)

[424655](#)