






Stecklänge / mating length




E = early mate, late break / voreilend

S = standard


L = late mate, early break / nacheilend



Bestückungsplan / contact layout



Leiterplatten- Lochbild / PCB drillhole pattern



elastische Einpresszone / compliant pressfit zone

Isolierwerkstoff / housing material : PBT GF 30

Bauart 4 / type 4

Anforderungsstufe 2 = 400 Steckzyklen / performance class 2 = 400 mating cycles

Fehlende Maße und Angaben nach IEC 60 603-2 / DIN EN 60 603-2

Missing information and dimensions per IEC 60 603-2 / DIN EN 60 603-2

1) Ø 1.0 ^{+0.09}/_{-0.06} Durchmesser des metallisierten Loches

Ø 1.0 ^{+0.09}/_{-0.06} Diameter of finished plated-through hole

Bedruckung siehe Zeichnung 294905

marking see drawing 294905

Information:		Tolerances		Scale	2:1
All rights reserved. Only for Information. To ensure that this is the latest version of this drawing, please contact one of the ERNI companies before using.		Subject to modification without prior notice. Drawing will not be updated.		Designation	
-		20.10.2009		Messerleiste C/2 32 EE	
Index		Date		Male Con.C/2 32 pressfit	
-		20.10.2009		384854	
-		20.10.2009		I	
-		20.10.2009		A3	
-		20.10.2009		Class	
-		20.10.2009		STVC/2	

Copyright by ERNI GmbH
Proprietary notice pursuant to ISO 16016 to be observed.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[ERNI Electronics:](#)

[384854](#)