








Bestückungsplan / contact layout

■ bestückt / assembled



Leiterplatten-Lochbild Vorschlag / PCB drillhole pattern proposal



Elastische Einpresszone / *compliant pressfit zone*

Isolierwerkstoff / *housing material*: PBT GF30

Bauart 7 / *type 7*

Anforderungsstufe 1 = 500 Steckzyklen / *performance class 1 = 500 mating cycles*

Fehlende Masse und Angaben nach IEC 60 603-2 / DIN EN 60 603-2

Missing information and dimensions per IEC 60 603-2 / DIN EN 60 603-2

Schichtaufbau im metallisierten Loch siehe Zeichnung 164062 / Nr. 10

diameter of drilled hole see drawing 164062 / No. 10

1) $\varnothing 1.6^{+0.09}_{-0.06}$ Durchmesser des metallisierten Loches

$\varnothing 1.6^{+0.09}_{-0.06}$ *Diameter of finished plated-through hole*

Copyright by ERNI GmbH
Proprietary notice pursuant to BG 1016 to be observed

Information:			Tolerances			Scale	2:1		
All rights reserved. Only for Information. To ensure that this is the latest version of this drawing, please contact one of the ERNI companies before using.			Subject to modification without prior notice. Drawing will not be updated.		Designation				
					Federleiste E 48 EE <i>Fem. Connector E 48 Pressfit</i>				
			a		25.04.2013			www.ERNI.com	
Index		Date					Class	STVE	I A3

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[ERNI Electronics:](#)

[354446](#)