






32 31 30 29 28 27 26 25 24 23 22 21 20 19 18 17 16 15 14 13 12 11 10 9 8 7 6 5 4 3 2 1

bestückt / assembled

Technical drawing of a mechanical part with a wavy top surface. The part has a total length of 88.9 and a width of 5.3 ± 0.1. It features a series of 31 holes with a diameter of 2.8 ± 0.1 and a pitch of 2.54. A feature control frame indicates a positional tolerance of 0.05 for all holes. A dimension of 5.08 is shown from the left edge to the first hole center. A note "1)" points to the hole pattern.

1) $\phi 1.0^{+0.09}_{-0.06}$ Durchmesser des metallisierten Loches
 $\phi 1.0^{+0.09}_{-0.06}$ Diameter of finished plated-through hole

Copyright by ERNI Production GmbH & Co. KG Proprietary notice pursuant to ISO 16016 to be observed.	Information: mit Pressteil <i>with pressed-in cover</i>			Tolerances	 All Dimensions in mm	Scale 2:1	
	All rights reserved. Only for Information. To ensure that this is the latest version of this drawing, please contact one of the ERNI companies before using.			Subject to modification without prior notice. Drawing will not be updated.		Designation Federleiste R 64 EE <i>Fem. Connector R 64 Pressfit</i>	
					www.ERNI.com	284262	
						A3	
b		30.05.2017				Class	STVR
Index		Date					

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[ERNI Electronics:](#)

[284262](#)