









RECOMMENDED PANEL CUTOUT
EMPFOHLENER FRONTPLATTEN-AUSSCHNITT



1:1

WIRING DIAGRAM



Technical specifications

Materials & Finish	Standard applic.	Value
Insulation body	Standard description	PBT 30%
Contact material	Standard description	C5210 (acc.JIS)
Contact finish, mating zone	Thickness of plating	50 µinAu over 50 µin Ni
Shell/shield material	Standard description	C2680 (acc.JIS)
Shell/shield plating	Thickness of plating	50 µin Ni

Packaging	Bag
-----------	-----

Approvals		
UL insulation body	UL 94	V0
UL File No.		E145613
RoHS compliant		Yes

Test Data	Standard applic.	Value
Mechanical properties		
Insertion/withdrawal force	IEC 603-7	max. 20 N
Mechanical operations	IEC 512-5, 9a	min 1.000
Effectiveness of connector coupling device	IEC 512-8, 15f	50 N

Electrical properties		
Creepage / clearance distances		
a)Contact - contact	IEC807-3	0.52 mm
b)Contact - shell	IEC807-3	min. 1.0 mm
Voltage proof (Dielectric Withstand Voltage)		
a)Contact - contact	IEC512-2, 4a	min. 1.000 VDC/VAC
b)Contact - shell/testpanel	IEC512-2, 4a	min. 1.500 VDC/VAC
Current carrying capacity	IEC512-3, 5b	1.5 A @ 25° C
Contact resistance	IEC512-2, 2a	max. 30 mOhm
Insulation resistance	IEC512-2, 3a	min. 500 MOhm

Environmental properties	
Operation temperature	-40 to +70° C

NOTE 1 : RECOMMENDED PANEL THICKNESS 1.6 mm [0.062"]
NOTE 2 : RoHS COMPLIANT

Copyright by ERNI GmbH
Proprietary notice pursuant to ISO 16016 to be observed.

Information:				Tolerances x,x ±0.38 x,xx ±0.25		 All Dimensions in mm [in]		Scale 2:1									
All rights reserved. Only for Information. To ensure that this is the latest version of this drawing, please contact one of the ERNI companies before using.				Subject to modification without prior notice. Drawing will not be updated.				Designation MOD JACK MJC <i>INLINE COUPLER, CAT 5 e</i>									
								www.ERNI.com				133513				1 (1/1)	
				c				29.02.2012				A3					
Index				Date				Class MJ									

Copyright by ERNI GmbH
Proprietary notice pursuant to ISO 16016 to be observed.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[ERNI Electronics:](#)

[133513](#)