




TECHNISCHE SKIZZE / Technical sketch



Ansicht: Steckgesicht Messer; Kontaktbelegung /
View: mating face male; pin assignment
M 2:1



BAUTEILE / FERTIGUNGSHINWEISE Piece parts / Manufacturing notices

- Kabelaufdruck mittels Tintenstrahldrucker entspr. Techn. Skizze
 Cable imprint with ink-jet printer see technical sketch
- Gute Chemikalien- und Ölbeständigkeit (Ölbeständigkeit gilt nicht für den Einsatz mit PVC-Kabel). Beim Einsatz aggressiver Medien ist die Materialbeständigkeit applikationsbezogen zu überprüfen.
 Good chemical and oil resistance (parts with PVC-cable are not resistant). When using aggressive media, material resistance based on application must be checked.

STROMLAUFPLAN / Schematic diagram

1	Litze weiss	flexible conductor white	1
2	Litze braun	flexible conductor brown	2
3	Litze grün	flexible conductor green	3
4	Litze gelb	flexible conductor yellow	4
5	Litze grau	flexible conductor gray	5
6	Litze pink	flexible conductor pink	6
7	Litze blau	flexible conductor blue	7
8	Litze rot	flexible conductor red	8

SPECIFICATIONS Circular Connector

Technical Specifications	Standard applic.	Value	Electrical Data	Standard applic.	Value
Housing:		M12 male, straight, black M12 male, straight black	Rated (nominal) voltage; max.	IEC 61-076-2-101	30 V DC
Pin assignment:		8 pin	Rated current; per contact, max.	IEC 61-076-2-101	2 A
Coding:		A-coding	Rated impulse voltage	IEC 61-076-2-101	0,8 kV
Connection:		Screw locking	Approvals		
		pluggable, screw locking, A/F 13 recommended breakaway torque 0,6 Nm	Protection class		
LED:		-	(mated and locked)	IEC 60529	IP 65/67
Packaging:		1 piece per bag	Pollution degree		3
			Insulation category	IEC 60664-1	I
			RoHS compliant		Yes
Materials & Finish					
Contact material:			Part Marking (cable imprint)		
a) male	Standard description	CuZn39Pb3F50	Part number		required
b) female	Standard description	-	Company Logo		required
Contact finish, mating zone:			Date of manufacturing		required
a) male	Thickness of plating	0,5 µm Au over 2 µm Ni	Jacket material		required
b) female	Thickness of plating	-	Flex. conductor diameter		required
Screw material:		Zinc pressure die casting	Transmission Characteristics IEC 11801		
Screw plating:	Standard description	Ni 4-6 µm			Class D
Cable (additional info see table)					
Jacket color		gray (RAL 7001)			
Conductor cross-section		8 x 0,25 mm ²			
Bending radius min.		15 x jacket diameter			

Artikel-Nr. Part No.	Leitungslänge (A) Cable length (A)	Kupfergewicht Copper weight	Schirm Kabelmantel Jacket material	shield Jacket diameter	Aderisolation Wire isolation	Zul. Temp.-Bereich für Kabel Permissible temp. for cable
464933	500 +50 mm [23.62 +2.4 in]	26,6 g	PUR, shielded	7 mm ±5% [0.263 in ±5%]	PP	-40... +80 °C (permanently installed) -20... +80 °C (movably mounted)
	1.000 +100 mm [39.37 +4 in]					
	1.500 +100 mm [59.05 +4 in]					
	2.000 +100 mm [78.74 +4 in]					
	3.000 + 100 mm [118.11 +4 in]					
Information:		Tolerances		Scale 1:1		
All rights reserved. Only for Information. To ensure that this is the latest version of this drawing, please contact one of the ERNI companies before using.		Subject to modification without prior notice. Drawing will not be updated.		Designation		
		www.ERNI.com		M12 8 pin / M12 m 8 pin Male, A-coding, shielded		
		324227		I A3		
Index		16.08.2012		Class CCCS		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[ERNI Electronics:](#)

[464933](#)