


# Actuator

704.113.0



<https://eao.com/p/704.113.0>

Your product:

---



## 704.113.0 Actuator

### FRONT

|                       |           |
|-----------------------|-----------|
| Front dimension:      | Ø 29 mm   |
| Front form:           | round     |
| Front bezel colour:   | Nature    |
| Front bezel material: | Aluminium |

### MOUNTING

|                |                |
|----------------|----------------|
| Design:        | raised         |
| Mounting type: | Panel mounting |

### ELECTRICAL CHARACTERISTICS

|            |                                                                                           |
|------------|-------------------------------------------------------------------------------------------|
| Standards: | The switches comply with the "Standards for low-voltage switching devices" DIN EN 60947-1 |
|------------|-------------------------------------------------------------------------------------------|

### MECHANICAL CHARACTERISTIC

|                      |                                            |
|----------------------|--------------------------------------------|
| Switching action:    | Maintained (a) - Rest (a) - Maintained (a) |
| Switching positions: | 3 positions                                |
| Switching angle:     | 90° left / 90° right                       |
| Mechanical lifetime: | ≤50 000 cycles of operation                |
| Weight:              | 0.07 kg                                    |

### AMBIENT CONDITION

|                        |                     |
|------------------------|---------------------|
| IP Protection:         | IP65 front side     |
| Operating temperature: | - 40 °C ... + 55 °C |

**Storage temperature:** – 40 °C ... + 85 °C

## CERTIFICATE

**REACH:** REACH compliant

**RoHS:** RoHS compliant


## OTHER

**Short Description:** Actuator, Ø 29 mm, round, Nature, Aluminium, Maintained (a) - Rest (a) - Maintained (a)

**Hints:** The standard lock Ronis 251, Further lock numbers on request, Max. 3 switching elements can be clipped on

**max. number of switching elements:** 3


**Switching positions:**



**Wiring diagrams:**




**Mounting cut-outs:**



A = Screw terminal  
B = Push-in terminal (PIT)  
C = Plug-in terminal 6.3 mm x 0.8 mm  
D = Double plug-in terminal 6.3 mm x 0.8 mm

**Dimension drawings:**



A = Screw terminal

## Where to Buy

| Distributor                                                                         |                               | Quantity in Stock |                                                                                                           |
|-------------------------------------------------------------------------------------|-------------------------------|-------------------|-----------------------------------------------------------------------------------------------------------|
|    | Distrelec                     | 25 in stock       | <a href="#">Buy</a>    |
|   | Digi-Key                      | 19 in stock       | <a href="#">Buy</a>   |
|  | Transfer Multisort Elektronik | 8 in stock        | <a href="#">Buy</a>  |
|  | element14 Singapore           | 3 in stock        | <a href="#">Buy</a>  |
|  | Farnell element14 UK          | 3 in stock        | <a href="#">Buy</a>  |

[Show more](#) 

Powered by oemsecrets.com

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[EAO:](#)

[704.113.0](#)