



# U60 LON<sup>®</sup> FT USB Module



U60 module connects LON devices via USB

## Product Description

The U60 FT USB network interface module enables a controller or computer to communicate with LON and IzoT<sup>®</sup> networks via USB. The compact boards include network and USB pin headers for simple integration into any controller or device.

The U60 is an interface to LON/IP-FT and LON-FT and is compatible with OpenLDV 5 and with hosts implementing the LON/IP stack which provides source code for LON/IP and LON compatible protocol stacks.

The interface facilitates communication to everyday devices like pumps, motors, valves, sensors, actuators and lights for process control, building automation, energy management, transportation systems control and telecommunications equipment management.

Tx and Rx signals provide an indication of LON packet transmission and reception and a service signal communicates device status to the host via the USB interface enabling the host controller to provide status indicators. Optional on-board Tx, Rx and service LED indicators are available.

## Features and Benefits

- USB interface for LON FT networks for any edge server, gateway, controller, or device, including Adesto's SmartServer<sup>™</sup> IoT
- Compatible with IzoT Net Server, OpenLNS<sup>®</sup> Server, LNS<sup>®</sup> Server and OpenLDV applications
- Works with IzoT Net and LNS compatible applications such as the IzoT Commissioning Tool and LonMaker Integration Tool
- Compatible with SmartServer IoT
- Compact 72mm x29mm (2.8" x 1.1") board-level form factor with 2.54mm center pin headers for simple integration
- Powered by 3.3VDC input
- Source code available as download for a Linux-compatible driver

# PRODUCT SPECIFICATIONS

## Hardware and electrical specifications

Processor:	Adesto FT 6050 Smart Transceiver
LON connector:	Network pin header
USB 2.0 pin header:	Certified USB 2.0 compatible, compatible with USB 1.1 and high-speed USB systems, peripherals and cables
Indicators (Model 65430R only):	LON Tx/Rx LEDs, Service LED
Input voltage:	3.3VDC
Input current	110mA maximum USB power
Temperature range:	-40°C to +70°C
Humidity:	10-90% RH @ 50°C
Dimensions:	72mm x 29mm x 13mm (2.8" x 1.1" x 0.5")

## Software Platform

Interface: LON/IP-FT and LON-FT (TP/FT-10) with a Layer 2 or Layer 5 interface

Drivers (free downloads from website):

- Linux source code for a U60 network driver
- OpenLDV 5, or newer, driver for Windows

## Safety, compliance and warranty

Agency approvals: MET 60950, TUV EN 60950, CE, C-Tick

EMC: FCC Part 15 Class A, EN55022 Class A, EN55024, CISPR 24 Class A


Warranty: 1 year limited warranty

## BOARD LAYOUT

JP1 Pin Assignment	
Pin #	Function
1	Do not connect
2	USB -
3	USB +
4	Ground

JP3 Pin Assignment	
Pin #	Function
1	+3.3VDC in
2	Tx LED out
3	Rx LED out
4	Service
5	Ground
6	Reset

JP5 Pin Assignment	
Pin #	Function
1	FT Network B
2	FT Network A
3	Do not connect
4	Do not connect



Host Interface: The interface to the host is provided via the USB interface. The host selects whether the interface is a Layer 2 or Layer 5 interface.

Model #	Product Name	Product Description
65430R	U60 FT Network Interface Module with LEDs	Board-level USB interface to LON/IP-FT and LON-FT free topology twisted pair networks with Tx, Rx and service indicators
65440R	U60 FT Network Interface Module	Board-level USB interface to LON/IP-FT and LON-FT free topology twisted pair networks

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adesto Technologies:](#)

[65440R](#) [65430R](#)