

## Pushbutton Ø 19 mm silver contact

82-5571.1000



<https://eao.com/p/82-5571.1000>

Your product:

---



82-5571.1000

Pushbutton Ø 19 mm silver contact

#### FRONT

**Front dimension:** Ø 22 mm

**Front form:** round

**Front bezel material:** Aluminium

**Front bezel shape:** flush

#### MOUNTING

**Mounting cut-out:** Ø 19 mm

**Mounting type:** Panel mounting

#### OPERATING-/INDICATION PART

**Lens colour:** Nature

**Lens material:** Aluminium

**Lens illumination:** non illuminative

**Lens shape:** convex

**Lens optics:** opaque

#### ELECTRICAL CHARACTERISTICS

**Contacts:** 1 C

**Switching voltage and switching current:**

according to IEC 60947-5-1 (Silver contacts)

Service categorie AC-15

Voltage

24 VAC

35 VAC

110 VAC

220 VAC

Current

1 A

1 A (M12 version)

1 A

0.5 A

Switch rating DC service categorie DC-13 (Silver contacts)

Voltage

24 VDC

35 VDC

110 VDC

220 VDC

Current

0.7 A

0.5 A (M12 version)

0.2 A

0.1 A

according to UL 508 (Silver contacts)

$\cos\phi$  0,75 ... 0,8

Voltage

120 VAC

240 VAC

24 VAC

Current

5 A

3 A

1 A

**Rated Operational Voltage  $U_e$ :** 250 VAC

**Rated insulation voltage  $U_i$ :** 250 V

**Electrical lifetime:** 50 000 cycles of operation

**Electric strength:** 1500 VAC, 50 Hz 1 minute between life terminals and ground

**Pollution degree:** 2, according to EN IEC 60947-1

**Thermal current  $I_{th}$ :** 5 A

## MECHANICAL CHARACTERISTIC

**Terminal:** Soldering terminal, 2.8 x 0.5 mm

**Contact material:** Silver

**Switching action:** Momentary

**Switching system:** Snap-action switching element

**Mechanical lifetime:** 1 Mio. cycles of operation

**Operating force:** 4 N ... 7 N

**Operating Travel:** ca. 3 mm

**Tightening torque:** 0.5 ... 0.6 Nm

**Weight:** 0.019 kg

## AMBIENT CONDITION

**IP front protection:** IP65, IP67

**Operating temperature:** - 30 °C ... + 70 °C

**Storage temperature:**

– 40 °C ... + 80 °C

**Shock resistance:**

Max. 500 m / s<sup>2</sup> as per IEC 60068-2-27

**Vibration resistance:**

10 ... 500 Hz, amplitude 1.5 mm p-p according to IEC 60068-2-6

**Climate resistance:**

Damp heat, 21 days according to IEC 60512-11

**CERTIFICATE**

**Approbations:**

CB, CCC, C UL, UL

**Conformities:**

CE, 2011 / 65 / EC (RoHS), 2014 / 35 / EU (LVD)

**REACH:**

REACH compliant

**RoHS:**


RoHS compliant

**OTHER**


**Short Description:**

Pushbutton Ø 19 mm silver contact, Momentary, 1 C, Soldering terminal, 2.8 x 0.5 mm, round, Aluminium, Nature


**Wiring diagrams:**




**Component layouts:**



**Mounting cut-outs:**













**Dimension drawings:**



A = Solder terminal  
B = Screw terminal

Where to Buy

Distributor		Quantity in Stock		
	RS UK	37 in stock	Buy	
	Farnell UK	22 in stock	Buy	
	element14 Singapore	21 in stock	Buy	
	TME	12 in stock	Buy	
	Mouser Electronics	8 in stock	Buy	

Show more +

Powered by oemsecrets.com

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[EAO:](#)

[82-5571.1000](#)