


AD3506 SERIES



External Dimensions



Frame:Plastic(UL:94V-0)
Impeller:Plastic(UL:94V-0)
Lead wire:UL1571AWG28

Specifications(Nominal)


*:Noise is measured at the distance of one (1) meter from the axis of intake.

Bearing type: ◎=Ball ※=Sleeve ●=Hypro bearing

Frame size (mm)	Model No.	Bearing System Type	Rated Voltage (VDC)	Current (A)	Power (W)	Rated Speed (rpm)	Maximum AirFlow (CMM) (CFM)	Maximum Pressure (InAq) (mmAq)	*Noise Level (dB/A)	Weight (g)
35x35x06	AD3505LX-K70(TX)	●	5	0.070	0.350	6500	0.099 3.500	0.080 2.032	26.0	7.0
	AD3505MX-K70(TX)	●	5	0.100	0.500	8000	0.118 4.200	0.100 2.540	33.0	
	AD3512LX-K70(TX)	●	12	0.060	0.720	6500	0.099 3.500	0.080 2.032	26.0	
	AD3512MX-K70(TX)	●	12	0.070	0.840	8000	0.118 4.200	0.100 2.540	33.0	

Specifications subject to change without notice.

The specification for bearing type is for reference only , for more bearing types information, please contact with your ADDA sales representative, thanks!!
(網頁上呈現產品軸承資訊均以參考為主，若需其他產品資訊請聯絡您在ADDA的業務代表，謝謝！！)



*Motor protective circuit and third lead wire functions

0	1	2	3	4	6	7	8	9	A	B
✓					✓					

*Safety approvals

UL	UL	SP	CE	CE
			✓	✓

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[ADDA:](#)

[AD3505MB-K70\(TX\)](#) [AD3505LB-K70\(TX\)](#) [AD3512LB-K70\(TX\)](#) [AD3512MB-K70\(TX\)](#)