


AD8025GP SERIES



External Dimensions



Frame: Plastic (UL: 94V-0)
 Impeller: Plastic (UL: 94V-0)
 Bearing: Ball, Sleeve, Hypro bearing
 Lead wire: UL 1007 AWG24
 VOLTAGE AVAILABLE: 12V


Specifications(Nominal)

*Noise is measured at the distance of one (1) meter from the axis of intake.

Bearing type: ⊗=Ball ⊕=Sleeve ○=1B1S ●=Hypro bearing

Frame size (mm)	Model No.	Bearing System Type	Rated Voltage (VDC)	Current (A)	Power (W)	Rated Speed (rpm)	Maximum AirFlow (CMM)	Maximum AirFlow (CFM)	Maximum Pressure (InAq)	Maximum Pressure (mmAq)	*Noise Level (dB/A)	Weight (g)
80x80x25	AD0812UB-A71GP	⊗ ⊕ ●	12	0.27	3.24	4000	1.585	56.00	0.250	6.35	43.5	95.0
	AD0812XB-A71GP	⊗	12	0.38	4.56	4500	1.896	67.00	0.300	7.62	46.0	
	AD0812VB-A71GP	⊗	12	0.53	6.36	5000	2.038	72.00	0.360	9.14	49.0	
	AD0824HB-A71GP	⊗	24	0.10	2.40	3500	1.415	50.00	0.190	4.83	38.5	
	AD0824UB-A71GP	⊗	24	0.13	3.12	4000	1.585	56.00	0.250	6.35	43.5	
	AD0824XB-A71GP	⊗	24	0.17	4.08	4500	1.896	67.00	0.300	7.62	46.0	
	AD0824VB-A71GP	⊗	24	0.26	6.24	5000	2.038	72.00	0.360	9.14	49.0	

Specifications subject to change without notice.



*Motor protective circuit and third lead wire functions

0	1	2	3	4	6	7	8	9	A	B
	✓	✓	✓					✓		✓

*Safety approvals

UL	cUL	SP®	RoHS	CE
✓	✓		✓	✓

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[ADDA:](#)

[AD0812VB-A71GP](#) [AD0824UX-A73GL-LF](#)