

# SPECIFICATION FOR APPROVAL

TO : \_\_\_\_\_

REF. No. \_\_\_\_\_

CUSTOMER APPROVED	APPROVED DATE	CHECKED DATE	PREPARED DATE
	研發處 2015.07.29 簡文榮	研發處 2015.07.29 徐俊祺	研發處 2015.07.29 盧簾清

MODEL No. \_\_\_\_\_ AD0412LB-C72GP \_\_\_\_\_ P.S. \_\_\_\_\_ (P)

DESCRIPTION: \_\_\_\_\_ DC FAN (RoHS) \_\_\_\_\_ REV. \_\_\_\_\_ B \_\_\_\_\_

ID No. \_\_\_\_\_

THIS OFFER IS MADE ACCORDING TO YOUR CURRENT INQUIRY.  
UNLESS OTHERWISE REVISED, THIS SPECIFICATION WILL BE FINAL FOR  
ALL FUTURE PRODUCTION OF ORDERS FROM YOUR RESPECTED COMPANY

KINDLY STUDY IN DETAILS AND RETURN TO US THE DUPLICATE DULY  
SIGNED AS YOUR CONFIRMATION OF SAME.



**ADDA CORPORATION**

# DATA - SHEET

Engineering

Printed On: 15/07/29

## BRUSHLESS AXIAL COOLING FANS

Customer	:				Ref: (RoHS)
Adda Model No	:	AD0412LB-C72GP	P.S:	(P)	
Samples attached	:	Piece(s),			
Safety Approval	:	UL,CUL,TUV,CE	TUV:EN 60950-1:2006+A11+A1+A12 UL:UL507 CE:EN 61000-6-1:2007 EN 61000-6-3:2007		
<u>Specifications</u>					
ITEM	SPECIFICATION / CONDITION				
DIMENSIONS	:	40x40x20	mm		
BEARING TYPE	:	BALL			
RATED VOLTAGE	:	12.0	VDC		
OPERATING VOLTAGE RANGE	:	10.8	VDC	—	13.2 VDC
START—UP VOLTAGE	:	9.0	VDC	, NORMAL	
REAL CURRENT	:	0.07	Amp		
REAL POWER	:	0.84	Watt		
RATED CURRENT	:	0.10	Amp	+	10 %MAX
RATED POWER	:	1.20	Watt		
RATED SPEED	:	5000	RPM	±	10 %
(IN FREE AIR AT RATED VOLTAGE)					
AIR FLOW	:	5.893	CFM	(min.:	5.303 CFM)
AIR FLOW	:	0.166	CMM	(min.:	0.149 CMM)
(IN FREE AIR AT RATED VOLTAGE)					
STATIC AIR PRESSURE	:	0.132	Inch H <sub>2</sub> O	(min.:	0.106 Inch H <sub>2</sub> O)
STATIC AIR PRESSURE	:	3.352	mm H <sub>2</sub> O	(min.:	2.715 mm H <sub>2</sub> O)
(IN FREE AIR AT RATED VOLTAGE)					
NOISE LEVEL	:	21.3	dB (A)	(max.:	25.3 dB(A))
MOTOR PROTECTION	:	BY	IC		
POLARITY PROTECTION	:	NO			
CONNECTION LEAD TYPE	:	WIRE, AWG#	26		
LIFE EXPECTANCY	:	70000	Hours	at	40°C / 65% RH
NET WEIGHT	:	28	Gram.		
PACKING	:	500	pcs.	Per Export Carton.	
Unless otherwise stated, the relative humidity is 65%, and the temperature is 25°C for the standard testing.					
Should you have any doubt, please refer to the environmental conditions specified in the acknowledgement document.					
ADDA CORPORATION		Model No.: AD0412LB-C72GP		P.S: (P)	
				Page 1/6	



## SPECIFICATION

### 1 · 0 SCOPE

- 1.1 If the information or other related document is inconsistent with this acknowledgement document, please refer to the acknowledge document.
- 1.2 This documentation defines the mechanical & electrical characteristics of DC brushless fans.
- 1.3 The specification of this product is described in details in the acknowledgement document. No guarantee is given to our product under the use of over specifications.
- 1.4 For any change or amendment to the specifications, such change will be noticed in writing beforehand.
- 1.5 If the product is used on the MIS system, please specify the specification in the purchase order.

### 2 · 0 MATERIAL

- 2 · 1 Frame : UL94V-0 Glass Filled polyester (P.B.T)
- 2 · 2 Fan Blade : UL94V-0 Glass Filled polyester (P.B.T)
- 2 · 3 Bearing Sys. : ☐ Sleeve, oil impregnated.  
☒ Two Ball Bearing  
☐ One Ball one Sleeve  
☐ Hypro Bearing  
☐ FDB Bearing
- 2 · 4 RoHS : ☒ YES  
HF : ☐ YES


### 3 · 0 DIMENSIONS & CONSTRUCTION

All dimensions, Direction of rotation and air flow were specified as per drawing attached.

### 4 · 0 CHARACTERISTICS & DEFINITION

- 4 · 1 All rated characteristics were specified as per data sheet enclosed.
- 4 · 2 Rated Current : Rated Current shall be measured after 3 minutes of continuous rotation at rated voltage.
- 4 · 3 Rated Speed : Rated Speed shall be measured after 3 minutes of continuous rotation at rated voltage.
- 4 · 4 Start Voltage : The voltage which is able to start the fan to operate by suddenly switching ' ON ' .
- 4 · 5 Input Power : Input Power shall be measured after 3 minutes of continuous rotation at rated voltage.
- 4 · 6 Locked Rotor Current : Locked current shall be measured within one minute of rotor locked, after 3 minutes of continuous rotation at rated voltage in clean air.
- 4 · 7 Air Flow & Static Pressure : The air flow data and static pressures should be determined in accordance with AMCA-210 standard in a doublechamber testing with intake – side measurement.
- 4 · 8 Noise Level : The measurement of noise level is carried out with reference to CNS8753 in an anechoic chamber with the microphone positioned 1 meter from the air intake. Testing fan shall be hung in clean air .

#### NOISE LEVEL MEASUREMENT



## SPECIFICATION

### 5.0 MECHANICAL INSPECTION

#### 5.1 Rotation Direction

Counterclockwise when look into impeller side.

#### 5.2 Protection

All fans have integrated protection against locked rotor condition so that there will be no damage to winding or any electronic component.

Restarting is automatic as soon as any constraint to rotation has been released.

As fan placed at dead angle position, and the switch was changed from off to on. Restarting was automatic normal as soon as and proved that this fan is good fan.

#### 5.3 Locked Rotor Protection

No damage shall be found after 72 hours continuously at condition of rotation locked.

Restarting is automatic as soon as constraint to running has been released.

#### 5.4 Avoid the damage, check the correct voltage and proper polarity before connecting with power.

#### 5.5 Free Drop Shock

In minimum package condition, the fan should withstand drops on any three faces from a height of 30cm onto a wood board of 10mm thick.

#### 5.6 Please do not stick a grease and/or an oil to the fan housing or blade which may have a harmful influence by a chemical reaction at high humidity.

#### 5.7 If the fan is reinstalled, please pay special attention to the noise due to the vibration (or resonance).

#### 5.8 During the testing of the fan, please make sure the finger guard is used for safety.

### 6.0 ELECTRICAL INSPECTION

#### 6.1 Insulation Resistance

Not less than 10M ohm between housing and positive end of lead wire (red) at 500V DC.

#### 6.2 Dielectric Strength

No damage should be found at 500 VAC for 60 seconds, measured with 1mA trip current between housing and positive end of lead wire.

#### 6.3 Life Expectancy

The continuous duty life at given temperature after which, 90% of testing units shall still be running.

#### 6.4 While the fan is running, do not intentionally lock the fan for a long time since the overheating of the motor produced by the long-time locking will damage the fan.

### 7.0 ENVIRONMENTAL

#### 7.1 Improper use such as disassembling the fan, being covered with dust, or dipping the fan in water that results in defects is not covered in the warranty. Do not use the fan in the environment with corrosive air or liquid.

#### 7.2 Operating Temperature / Humidity

-10°C to +70°C at humidity 65%+/-20% RH.

#### 7.3 Storage Temperature

All function shall be normal after 500 hours storage at -40°C to +70 °C with a 24 hour recovery period at room temperature.

#### 7.4 Humidity

After 96 hours, 95% RH, 40+/-2°C per MIL-STD-202F, method 103B humidity test, the measured data on insulation resistance and dielectric strength shall meet the specification.

#### 7.5 Do not place or store the fan in the environment with high/low temperature/humidity. Do not store the fan for over 6 months; even if the fan is stored in room temperature for over 6 months, the fan may have the electric current leakage.




SPECIFICATION

8.0 REMARKS

- 8.1 Material and construction are subject to change without advance notice. The changes should be within specification.
- 8.2 All fans shall meet the quality inspection under sampling plan MIL-STD-105E as follow:

Critical	0.25%
Major	1.00%
Minor	2.50%

9.0 OUTLINE STYLING & DIMENSIONS



LEAD WIRES : UL 1007, AWG26 , L = 295 +/- 10 mm  
Red = positive ; Black = negative.  
Yellow = RD

10.0 Notes:

- 10.1 Please do not touch and push Fan Blade with fingers or others, fan blade and ball bearings may be damaged and it causes noise defect.
- 10.2 Do not carry the fan by its lead wires.
- 10.3 If the fan does not have the polarity protection function, the connection of the colored wires should be red + red, and black + black, or else the fan will be damaged in no time.
- 10.4 For the models without reverse connection of polarity protection, please do not connect the lead wire in reverse
- 10.5 Please don't install this fan in series with 2x voltage inputs. For example, if a single fan rated at 12V, then don't install two of them in series with 24V input.
- 10.6. Every specific fan is designed for its certain application (project). Therefore, if you want to use this fan in other application (project), please inform ADDA first so that we can confirm whether there is any issue which might be incurred from the reason of this different application (project) or not.
- 10.7 The "Life Expectancy" of this fan has not been evaluated for use in combination with any end application. Therefore, the Life Expectancy in the Test Reports (L10 and MTTF Report) that relate to this fan is for reference only and shall not construe any kind of warranty of ADDA to the life of any specific fan, either expressed or implied.
- 10.8 The period of product warranty, unless otherwise agreed by ADDA in written, shall be 12 months starting from the date of production.






Output of locked signal

\*Output type.....Open collector type

\*Electrical design suggestion:

(External signal function design is decided by customer)



\*Transistor Q1 at "ON" position

Collector current..... $I_C=5\text{mA Max}$


Saturation Voltage..... $V_{OL}=1.0\text{V Max}$

(Between Collector and Emitter at  $I_C=5\text{mA}$ )


\*Transistor Q1 at "OFF" position

Release Voltage..... $V_{OH}=15\text{V Max}$

\*Output waveform



## Fan Performance Curve



## Zertifikat

## Certificate



Zertifikat Nr. Certificate No.  
R 50068602

Blatt Page  
0065

Ihr Zeichen Client Reference  
8382500006

Unser Zeichen Our Reference  
ZTW2-HCY- 11005418 051

Ausstellungsdatum  
02.01.2008

Date of Issue  
(day/month/year)

## Genehmigungsinhaber License Holder

Adda Corporation  
6, East Section, Industry 6 Road  
Pingtung City 900  
Taiwan, R.O.C.

## Fertigungsstätte Manufacturing Plant

Adda Corporation  
6, East Section, Industry 6 Road  
Pingtung City 900  
Taiwan, R.O.C.

## Prüfzeichen Test Mark

Geprüft nach Tested acc. to  
EN 60950-1:2001+A11



Zertifiziertes Produkt (Geräteidentifikation)  
Certified Product (Product Identification)

Lizenzentgelte - Einheit  
License Fee - Unit

Ventilator (DC Fan)

Wie Blatt (As Page) 01

Ergänzung (Addition)

Bezeichnung (Type Designation) : a) AD0412E1B-C7E2GP  
b) AD0424J1J2-G7J3  
c) AD0812K1K2-D7B  
d) AD1212UN1-Y5N2  
e) AD12Z1Z2Z3-F5Z4  
f) AD0912MB-U7BGL  
g) ADL312HB-X31

E1 steht für (stands for) : U, H, M oder (or) L

E2 steht für (stands for) : 1, 2 oder (or) 3

J1 steht für (stands for) : H, M oder (or) L

J2 steht für (stands for) : B, S oder (or) X

J3 steht für (stands for) : 1, 2 oder (or) 3

1  
1  
1  
1  
1  
1  
1  
1  
1  
1  
1

Fortsetzung auf Blatt (Continued on Page) 066



12

## ANLAGE (Appendix) 1.48

Dem Zertifikat liegt unsere Prüf- und Zertifizierungsordnung zugrunde.  
Das Produkt entspricht den o.g. Anforderungen, die Herstellung wird überwacht.  
This certificate is based on our Testing and Certification Regulation. The product fulfills above mentioned requirements, the production is subject to surveillance.

Zertifizierungsstelle



TÜV Rheinland Product Safety GmbH, Am Grauen Stein, D-51105 Köln  
Tel.: (+49/221) 8 06 - 13 71 e-mail: cert-validity@de.tuv.com  
Fax: (+49/221) 8 06 - 39 35 http://www.tuv.com/safety

Dipl.-Ing. B. Scheirer

# Zertifikat

# Certificate



Zertifikat Nr. Certificate No.  
R 50068602

Blatt Page  
0066

Ihr Zeichen Client Reference  
8382500006

Unser Zeichen Our Reference  
ZTW2-HCY- 11005418 051

Ausstellungsdatum  
02.01.2008


Date of Issue  
(day/month/year)

Genehmigungsinhaber License Holder  
Adda Corporation  
6, East Section, Industry 6 Road  
Pingtung City 900  
Taiwan, R.O.C.

Fertigungsstätte Manufacturing Plant  
Adda Corporation  
6, East Section, Industry 6 Road  
Pingtung City 900  
Taiwan, R.O.C.

## Prüfzeichen Test Mark

Geprüft nach Tested acc. to  
EN 60950-1:2001+A11



Zertifiziertes Produkt (Geräteidentifikation)  
Certified Product (Product Identification)


Lizenzentgelte - Einheit  
License Fee - Unit

Ventilator (DC Fan)

Wie Blatt (As Page) 01  
Fortsetzung (Continuation)

K1 steht für (stands for) : V, X, U, H, M, L oder (or) D	1
K2 steht für (stands for) : B, S oder (or) X	1
N1 steht für (stands for) : B, S oder (or) X	1
N2 steht für (stands for) : 1, 2 oder (or) 3	1
Z1 steht für (stands for) : 12 oder (or) 24	1
Z2 steht für (stands for) : H, M, L oder (or) D	1
Z3 steht für (stands for) : B, S oder (or) X	1
Z4 steht für (stands for) : 0 oder (or) 6	1

Nennspannung : siehe Anlage  
(Rated Voltage) (see Appendix)  
Nennstrom : siehe Anlage  
(Rated Current) (see Appendix)



ANLAGE (Appendix) : 1.48

Dem Zertifikat liegt unsere Prüf- und Zertifizierungsordnung zugrunde.  
Das Produkt entspricht den o.g. Anforderungen, die Herstellung wird überwacht.  
This certificate is based on our Testing and Certification Regulation. The product fulfills above mentioned requirements, the production is subject to surveillance.

Zertifizierungsstelle



TÜV Rheinland Product Safety GmbH, Am Grauen Stein, D-51105 Köln  
Tel.: (+49/221) 8 06 - 13 71 e-mail: cert-validity@de.tuv.com  
Fax: (+49/221) 8 06 - 39 35 http://www.tuv.com/safety

Dipl.-Ing. B. Scheirer

# Zertifikat

# Certificate



Zertifikat Nr. Certificate No.  
R 50068602

Blatt Page  
0110

Ihr Zeichen Client Reference  
12060494/ST160712

Unser Zeichen Our Reference  
ZTW1-YML- 11005418 091

Ausstellungsdatum  
16.08.2012

Date of Issue  
(day/mo/yr)


## Genehmigungsinhaber License Holder

Adda Corporation  
6, East Section, Industry 6 Road  
Pingtung City 900  
Taiwan, R.O.C.

## Fertigungsstätte Manufacturing Plant

Adda Corporation  
6, East Section, Industry 6 Road  
Pingtung City 900  
Taiwan, R.O.C.

## Prüfzeichen Test Mark



## Geprüft nach Tested acc. to

EN 60950-1:2006+A11+A1+A12

Zertifiziertes Produkt (Geräteidentifikation)  
Certified Product (Product Identification)

Lizenzentgelte - Einheit  
License Fee - Unit

Ventilator (DC Fan)

wie Blatt (as page) 01

Änderung  
(Change)

Prüfgrundlage : siehe oben  
(Test Requirement) (see above)




ANLAGE (Appendix): 1 - 1.79

Dem Zertifikat liegt unsere Prüf- und Zertifizierungsordnung zugrunde und es bestätigt die Konformität des Produktes mit den oben genannten Standards und Prüfgrundlagen. Zusätzliche Anforderungen in Ländern, in denen das Produkt in Verkehr gebracht werden soll, müssen zusätzlich betrachtet werden. Die Herstellung des zertifizierten Produktes wird überwacht.  
This certificate is based on our Testing and Certification Regulation and states the conformity of the product with the standards and testing requirements as indicated above. Any additional requirements in countries where the product is going to be marketed have to be considered additionally. The manufacturing of the certified product is subject to surveillance.

TÜV Rheinland LGA Products GmbH - Tillystraße 2 - 90431 Nürnberg  
Tel.: (+49/221)8 06 - 13 71 e-mail: cert-validity@de.tuv.com  
Fax: (+49/221)8 06 - 39 35 http://www.tuv.com/safety

Zertifizierungsstelle



Dipl.-Ing. (FH) A. Klinker

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[ADDA:](#)

[AD0412LB-C72GP\(P\)](#)