Subminiature Toggle Switches

Features/Benefits

- Compact size—small footprint
- Single and double pole models
- PC and panel mount options available
- RoHS compliant models available

Typical Applications

- Hand-held telecommunications
- Instrumentation
- Medical equipment



Specifications

CONTACT RATING: B contact material: 0.4 VA max. @ 20 V AC or DC max. Q contact material (TX01 models): 3 AMPS @ 120 V AC or 28 V DC. All other models: 2 AMPS @ 120 V AC or 28 V DC. See page F-42 for additional ratings.

ELECTRICAL LIFE: TX01 models: 60,000 make-and-break cycles at full load. All other models: 30,000 cycles.

CONTACT RESISTANCE: Below 20 m Ω typ. initial @

2-4 V DC, 100 mA, for both silver and gold plated contacts.

INSULATION RESISTANCE: $10^9 \Omega$ min.

DIELECTRIC STRENGTH: 1000 Vrms min. @ sea level.

OPERATING TEMPERATURE: -30°C to 85°C.

SOLDERABILITY: Per MIL-STD-202F method 208D, or EIA RS-186E method 9 (1 hour steam aging).

NOTE: Any models supplied with P, R, Q, B or G contact material are RoHS compliant and compatible.

NOTE: Specifications and materials listed above are for switches with standard options. For information on specific and custom switches, consult Customer Service Center.

Materials

CASE: Glass filled nylon 6/6, flame retardant, heat stabilized or diallyl phthalate (DAP), (UL 94V-0) or glass filled nylon 4/6, flame retardant, heat stabilized.

ACTUATOR: Brass, chrome plated. BUSHING: Brass, nickel plated. HOUSING: Stainless steel.

SWITCH SUPPORT: Brass, matte-tin plated.

END CONTACTS: B contact material: Copper alloy, with gold plate over nickel plate. Q contact material: Coin silver, silver plated. See above for additional contact materials.


CENTER CONTACTS & TERMINALS: B contact material: Copper alloy, with gold plate over nickel plate. Q contact material: Copper alloy, silver plated. See page F-42 for additional contact materials.

TERMINAL SEAL: Epoxy.

HARDWARE: Nut & Locking Ring: Brass, nickel plated. Lockwasher: Steel, nickel plated. Additional hardware available separately, see Section N.

Build-A-Switch

To order, simply select desired option from each category and place in the appropriate box. Available options are shown and described on pages F-38 thru F-42. For additional options not shown in catalog, consult Customer Service Center. All models have epoxy terminal seal and are compatible with all "bottom-wash" PCB cleaning methods.







Dimensions are shown: Inches (mm) Specifications and dimensions subject to change

Subminiature Toggle Switches

		SWITCH FUNCTION		CONNECTED TERMINALS					
		POS. 1	POS. 2	POS. 3	POS. 1	POS. 2	POS. 3		
		7	1	1	7	1	4		
NO. POLES	MODEL NO.	C&K marking on opposite side			C&K marking on opposite side				SCHEMATIC
	T101	ON	NONE	ON	2-3	N/A	2-1		
SP	T103	ON	OFF	ON					• 2 (00MI)
	T105	мом.	OFF	мом.	2-3	OPEN	2-1		2 (COMM) 1 • 3
	T107	ON	OFF	мом.					
	T108	ON	NONE	мом.	2-3	NA	2-1	SPDT	
	T102	OFF	NONE	ON	OPEN	N/A	3-1	SPST	1 • 3

SPDT







Part number shown: T101SHZQE

		SWITCH FUNCTION			CONNECTED TERMINALS			
		POS. 1	POS. 2	POS. 3	POS. 1	POS. 2	POS. 3	
		7	1	1	7	1	_ ▲	
NO. POLES	MODEL NO.	C&K marking on opposite side			C&K marking on opposite side			SCHEMATIC
DP	T201	ON	NONE	ON	2-3,5-6	N/A	2-1,5-4	
	T203	ON	OFF	ON	2-3,5-6	OPEN	2-1,5-4	1 • • 2 <u>(COMM)</u> 5 • 6
	T205	мом.	OFF	мом.				
	T208	ON	NONE	мом.	2-3,5-6	N/A	2-1,5-4	
	T211*	ON	ON	ON.	2-3,5-6	2-3,5-4	2-1,5-4	DPDT

DPDT





Terminal Nos. For Reference Only

Part number shown: T201SHZQE

MOM. = Momentary

Toggle 1

* Wiring for 3-way switch refer to page N-10

All models with all options when ordered with G, L, R or Q contact material.



Dimensions are shown: Inches (mm) Specifications and dimensions subject to change




ACTUATOR ---


.210" HIGH


S .370" HIGH


.220" HIGH (with "T" bushing)

\$1 .410" HIGH (with "T" bushing)










Standard with A, AV or V3 terminations.


Standard with Z, C or W terminations.


.290" HIGH

L1 .640" HIGH

P3 ANTI-ROTATION, FLATTED, .450" HIGH








Available with T & T9 bushings only. Dress nut part number 709901201 supplied standard with threaded bushing.

- ¹ Actuator shown with standard H bushing. Subtract .040 (1,02) for TD and D9 bushings, subtract .090 (2,29) for T, T9, TK, K9 & CF bushings.
- ² Actuators shown with T, T9, TK & CF bushings, add .050 (1,27) for TD and D9 bushings, add .090 (2,29) for H, H9, Y & Y9 bushings.

All actuators have chrome finish (except K).

K LOCKING LEVER



Not available with CF bushing option.

Bushing option code not required. Not available with TX05 & TX07 models.

Locking Positions







-01 & -02 Models 2 Position lock

-03 & -11 Mode 3 Position lock

-08 Models 1 Position lock


K actuators have natural aluminum finish.

Keyway on right side. To prevent accidental actuation, toggles must be lifted before being actuated. When released, toggles again lock in place. Overtightening mounting nut may cause actuator to bind.

BUSHING -


H .220" HIGH THREADED, FLAT


H9 .220" HIGH UNTHREADED, FLAT




H standard with C, W & Z terminations. (0) H9 standard with A, AV & V3 terminations.

Y .220" HIGH THREADED, KEYWAY








T .310" HIGH THREADED, FLAT

T9 .310" HIGH UNTHREADED, FLAT






Dimensions are shown: Inches (mm) Specifications and dimensions subject to change




TK .310" HIGH THREADED, KEYWAY




TD .260" HIGH THREADED, KEYWAY

D9 .260" HIGH UNTHREADED, KEYWAY




CF SPLASHPROOF, .310" HIGH THREADED, FLAT



Internal o-ring actuator seal and external bushing seal washer standard.


Not available with K locking lever option.




TERMINATIONS





Z SOLDER LUG



C PC THRU-HOLE








T102 – omit center hole.


WIRE WRAP


Not available with P or R contact materials.





.020 THK. (0,51)







Dimensions are shown: Inches (mm) Specifications and dimensions subject to change




TERMINATIONS ----




Not available with T102 model.




AV VERTICAL RIGHT ANGLE, PC THRU-HOLE




NOTE: Terminal bend radii and lead-in manufacturing option.
















T101MH9V3BE **SPDT**



Dimensions are shown: Inches (mm) Specifications and dimensions subject to change





TERMINATIONS ----


V3 VERTICAL MOUNT, V-BRACKET



T201MH9V3BE **DPDT**







CONTACT MATERIAL

OPTION CODE	CONTACT MATERIAL	TERMINAL PLATING	RATINGS			
В	GOLD ¹	GOLD ¹ MATTE-TIN ⁶	LOW LEVEL/ DRY CIRCUIT	0.4 VA MAX. @ 20 V AC OR DC MAX.		
Р						
Q	SILVER ^{4,5}	SILVER ⁵	POWER	TX01 MODELS: 3 AMPS @ 120 V AC OR 28 V DC. ALL OTHER MODELS: 2 AMPS @ 120 V AC OR 28 V DC.		
G R	GOLD OVER SILVER ^{2,3}	GOLD ³ MATTE-TIN ⁶	LOW LEVEL/DRY CIRCUIT OR POWER	TX01 MODELS: 0.4 VA MAX @ 20 V AC OR DC MAX. OR 3 AMPS @ 120 V AC OR 28 V DC. ALL OTHER MODELS: 0.4 VA MAX @ 20 V AC OR DC MAX. OR 2 AMPS @ 120 V AC OR 28 V DC.		

^{*} Note: See Technical Data section of this catalog for RoHS compliant and compatible definitions and specifications.

- ¹ CONTACTS & TERMINALS: Copper alloy, with gold plate over nickel plate.
- ² END CONTACTS: Coin silver, with gold plate over nickel plate.
- $^{\rm 3}$ CENTER CONTACTS & ALL TERMINALS: Copper alloy, with gold plate over nickel plate.
- ⁴ END CONTACTS: Coin silver, silver plated.
- $^{\rm 5}$ CENTER CONTACT & ALL TERMINALS: Copper alloy, silver plated.
- ⁶ TERMINALS: Copper alloy, with matte-tin over nickel plate.

All models with all options when ordered with R, G, or Q contact material.


B contact material standard with A, AV, V3 & W terminations.

Q contact material standard with C & Z terminations.

SEAL









AVAILABLE HARDWARE

759D02000 SEALING BOOT



* Note: For use with S1 actuator style when combined with T, TK, and CF bushings.





Dimensions are shown: Inches (mm) Specifications and dimensions subject to change





Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

C&K Switches:

T101MCFZGE T103SCFCQE T101KAKE T101KH9AK T101SK9V3BE T105SH9AVME T103SK9AVBE
T102M1TKZBE T103M1TKZBE T101MCFAQE T101STV3GE T103P3TABE T102MH9AVQE T103LTABE
T101SY9CBE T101SHARE T103STABE T101SHV3GE T103MTABE T101P3T9V3QE T102MH9AVPE
T101L1T9V3QE T101P3TCBE T101P3T9CBE T101L1H9V3QE T102SHAVBE T103MH9V3QE T103MH9AVQE