

## Bi-colour LED

10-2H12.314C



<https://eao.com/p/10-2H12.314C>

Your product:

---



## 10-2H12.314C Bi-colour LED

### OPERATING-/INDICATION PART

**Illumination colour:** Green / Yellow

### ELECTRICAL CHARACTERISTICS

**Operating voltage:** 24 V DC +10%

**Operation current:** 15 mA  $\pm$ 15 %

**Lumi. Intensity:** 900/550 mcd

### MECHANICAL CHARATERISTIC

**Weight:** 0.002 kg

### CERTIFICATE

**REACH:** REACH compliant

**RoHS:** RoHS compliant


### OTHER

**Short Description:** Bi-colour LED, BA9s, Green / Yellow, 24 V DC +10%


**Kind of illumination:** Bi-colour-LED

**Hints:** The max. overall length of the lamp may not exceed 25mm,Electrical and optical data are measured at 25 °C,The specified 6 V DC, 24 V DC Bi-colour; 130 V AC, 130 V DC and 230 V AC versions are built with a protection diode,Luminosity and wave length variations caused by LED manufacturing processes may cause slight differences regarding the illumination. The customer has to decide what resistor shall be used to the LED

**Wiring diagrams:**



**Dimension drawings:**



A = (standard)  
B = (super bright)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[EAO:](#)

[10-2H12.314C](#)