

Single-LED

10-2J06.3144



<https://eao.com/p/10-2J06.3144>

Your product:



10-2J06.3144

Single-LED

OPERATING-/INDICATION PART

Illumination colour: Yellow

ELECTRICAL CHARACTERISTICS

Operating voltage: 6 V DC +10%

Operation current: 15 mA \pm 15 %

Lumi. Intensity: 300 mcd

MECHANICAL CHARATERISTIC

Weight: 0.002 kg

CERTIFICATE

REACH: REACH compliant

RoHS: RoHS compliant


OTHER

Short Description: Single-LED, T1 ¼ MG, Yellow, 6 V DC +10%


Kind of illumination: Single-LED

Hints: Due to high surface temperatures, the series resistor must not be soldered directly to the terminals of the equipment (use a terminal plate),When using AC/DC types with AC operation, slight flickering can occur,The luminous intensity stated is for when used with DC,Electrical and optical data are measured at 25 °C,The specified versions are built with a protection diode (halve wave rectifier) in series and the LED,Luminosity and wave length variations caused by LED manufacturing processes may cause slight differences regarding the illumination. The customer has to decide what resistor shall be used to the LED,Where supply voltages are over 48 V, a voltage-reduction element (external protective series resistor) must be used.,Keep to the country specific safety instructions











Wiring diagrams:



Dimension drawings:



Where to Buy

Distributor		Quantity in Stock		
	element14 Singapore	123 in stock	Buy	
	Farnell UK	123 in stock	Buy	
	Distrelec	25 in stock	Buy	
	DigiKey	23 in stock	Buy	
	RS UK	15 in stock	Buy	

Show more +

Powered by oemsecrets.com

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[EAO:](#)

[10-2J06.3144](#)