

# Single-LED

10-2J12.1069



<https://eao.com/p/10-2J12.1069>

Your product:

---



## 10-2J12.1069

### Single-LED

#### OPERATING-/INDICATION PART

**Illumination colour:** White

#### ELECTRICAL CHARACTERISTICS

**Operating voltage:** 24 V AC/DC +10%

**Operation current:** 2,5 - 5,00 mA  $\pm$ 15 %

**Lumi. Intensity:** 750 mcd

#### MECHANICAL CHARATERISTIC

**Weight:** 0.001 kg


#### OTHER

**Short Description:** Single-LED, T1  $\frac{3}{4}$  MG, White, 24 V AC/DC +10%


**Kind of illumination:** Single-LED

**Hints:** Due to high surface temperatures, the series resistor must not be soldered directly to the terminals of the equipment (use a terminal plate). When using AC/DC types with AC operation, slight flickering can occur. The luminous intensity stated is for when used with DC. Electrical and optical data are measured at 25 °C. The specified versions are built with a protection diode (half wave rectifier) in series and the LED. Luminosity and wave length variations caused by LED manufacturing processes may cause slight differences regarding the illumination. The customer has to decide what resistor shall be used to the LED. Where supply voltages are over 48 V, a voltage-reduction element (external protective series resistor) must be used. Keep to the country specific safety instructions











**Wiring diagrams:**



Dimension drawings:



Where to Buy

	Distributor	Quantity in Stock	
	Distrelec	869 in stock	<a href="#">Buy</a> 
	DigiKey	324 in stock	<a href="#">Buy</a> 
	RS UK	319 in stock	<a href="#">Buy</a> 
	Mouser Electronics	175 in stock	<a href="#">Buy</a> 
	Farnell UK	161 in stock	<a href="#">Buy</a> 

[Show more](#) 

Powered by oemsecrets.com

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[EAO:](#)

[10-2J12.1069](#)