

Single-LED

10-2J19.1046



<https://eao.com/p/10-2J19.1046>

Your product:



10-2J19.1046

Single-LED

OPERATING-/INDICATION PART

Illumination colour: Blue

ELECTRICAL CHARACTERISTICS

Operating voltage: 48 V AC/DC +10%

Operation current: 4 - 8 mA \pm 15 %

Lumi. Intensity: 400 mcd

MECHANICAL CHARACTERISTIC

Weight: 0.001 kg

CERTIFICATE

REACH: REACH compliant

RoHS: RoHS compliant

OTHER

Short Description: Single-LED, T1 ¼ MG, Blue, 48 V AC/DC +10%


Kind of illumination: Single-LED

Hints: Due to high surface temperatures, the series resistor must not be soldered directly to the terminals of the equipment (use a terminal plate). When using AC/DC types with AC operation, slight flickering can occur. The luminous intensity stated is for when used with DC. Electrical and optical data are measured at 25 °C. The specified versions are built with a protection diode (half wave rectifier) in series and the LED. Luminosity and wave length variations caused by LED manufacturing processes may cause slight differences regarding the illumination. The customer has to decide what resistor shall be used to the LED. Where supply voltages are over 48 V, a voltage-reduction element (external protective series resistor) must be used. Keep to the country specific safety instructions











Wiring diagrams:



Dimension drawings:



Where to Buy

Distributor		Quantity in Stock		
	DigiKey	21 in stock	Buy	
	Mouser Electronics	0 in stock	Buy	
	Newark	0 in stock	Buy	
	Sager	0 in stock	Buy	
	RS Americas	0 in stock	Buy	

Powered by oemsecrets.com

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[EAO:](#)

[10-2J19.1046](#)