

Switching element

46-312.1Z10



<https://eao.com/p/46-312.1Z10>

Your product:



46-312.1Z10

Switching element

FRONT

Colour: Red

ELECTRICAL CHARACTERISTICS

Contacts: 1 NC

Switching voltage and switching current:

at AC-15				
Voltage	24 V	120 V	240 V	600 V
Current	10 A	6 A	3 A	1,2 A
at DC-13				
Voltage	24 V	120 V	240 V	
Current	5 A	1,1 A	0,55 A	

Insulation voltage: Ui 690V - Uimp 4KV (IEC-EN60947-1)

Pollution degree: 3

Thermal current Ith: 10 A (IEC-EN60947-1)

MECHANICAL CHARACTERISTIC

Terminal: Screw terminal

Contact material: Silver

Switching system: Slow-make switching element

Mechanical lifetime: 1 Mio. cycles of operation

Operating force: 2 N

Tightening torque: 0.8 ... 1 Nm for screw terminal

Weight: 0.011 kg

AMBIENT CONDITION

IP Protection: IP20


Operating temperature:	– 25 °C ... + 55 °C
Shock resistance:	30g, 18ms (EN-IEC 60068-2-27) 50g, 11ms (EN-IEC 60068-2-27)
Vibration resistance:	5g f= 2...500Hz (EN-IEC 60068-2-6)
Climate resistance:	+25°C-97%RH / +45°C-93%RH (IEC-EN60068-2-30)

CERTIFICATE


Approbations:	CSA, EAC, UL
Conformities:	CE
REACH:	REACH compliant
RoHS:	RoHS compliant
Standards:	CSA C22-2, IEC EN 60947-1, IEC EN 60947-5-1, UL508

OTHER

Short Description:	Switching element, Slow-make switching element, Silver, 1 NC, Screw terminal
Material:	Plastic
Wiring diagrams:	



Dimension drawings:



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[EAO:](#)

[46-312.1Z10](#)