


Switching element

61-8720.37



<https://eao.com/p/61-8720.37>

Your product:



61-8720.37

Switching element

ELECTRICAL CHARACTERISTICS

Contacts:	2 NO		
Switching voltage and switching current:	Switch rating AC with gold contact		
	Service category AC-15		
	according to EN IEC 60947-5-1		
	Voltage	50 VAC	
	Current	0.5 A	
	Switch rating DC with gold contact		
	Service category DC-13		
	according to EN IEC 60947-5-1		
	Voltage	50 VDC	
	Current	0.1 A	
Rated Operational Voltage Ue:	50 VAC / DC, according to EN / IEC 60947-5-1		
Rated impulse withstand voltage Uimp:	0,8 kV, according to EN / IEC 60947-5-1		
Rated insulation voltage Ui:	320 VAC, according to EN / IEC 60947-5-1		
Recommended minimum operational data:	Voltage	10 VAC/DC	
	Current	2 mA	
Switching rating:	50 V AC/DC @ 0,3 A		
Electric strength:	4000 VAC, 50 Hz, 1 minute, as per DIN / IEC 60512-2 between all terminals and earth		
Overvoltage category:	III, according to EN / IEC 60947-5-1		
Pollution degree:	3, according to EN IEC 60947-1		
Protection class:	II, according to EN / IEC 61058-1		
Standards:	The switches comply with the “Standards for low-voltage switching devices” EN IEC 61058-1, EN IEC 60947-5-1		
Thermal current Ith:	3 A		

MECHANICAL CHARACTERISTIC

Terminal:	Plug-in terminal, 2.8 x 0.5 mm
Contact material:	Gold

Switching system:	Slow-make switching element
Switching system:	Double-break slow-make system, contact opening width 2 x 1.5 mm, with 2 x 2 contact points per switching element. NC-contact elements in the slow-make elements fulfill requirements of switches with forced opening as per EN / IEC 60947-5-12.17.
Switching positions:	3 positions
Wire cross section:	1 wire flexible: 0.5 ... 0.75 mm ² 1 wire super flexible: 0.5 mm ² 1 wire rigid: 0.5 ... 1.5 mm ² 2 wires flexible: 0.5 ... 0.75 mm ² 2 wires super flexible: 0.5 mm ² 2 wires rigid: 0.5 ... 1.5 mm ²
Weight:	0.008 kg

AMBIENT CONDITION


IP Protection:	IP40
Operating temperature:	– 25 °C ... + 55 °C
Storage temperature:	– 40 °C ... + 85 °C
Shock resistance:	Max. 100 m / s ² , pulse width, 3-axis (sinusoidal EN IEC 60068-2-27)
Vibration resistance:	Max. 100 m / s ² from 10 Hz ... 500 Hz, (sinusoidal EN IEC 60068-2-6)
Climate resistance:	Damp heat, cyclic: 96 hours, + 25 °C/97 %, + 55 °C/93 % relative humidity, as per EN IEC 60068-2-30 Damp heat, steady: 56 days, + 40 °C/93 % relative humidity, according to EN IEC 60068-2-78 Rapid change of temperature: 100 cycles, – 40 °C ... + 80 °C, as per EN / IEC 60068-2-14

CERTIFICATE


Approbations:	CB (IEC 60947-5-1), CB (IEC 61058-1), CENELEC CCA-NTR (EN 60947-5-1), CQC, CSA, DNV, EAC, ENEC (EN 61058-1), NFF, SEV (EN / IEC 60947-5-1), UL
Conformities:	CE, UKCA, 2011 / 65 / EC (RoHS), 2014 / 35 / EU (LVD)
REACH:	REACH compliant
RoHS:	RoHS compliant

OTHER

Short Description:	Switching element, Slow-make switching element, 50 V AC/DC @ 0,3 A, Gold, 2 NO, Plug-in terminal, 2.8 x 0.5 mm
Material:	Plastic, according to UL 94 V0
Hints:	With lamp terminal
Wiring diagrams:	



Component layouts:



Where to Buy

	Distributor	Quantity in Stock	
	Mouser Electronics	22 in stock	Buy 
	Digi-Key	8 in stock	Buy 
	Newark Electronics	0 in stock	Buy 
	Sager	0 in stock	Buy 
	RS Americas	0 in stock	Buy 

Powered by oemsecrets.com

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[EAO:](#)

[61-8720.37](#)