


Switching element

84-8511.4340



<https://eao.com/p/84-8511.4340>

Your product:



84-8511.4340

Switching element

OPERATING-/INDICATION PART

Illumination colour: Yellow

ELECTRICAL CHARACTERISTICS

Contacts: 1 NO

Operating voltage: 12 V DC $\pm 10\%$

Operation current: 10 mA

| | | |
|---|---------|-----------|
| Switching voltage and switching current: | Voltage | 42 VAC/DC |
| | Current | 100 mA |
| | Power | max. 2 W |

Switching rating: 42 V AC/DC @ 0,1 A

Electric strength: 500 VAC, 50 Hz, 1 minute according to DIN IEC 60512-2

MECHANICAL CHARACTERISTIC

Terminal: Flat ribbon cable

Contact material: Gold-plated silver

Switching system: Short-travel element

Switching system: Short-travel snap-action switching system with two independent contact points and tactile operation
Guarantees reliable switching even of very light loads. Fitted with 1 normally open contact

Mechanical lifetime: ≥ 1 Mio. cycles of operation

Operating force: 4.5 N ± 1 N (measured at the lens)

Operating Travel: ca. 0.5 mm

Weight: 0.015 kg

AMBIENT CONDITION


| | |
|-------------------------------|---|
| IP Protection: | IP40 rear side, standard version, IP67 rear side, fully sealed version, with mounted actuator only. |
| Operating temperature: | – 25 °C ... + 70 °C |
| Storage temperature: | – 40 °C ... + 85 °C |
| Shock resistance: | Max. 100 m / s ² , pulse width, 3-axis (sinusoidal EN IEC 60068-2-27) |
| Vibration resistance: | Max. 50 m / s ² from 10 Hz ... 500 Hz, 10 cycles, 3-axis (sinusoidal EN IEC 60068-2-6) |

CERTIFICATE

| | |
|---------------|-----------------|
| REACH: | REACH compliant |
| RoHS: | RoHS compliant |

OTHER











| | |
|---------------------------|--|
| Short Description: | Switching element, Short-travel element, 42 V AC/DC @ 0,1 A, Gold-plated silver, 1 NO, Flat ribbon cable |
| Material: | Plastic |
| Hints: | LED and built-in resistor included, Standard version: Cable length 300 mm, Other options on request: Customisation of cable and connectors, rear side fully sealed (IP 67), Protection degree (rear side): IP 40, upgrade to IP 67 with plug Part No. 84-900 possible. With applications where strong vibrations occur, the plugs may become loose, Luminosity and wave length variations caused by LED manufacturing processes may cause slight differences regarding the illumination. The customer has to decide what resistor shall be used to the LED |
| Wiring diagrams: | |



Component layouts:



Where to Buy

| Distributor | | Quantity in Stock | | |
|---|--------------------|-------------------|-----|---|
|  | DigiKey | 10 in stock | Buy |  |
|  | Mouser Electronics | 0 in stock | Buy |  |
|  | Newark | 0 in stock | Buy |  |
|  | RS Americas | 0 in stock | Buy |  |
|  | Sager | 0 in stock | Buy |  |

Powered by oemsecrets.com

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[EAO:](#)

[84-8511.4340](#)